

## IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

## CB TEST CERTIFICATE

|   |   |
|---|---|
| Product   | Switch Mode Power Supply  |
| Name and address of the applicant   | TDK-LAMBDA UK LTD<br>KINGSLEY AVE ILFRACOMBE DEVON EX34 8ES<br>UNITED KINGDOM   |
| Name and address of the manufacturer  | TDK-LAMBDA UK LTD<br>KINGSLEY AVE ILFRACOMBE DEVON EX34 8ES<br>UNITED KINGDOM   |
| Name and address of the factory<br><i>Note: When more than one factory, please report on page 2</i> | TDK-LAMBDA UK LTD<br>KINGSLEY AVE ILFRACOMBE DEVON EX34 8ES<br>UNITED KINGDOM<br><input checked="" type="checkbox"/> Additional Information on page 2 |
| Ratings and principal characteristics   | 100-240Vac nominal, (90-264Vac including tolerances).<br>47-440Hz, 11A rms Max. (see Test Report for details)   |
| Trademark (if any)  | TDK-Lambda<br>  |
| Type of Customer's Testing Facility (CTF) Stage used  | CTF Stage 3   |
| Model / Type Ref.   | NV-700, NV700, NV7<br>See Page 2  |
| Additional information (if necessary may also be reported on page 2)                                | <input checked="" type="checkbox"/> Additional Information on page 2  |
| A sample of the product was tested and found to be in conformity with                               | IEC 61010-1(ed.3)   |
| As shown in the Test Report Ref. No. which forms part of this Certificate                           | E331788-A15-CB-2 issued on 2018-04-26   |

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

Date: 2018-04-27  
Original Issue Date: 2015-09-22

Signature:

  
Jan-Erik StorgaardFor full legal entity names see [www.ul.com/ncbnames](http://www.ul.com/ncbnames)



Ref. Certif. No.

**DK-48638-A2-UL**

**Model Details:**

NV700 (see model differences for details of NV700 range model configurations)

**Factories:**

PANYU TRIO MICROTRONIC CO. LTD  
SHIJI INDUSTRIAL ESTATE DONGYONG NANSHA GUANGZHOU GUANGDONG  
CHINA

**Additional Information:**

The original report was modified to include the following changes/additions:  
To add an alternate boost capacitor C12/C13 to the critical components list.

Additionally evaluated to EN 61010-1:2010.  
National Differences specified in the CB Test Report.

**Additional information (if necessary)**



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see [www.ul.com/ncbnames](http://www.ul.com/ncbnames)

Date: 2018-04-27  
Original Issue Date: 2015-09-22

Signature:   
Jan-Erik Storgaard