





Test Report issued under the responsibility of



<b>TEST REPORT</b>	
<b>IEC 60950-1: 2005 (2nd Edition) and/or EN 60950-1:2006</b>	
<b>Information technology equipment – Safety –</b>	
<b>Part 1: General requirements</b>	
Report Reference No. ....	2520400-3336-0018 ( 140256 ) CB/DE1- 36535 / A3
Tested by (name + signature) .....	Frank Richter 
Approved by (name + signature) .....	Günter Straube 
Date of issue.....	2010-09-16
CB Testing Laboratory .....	VDE Testing and Certification Institute
Address .....	Merianstrasse 28, D-63069 Offenbach, Germany
Testing location / procedure .....	CBTL <input type="checkbox"/> RMT <input type="checkbox"/> SMT <input type="checkbox"/> WMT <input checked="" type="checkbox"/> TMP <input type="checkbox"/>
Testing location / address .....	TDK Innoveta Inc. 3320 Matrix Drive, Suite 100, Richardson, Texas 75082, USA WMT (TDAP File no. 2520400-9501-0001)
Applicant's name .....	TDK Innoveta Inc.
Address .....	3320 Matrix Drive, Suite 100, Richardson, Texas 75082, USA
<b>Test specification:</b>	
Standard .....	IEC 60950-1:2005 (2 <sup>nd</sup> Edition) ;EN 60950-1:2006+A11:2009-03 DIN EN 60950-1:2006 + A11 ( VDE 0805 Teil 1 + A11): 2009-11
Test procedure.....	CB –scheme, VDE
Non-standard test method.....	N/A
Test Report Form No. ....	IECEN60950_1C
Test Report Form(s) Originator .....	SGS Fimko Ltd
Master TRF.....	2006-06
<b>Copyright © 2006 IEC System for Conformity Testing and Certification of Electrical Equipment (IECEE), Geneva, Switzerland. All rights reserved.</b>	
This publication may be reproduced in whole or in part for non-commercial purposes as long as the IECEE is acknowledged as copyright owner and source of the material. IECEE takes no responsibility for and will not assume liability for damages resulting from the reader's interpretation of the reproduced material due to its placement and context.	
If this Test Report Form is used by non-IECEE members, the IECEE/IEC logo shall be removed	
<b>This report is not valid as a CB Test Report unless signed by an approved CB Testing Laboratory and appended to a CB Test Certificate issued by an NCB in accordance with IECEE 02.</b>	

<b>Test item description</b> .....	DC DC Converter for building in		
Trade Mark .....	TDK		
Manufacturer .....	TDK Innoveta Inc.		
Model/Type reference .....	iQL Series (see model matrix appendix 1)		
Serial Number.....			
Ratings .....			
	Input:	DC 36 - 60 V (SELV), or DC 36 – 75V (TNV-2), max. 10A	See main report
	Output:	(SELV) refer to model matrix	
	Ambient:	Max. 125°C at Q403	

**Copy of marking plate:**  
See main report

<b>Summary of testing: (see main test report)</b>			
Clause 1.5	Components .....	<input checked="" type="checkbox"/> Pass	<input type="checkbox"/> N/A
Clause 1.6	Power interface .....	<input checked="" type="checkbox"/> Pass	<input type="checkbox"/> N/A
Clause 1.7	Markings and instructions.....	<input checked="" type="checkbox"/> Pass	<input type="checkbox"/> N/A
Clause 2.1	Protection from electric shock and energy hazards .....	<input checked="" type="checkbox"/> Pass	<input type="checkbox"/> N/A
Clause 2.2	SELV circuits .....	<input checked="" type="checkbox"/> Pass	<input type="checkbox"/> N/A
Clause 2.3	TNV circuits .....	<input checked="" type="checkbox"/> Pass	<input type="checkbox"/> N/A
Clause 2.4	Limited current circuits .....	<input type="checkbox"/> Pass	<input checked="" type="checkbox"/> N/A
Clause 2.5	Limited power sources .....	<input type="checkbox"/> Pass	<input checked="" type="checkbox"/> N/A
Clause 2.6	Provisions for earthing and bonding .....	<input checked="" type="checkbox"/> Pass	<input type="checkbox"/> N/A
Clause 2.7	Overcurrent and earth fault protection in primary circuits .....	<input checked="" type="checkbox"/> Pass	<input type="checkbox"/> N/A
Clause 2.8	Safety interlocks.....	<input type="checkbox"/> Pass	<input checked="" type="checkbox"/> N/A
Clause 2.9	Electrical insulation .....	<input checked="" type="checkbox"/> Pass	<input type="checkbox"/> N/A
Clause 2.10	Clearances, creepage distances and distances through insulation :	<input checked="" type="checkbox"/> Pass	<input type="checkbox"/> N/A
Clause 3.1	Wirings.....	<input checked="" type="checkbox"/> Pass	<input type="checkbox"/> N/A
Clause 3.2	Connection to an a.c. mains supply or a d.c. mains supply .....	<input checked="" type="checkbox"/> Pass	<input type="checkbox"/> N/A
Clause 3.3	Wiring terminals for connection of external conductors .....	<input checked="" type="checkbox"/> Pass	<input type="checkbox"/> N/A
Clause 3.4	Disconnection from the mains supply .....	<input type="checkbox"/> Pass	<input checked="" type="checkbox"/> N/A
Clause 3.5	Interconnection of equipment .....	<input checked="" type="checkbox"/> Pass	<input type="checkbox"/> N/A
Clause 4.1	Stability.....	<input type="checkbox"/> Pass	<input checked="" type="checkbox"/> N/A
Clause 4.2	Mechanical strength .....	<input type="checkbox"/> Pass	<input checked="" type="checkbox"/> N/A
Clause 4.3	Design and construction.....	<input type="checkbox"/> Pass	<input checked="" type="checkbox"/> N/A
Clause 4.4	Protection against hazardous moving parts .....	<input type="checkbox"/> Pass	<input checked="" type="checkbox"/> N/A
Clause 4.5	Thermal requirements .....	<input checked="" type="checkbox"/> Pass	<input type="checkbox"/> N/A
Clause 4.6	Openings in enclosures.....	<input type="checkbox"/> Pass	<input checked="" type="checkbox"/> N/A
Clause 4.7	Resistance to fire .....	<input checked="" type="checkbox"/> Pass	<input type="checkbox"/> N/A
Clause 5.1	Touch current and protective conductor current.....	<input type="checkbox"/> Pass	<input checked="" type="checkbox"/> N/A
Clause 5.2	Electric strength .....	<input checked="" type="checkbox"/> Pass	<input type="checkbox"/> N/A
Clause 5.3	Abnormal operating and fault conditions .....	<input checked="" type="checkbox"/> Pass	<input type="checkbox"/> N/A
Clause 6	Connection to telecommunication networks.....	<input checked="" type="checkbox"/> Pass	<input type="checkbox"/> N/A
Clause 7	Connection to cable distribution systems .....	<input type="checkbox"/> Pass	<input checked="" type="checkbox"/> N/A
Annex B	Motor Tests under abnormal conditions .....	<input type="checkbox"/> Pass	<input checked="" type="checkbox"/> N/A
Annex C	Transformers.....	<input checked="" type="checkbox"/> Pass	<input type="checkbox"/> N/A
Annex G	Alternative Method for determining minimum clearances .....	<input type="checkbox"/> Pass	<input checked="" type="checkbox"/> N/A
Annex M	Criteria for telephone ringing signals.....	<input type="checkbox"/> Pass	<input checked="" type="checkbox"/> N/A
Annex U	Insulated winding wires for use without interleaved insulation .....	<input type="checkbox"/> Pass	<input checked="" type="checkbox"/> N/A

<b>Test item particulars</b> .....	
Equipment mobility.....	<input type="checkbox"/> movable <input type="checkbox"/> hand-held <input type="checkbox"/> stationary <input type="checkbox"/> fixed <input type="checkbox"/> transportable <input checked="" type="checkbox"/> for building-in
Connection to the mains .....	<input type="checkbox"/> pluggable equipment <input type="checkbox"/> direct plug-in <input type="checkbox"/> permanent connection <input checked="" type="checkbox"/> for building-in
Operating condition.....	<input checked="" type="checkbox"/> continuous <input type="checkbox"/> short-time <input type="checkbox"/> intermittent
Over voltage category .....	<input checked="" type="checkbox"/> OVC I <input type="checkbox"/> OVC II <input type="checkbox"/> OVC III <input type="checkbox"/> OVC IV
Mains supply tolerance (%).....	Unit is rated 0% tolerance
Tested for IT power systems .....	<input type="checkbox"/> Yes <input checked="" type="checkbox"/> No
IT testing, phase-phase voltage (V) .....	--
Class of equipment .....	<input type="checkbox"/> Class I <input type="checkbox"/> Class II <input type="checkbox"/> Class III <input checked="" type="checkbox"/> Not classified
Mass of equipment (kg).....	<18kg
Pollution degree .....	<input checked="" type="checkbox"/> PD 2 <input type="checkbox"/> PD 3
IP protection class .....	IP---
<b>Possible test case verdicts</b>	
- test case does not apply to the test object.....	N/A (Not Applicable)
- test object does meet the requirement .....	P (Pass)
- test object does not meet the requirement .....	F (Fail)
<b>Testing</b> .....	
Date of receipt of test item.....	2010-09-16
Date(s) of performance of tests .....	2010-09-16
<b>General remarks:</b>	
The test results presented in this report relate only to the object tested. This report shall not be reproduced, except in full, without the written approval of the Issuing testing laboratory.	
"(see Enclosure #)" refers to additional information appended to the report. "(see appended table)" refers to a table appended to the report.	
Throughout this report a <input type="checkbox"/> comma / <input checked="" type="checkbox"/> point is used as the decimal separator.	
<b>Factory</b> (for information only)	
Name.....	TDK Innoveta Inc.
Address.....	3320 Matrix Drive, Suite 100, Richardson, Texas 75082, USA
Name.....	TDK Lambda Malaysia
Address .....	PL033 Kawasan perindustrian Senai, Locked Bag No. 110 81400 Senai, Johor, Malaysia

**General product information:****Conditions of Installation:**

The equipment shall be installed in compliance with the enclosure, mounting, spacing, casualty and segregation requirements of the end-use application.

DC-DC Power Supply for building-in, ratings see page 2.

The units were tested with a maximum continuous output.

The manufacturer specified max. 125°C at Q403

The Electrical and Fire Enclosures are to be provided by the end product.

**The power supply series provides Basic insulation based on DC 75 V, between input and output. (see main report)**

Operating Conditions:

Units are components within customer's end-use system. Input to converters is DC 40 - 75 V (SELV)

A. If the input meets all requirements for SELV, then the output may be considered SELV

B. If the input meets all requirements for TNV-2, then the output may be considered SELV

C. If the input meets all requirements for ELV, then the output may be considered ELV

The unit is suitable for a maximum manufacturer's recommended ambient operating temperature (T<sub>mra</sub>) of 25 deg C.

Unit is for building in (Class I or Class II) and designed for Pollution Degree 2 and Overvoltage Category 1.

The power models are not internally fused. An external input line normal blow fuse with a max. value of 20A is required.

The product has been tested according to standard IEC 60950-1:2005 (2 <sup>nd</sup> Edition) / EN 60950-1:2006 and those deviations taken into account of <b>(see main test report)</b>				
<input checked="" type="checkbox"/> CENELEC common modifications	<input checked="" type="checkbox"/> United Kingdom	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>
<input checked="" type="checkbox"/> Finland	<input checked="" type="checkbox"/> Denmark	<input checked="" type="checkbox"/> Ireland	<input type="checkbox"/>	<input type="checkbox"/>
<input checked="" type="checkbox"/> Sweden	<input checked="" type="checkbox"/> Germany	<input checked="" type="checkbox"/> Spain	<input type="checkbox"/>	<input type="checkbox"/>
<input checked="" type="checkbox"/> Norway	<input checked="" type="checkbox"/> Switzerland	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>

<input checked="" type="checkbox"/> <b>CB Bull. NATIONAL DIFFERENCES IEC 60950-1(2<sup>nd</sup> Edition)</b>				
<input checked="" type="checkbox"/> Switzerland	<input checked="" type="checkbox"/> Spain	<input checked="" type="checkbox"/> Ireland	<input checked="" type="checkbox"/> Sweden	<input checked="" type="checkbox"/> USA
<input checked="" type="checkbox"/> Germany	<input checked="" type="checkbox"/> Finland	<input checked="" type="checkbox"/> Korea	<input checked="" type="checkbox"/> Group Differences	<input type="checkbox"/>
<input checked="" type="checkbox"/> Denmark	<input checked="" type="checkbox"/> United Kingdom	<input checked="" type="checkbox"/> Norway	<input checked="" type="checkbox"/> Canada	<input type="checkbox"/>

These tests fulfil the requirements of standard EN ISO/IEC 17025.

<b>This test report includes the following Appendices:</b>		
Appendix No.	Description	Page(s)
1	Model Matrix	1

Appendix to test report reference No. :		2520400-3336-0018
VDE Test- and Certification Institute Merianstrasse 28 D - 63069 Offenbach	IEC 60950-1:2005 (2 <sup>nd</sup> Edition) and/or EN 60950-1:2006 DIN EN 60950-1 (VDE0805 )	
TYPE OF APPLIANCE :	DC DC Converter	
Made by :	TDK	
Trade mark :	TDK	
Model/type ref. :	iQL48020A120V-0xx	
Rated :	see main test report	
Commission received from :	Steven F. McKitrick	Date: 2010-09-16
<i>Modification on the appliance</i>		
1. Add model iQL48020A120V-0xx (-R) to the VDE licences 40020283, for model differences refer to model matrix		
Remarks: No testing necessary		