

UL TEST REPORT AND PROCEDURE

Standard:	UL 60950-1, 2nd Edition, 2011-12-19 (Information Technology Equipment - Safety - Part 1: General Requirements) CSA C22.2 No. 60950-1-07, 2nd Edition, 2011-12 (Information Technology Equipment - Safety - Part 1: General Requirements)
Certification Type:	Component Recognition
CCN:	QQGQ2, QQGQ8 (Power Supplies for Information Technology Equipment Including Electrical Business Equipment)
Product:	AC-DC Power Supply
Model:	DRB15-24-1-xyz Where x, y and z can be any alphanumeric character or blank and is non safety relevant information.
Rating:	Input: 100-240 Vac; 0.39 A max.; 50/60 Hz Output: 24-28 Vdc / 0.63-0.54 A; Max. output power: 15 W.
Applicant Name and Address:	TDK-LAMBDA UK LTD KINGSLEY AVE ILFRACOMBE DEVON EX34 8ES UNITED KINGDOM

This is to certify that representative samples of the products covered by this Test Report have been investigated in accordance with the above referenced Standards. The products have been found to comply with the requirements covering the category and the products are judged to be eligible for Follow-Up Service under the indicated Test Procedure. The manufacturer is authorized to use the UL Mark on such products which comply with this Test Report and any other applicable requirements of UL LLC ('UL') in accordance with the Follow-Up Service Agreement. Only those products which properly bear the UL Mark are considered as being covered by UL's Follow-Up Service under the indicated Test Procedure.

The applicant is authorized to reproduce the referenced Test Report provided it is reproduced in its entirety.

UL authorizes the applicant to reproduce the latest pages of the referenced Test Report consisting of the first page of the Specific Technical Criteria through to the end of the Conditions of Acceptability.

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL.

Prepared by: Grzegorz Goraj

Reviewed by: Mengis Tesfay

Supporting Documentation

The following documents located at the beginning of this Procedure supplement the requirements of this Test Report:

- A. Authorization - The Authorization page may include additional Factory Identification Code markings.
- B. Generic Inspection Instructions -
- i. Part AC details important information which may be applicable to products covered by this Procedure. Products described in this Test Report must comply with any applicable items listed unless otherwise stated in the body of this Test Report.
 - ii. Part AE details any requirements which may be applicable to all products covered by this Procedure. Products described in this Test Report must comply with any applicable items listed unless otherwise stated in the body of each Test Report.
 - iii. Part AF details the requirements for the UL Certification Mark which is not controlled by the technical standard used to investigate these products. Products are permitted to bear only the Certification Mark(s) corresponding to the countries for which it is certified, as indicated in each Test Report.

Product Description

The equipment is a switching power supply intended to be mounted in vertical position on DIN rail. Output voltage can be adjusted from 24V to 28V (total output power 15W).

Model Differences

N/A

Technical Considerations

- Equipment mobility : for building-in
- Connection to the mains : n/a (for building-in, terminal block suitable for field wiring)
- Operating condition : continuous
- Access location : n/a (for building-in)
- Over voltage category (OVC) : OVC II
- Mains supply tolerance (%) or absolute mains supply values : 85-264 Vac
- Tested for IT power systems : No
- IT testing, phase-phase voltage (V) : n/a
- Class of equipment : Class I (earthed)
- Considered current rating of protective device as part of the building installation (A) : 20
- Pollution degree (PD) : PD 2
- IP protection class : IP X0
- Altitude of operation (m) : up to 3 000 m
- Altitude of test laboratory (m) : less than 2000 meters
- Mass of equipment (kg) : approx. 0.085
- The product was submitted and evaluated for use at the maximum ambient temperature (T_{ma}) permitted by the manufacturer's specification of: 70 °C
- The means of connection to the mains supply is: to be determined in end product.
- The product is intended for use on the following power systems: TT, TN
- The equipment disconnect device is considered to be: provided in end product

- The following were investigated as part of the protective earthing/bonding: Printed wiring board trace (refer to Enclosure - Schematics + PWB for layouts)
- The following are available from the Applicant upon request: Installation (Safety) Instructions / Manual
- LEDs provided in the product are considered low power devices: Yes
- The Clearances and Creepage Distances have additionally been assessed for suitability up to 3000 m elevation.
- Model DRB15-24-1 has been tested also for supply 120-373Vdc, not considered as rating.

Engineering Conditions of Acceptability

For use only in or with complete equipment where the acceptability of the combination is determined by UL LLC. When installed in an end-product, consideration must be given to the following:

- The following Production-Line tests are conducted for this product: Electric Strength,
- The end-product Electric Strength Test is to be based upon a maximum working voltage of: Primary-SELV: 241.8 Vrms, 448 Vpk, Primary-Earthed Dead Metal: 335.8 Vrms, 440 Vpk
- The following secondary output circuits are SELV: 24Vdc output
- The following secondary output circuits are at non-hazardous energy levels: 24Vdc output
- The following secondary output circuits are supplied by a Limited Power Source: 24Vdc output
- The power supply terminals and/or connectors are: Suitable for field wiring
- The maximum investigated branch circuit rating is: 20 A
- The investigated Pollution Degree is: 2
- Proper bonding to the end-product main protective earthing termination is: Required
- An investigation of the protective bonding terminals has: Been conducted
- The following input terminals/connectors must be connected to the end-product supply neutral: TB1 (pin 2)
- The following magnetic devices (e.g. transformers or inductor) are provided with an OBJY2 insulation system with the indicated rating greater than Class A (105°C): T1 (class B)
- The following end-product enclosures are required: Fire, Electrical

Additional Information

N/A

Additional Standards

The product fulfills the requirements of: CSA C22.2 No. 60950-1-07 + A1:2011, UL 60950-1 2nd Ed. Revised 2011-12-19

Markings and instructions

Clause Title	Marking or Instruction Details
Power rating - Ratings	Ratings (voltage, frequency/dc, current)
Power rating - Company identification	Listee's or Recognized company's name, Trade Name, Trademark or File Number

Power rating - Model	Model Number
Fuses - Rating	Rated current and voltage and type located on or adjacent to fuse or fuseholder.
Special Instructions to UL Representative N/A	

Production-Line Testing Requirements						
<u>Electric Strength Test Special Constructions - Refer to Generic Inspection Instructions, Part AC for further information.</u>						
Model	Component	Removable Parts	Test probe location	V rms	V dc	Test Time, s
DRB15-24-1	T1	n/a	primary to secondary pins	300 0	4242	1
<u>Earthing Continuity Test Exemptions - This test is not required for the following models:</u>						
DRB15-24-1						
<u>Electric Strength Test Exemptions - This test is not required for the following models:</u>						
N/A						
<u>Electric Strength Test Component Exemptions - The following solid-state components may be disconnected from the remainder of the circuitry during the performance of this test:</u>						
N/A						
<u>Sample and Test Specifics for Follow-Up Tests at UL</u>						
Model	Component	Material	Test	Sample(s)	Test Specifics	
n/a	-	-	-	-	-	