

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST
CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME

SYSTEME CEI D'ACCEPTATION MUTUELLE DE
CERTIFICATS D'ESSAIS DES EQUIPEMENTS
ELECTRIQUES (IECEE) METHODE OC

CB TEST CERTIFICATE**CERTIFICAT D'ESSAI OC**

Product
Produit

Switching Power Supply

Name and address of the applicant
Nom et adresse du demandeur

TDK-LAMBDA CORP
NAGAOKA TECHNICAL CENTER
R&D DIV
2704-1 SETTAYA-MACHI
NAGAOKA-SHI
NIIGATA 940-1195 JAPAN

Name and address of the manufacturer
Nom et adresse du fabricant

TDK-LAMBDA CORP
NAGAOKA TECHNICAL CENTER
R&D DIV
2704-1 SETTAYA-MACHI
NAGAOKA-SHI
NIIGATA 940-1195 JAPAN

Name and address of the factory
Nom et adresse de l'usine

TDK-LAMBDA CORP
2704-1 SETTAYA-MACHI
NAGAOKA-SHI
NIIGATA-KEN 940-1195 JAPAN

*Note: When more than one factory, please report on page 2
Note: Lorsque il y plus d'une usine, veuillez utiliser la 2^{eme} page*

Ratings and principal characteristics
Valeurs nominales et caractéristiques principales

Additional Information on page 2
See Page 2

Trademark (if any)
Marque de fabrique (si elle existe)

TDK·Lambda or **TDK·Lambda**

Type of Manufacturer's Testing Laboratories used
Type de programme du laboratoire d'essais
constructeur

Model / Type Ref.
Ref. De type

See Page 2

Additional information (if necessary may also be
reported on page 2)
Les informations complémentaires (si nécessaire,,
peuvent être indiqués sur la 2^{eme} page

Additionally evaluated to EN 60950-1:2006 /A11:2009/A1:2010/
A12:2011/ A2:2013; National Differences specified in the CB Test
Report.

Additional Information on page 2

A sample of the product was tested and found
to be in conformity with
Un échantillon de ce produit a été essayé et a été
considéré conforme à la

IEC 60950-1(ed.2), IEC 60950-1(ed.2);am1,
IEC 60950-1(ed.2);am2

As shown in the Test Report Ref. No. which forms part
of this Certificate
Comme indiqué dans le Rapport d'essais numéro de
référence qui constitue partie de ce Certificat

4786910627-10 issued on 2015-10-19

This CB Test Certificate is issued by the National Certification Body
Ce Certificat d'essai OC est établi par l'Organisme **National de Certification**



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Denko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2015-10-23

Signature:

Akira Kato



Ref. Certif. No.

JP-12840-UL

Model Details:

JWT75-522, JWT75-5FF, JWT75-525

(may be provided with suffix: "/A", "/B", "/C", "/R", "/RA", "/RB" or "/RC")

Factories:

Wuxi TDK-Lambda Electronics Co Ltd
NO 6 XING CHUANG ER LU WUXI JIANGSU 214028
CHINA

TDK-LAMBDA MALAYSIA SDN BHD
LOT 2 & 3, BATU 9 3/4 KAWASAN PERINDUSTRIAN BANDAR BARU JAYA GADING 26070 KUANTAN
MALAYSIA

ALPS LOGISTICS FACILITIES CO LTD
593-1 NISHIOHASHI TSUKUBA-SHI IBARAKI-KEN 305-0831
JAPAN

TDK-LAMBDA MALAYSIA SDN BHD
PLO33 KAWASAN PERINDUSTRIAN SENAI 81400 SENAI
MALAYSIA

SENDAN ELECTRONICS MFG CO LTD
1010 HABUSHIN NANTO-SHI TOYAMA-KEN 939-1756
JAPAN

Ratings:

Input:

AC 100-240V, 50/60Hz, 1.4A

Output:

JWT75-522	DC +5V/8.0A	DC +12V/4.0A	DC -12V/0.5A
JWT75-5FF	DC +5V/8.0A	DC +15V/3.2A	DC -15V/0.5A
JWT75-525	DC +5V/8.0A	DC +12V/4.0A	DC -5V/0.5A

All current values are maximum values, of separate outputs.

The maximum total output power for each model: 75W

Additional information (if necessary)

Information complémentaire (si nécessaire)



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2015-10-23

Signature:

Akira Kato