

Buffer module – 24V 20A DBM20



TDK-Lambda

Aspectos Destacados

- Previene la pérdida de datos durante los cortes de tensión
- Condensadores electrolíticos para el almacenamiento de energía
- Sin baterías y suministra picos de energía

Especificaciones Clave

- 24V de entrada y 20A de corriente nominal
- 250 ms de hold-up time a 448W
- Encendido / apagado remoto para detener descargas no seguras
- 49 mm de ancho en Carril DIN

Aplicaciones Típicas

- Fabricación de semiconductores
- Procesos de control
- Maquinaria Industrial
- Equipos de test y medida

Product Highlights

- Prevents data loss during brief AC input losses
- Uses electrolytic capacitors to store energy
- No batteries to service or maintain
- Can also provide peak power capability

Key Specifications

- 20A current rating, 24V input
- 250ms additional hold-up time at 448W
- Remote on/off to stop unsafe discharging
- Narrow 49mm width on DIN rail

Typical Applications

- Semiconductor fabrication
- Process control
- Industrial machinery
- Test and measurement equipment