

Programmable DC Load  
SFL series 300W and 1000W



## TDK-Lambda

### Aspectos Destacados

- Control de corriente de alta velocidad
- 7 modos de funcionamiento, incluyendo CC/CR/CP/CV
- Gran pantalla LCD en color de 89 mm
- Almacena y recupera hasta 8 ajustes de memoria

### Especificaciones Clave

- 120V (60A/180A) o 500V (18A/36A)
- Conexión en paralelo de hasta diez unidades
- 3U de altura, 300W 1/2 rack, 1000W full rack
- Interfaz iEEE opcional y medición de ondulación

### Aplicaciones Típicas

- Equipos de ensayo automatizados
- Laboratorios de I+D
- Pruebas de baterías
- Pruebas de fuentes de alimentación

### Product Highlights

- High speed current control
- 7 operating modes including CC/CR/CP/CV
- Large 89mm colour LCD display
- Store and recall up to 8 memory settings

### Key Specifications

- 120V (60A/180A) or 500V (18A/36A) ratings
- Parallel capability of up to ten units
- 3U high, 300W half-rack, 1000W full-rack
- Optional iEEE interface and ripple measurement

### Typical Applications

- Automated Test Equipment
- R&D laboratories
- Battery testing
- Power supply testing