



Test Report issued under  
the responsibility of:



**TEST REPORT**  
**IEC 60950-1**  
**Information technology equipment - Safety -**  
**Part 1: General requirements**

**Report Reference No** ..... : E135494-A55-CB-3  
**Date of issue** ..... : 2015-03-20  
**Total number of pages** ..... : 95

**CB Testing Laboratory** ..... : UL International Demko A/S  
**Address** ..... : Borupvang 5A, 2750 Ballerup, Denmark

**Applicant's name** ..... : TDK-LAMBDA UK LTD  
KINGSLEY AVE  
**Address** ..... : ILFRACOMBE  
DEVON  
EX34 8ES UNITED KINGDOM

**Test specification:**

**Standard** ..... : IEC 60950-1:2005 (Second Edition); Am1:2009 + Am2:2013  
**Test procedure** ..... : CB Scheme  
**Non-standard test method** ..... : N/A

**Test Report Form No.** ..... : IEC60950\_1F  
**Test Report Form originator** ..... : SGS Fimko Ltd  
**Master TRF** ..... : Dated 2014-02

**Copyright © 2014 Worldwide System for Conformity Testing and Certification of Electrotechnical Equipment and Components (IECEE), Geneva, Switzerland. All rights reserved.**


This publication may be reproduced in whole or in part for non-commercial purposes as long as the IECEE is acknowledged as copyright owner and source of the material. IECEE takes no responsibility for and will not assume liability for damages resulting from the reader's interpretation of the reproduced material due to its placement and context.



If this test Report is used by non-IECEE members, the IECEE/IEC logo and the reference to the CB Scheme procedure shall be removed.

**This report is not valid as a CB Test Report unless signed by an approved CB Testing Laboratory and appended to a CB Test Certificate issued by an NCB in accordance with IECEE 02.**

**General disclaimer**

The test results presented in this report relate only to the object tested. This report shall not be reproduced, except in full, without the written approval of the Issuing CB Testing Laboratory. The authenticity of this Test Report and its contents can be verified by contacting the NCB, responsible for this Test Report.

<b>Test item description</b> .....	Switch Mode Power Supply
Trade Mark .....	TDK-Lambda
	
Manufacturer .....	TDK-LAMBDA UK LTD KINGSLEY AVE ILFRACOMBE DEVON EX34 8ES UNITED KINGDOM
Model/Type reference .....	Series Alpha 400, Alpha 400W, MA400, CA400, Alpha-400, Alpha-400W, MA-400, CA-400
Ratings .....	Nominal Input Voltage Range: 100 - 240VAC, 7A max, 47-63Hz Output: See Model Differences

<b>Testing procedure and testing location:</b>	
<input checked="" type="checkbox"/> <b>CB Testing Laboratory</b>	Testing location / address .....: UL International Demko A/S Borupvang 5A, 2750 Ballerup, Denmark
<input type="checkbox"/> <b>Associated CB Test Laboratory</b>	Testing location / address .....:
	Tested by (name + signature) .....: Mike Burns 
	Approved by (name + signature).....: David Snook 
<input type="checkbox"/> <b>Testing Procedure: TMP/CTF Stage 1</b>	Testing location / address .....:
	Tested by (name + signature) .....: _____
	Approved by (name + signature).....: _____
<input type="checkbox"/> <b>Testing Procedure: WMT/CTF Stage 2</b>	Testing location / address .....:
	Tested by (name + signature) .....: _____
	Witnessed by (name + signature) ...: _____
	Approved by (name + signature).....: _____
<input type="checkbox"/> <b>Testing Procedure: SMT/CTF Stage 3 or 4</b>	Testing location / address .....:
	Tested by (name + signature) .....: _____
	Approved by (name + signature).....: _____
	Supervised by (name + signature) .: _____
<input type="checkbox"/> <b>Testing Procedure: RMT</b>	Testing location / address .....:
	Tested by (name + signature) .....: _____
	Approved by (name + signature).....: _____
	Supervised by (name + signature) .: _____

<b>List of Attachments</b>
National Differences (50 pages)
Enclosures (136 pages)
<b>Summary of Testing:</b>
All Applicable tests according to the referenced standard(s) have been carried out
<b>Summary of Compliance with National Differences:</b>
Countries outside the CB Scheme membership may also accept this report.

List of countries addressed: AR, AT, AU, BE, BG, BY, CA, CH, CS, CZ, DE, DK, ES, EU, FI, FR, GB, GR, HU, IE, IL, IN, IT, JP, KR, MY, NL, NO, NZ, PL, PT, RO, SA, SE, SI, SK, UA, US, ZA

The product fulfills the requirements of: CSA C22.2 No. 60950-1-07 + A2:2014, UL 60950-1 2nd Ed. Revised 2014-10-14, EN 60950-1:2006 + A1:2010 + A11:2009 + A12:2011 + A2:2013

**Copy of Marking Plate**

The artwork below may be only a draft. The use of certification marks on a product must be authorized by the respective NCBs that own these marks.

SLOT 5	SLOT 4	SLOT 3	SLOT 2	SLOT 1
--------	--------	--------	--------	--------

<input type="checkbox"/> N/A OPTION	<input type="checkbox"/> N/A OPTION	<input type="checkbox"/> N/A OPTION	<input type="checkbox"/> N/A OPTION	<input type="checkbox"/> N/A OPTION
<input type="checkbox"/> 0V	<input type="checkbox"/> 0V	<input type="checkbox"/> 0V	<input type="checkbox"/> 0V	<input type="checkbox"/> 0V
<input type="checkbox"/> 19V	<input type="checkbox"/> 19V	<input type="checkbox"/> 19V	<input type="checkbox"/> 19V	<input type="checkbox"/> 19V
<input type="checkbox"/> 0V	<input type="checkbox"/> 0V	<input type="checkbox"/> 0V	<input type="checkbox"/> 0V	<input type="checkbox"/> 0V
<input type="checkbox"/> 12V	<input type="checkbox"/> 12V	<input type="checkbox"/> 12V	<input type="checkbox"/> 12V	<input type="checkbox"/> 12V
<input type="checkbox"/> 24V	<input type="checkbox"/> 24V	<input type="checkbox"/> 24V	<input type="checkbox"/> 24V	<input type="checkbox"/> 24V
<input type="checkbox"/> 0V	<input type="checkbox"/> 0V	<input type="checkbox"/> 0V	<input type="checkbox"/> 0V	<input type="checkbox"/> 0V
<input type="checkbox"/> 25A	<input type="checkbox"/> 25A	<input type="checkbox"/> 25A	<input type="checkbox"/> 25A	<input type="checkbox"/> 25A

**OUTPUT DETAILS**

POWER SUPPLY
CODE: CA400L 59 24D 12/12E 15/15E
MADE IN THE UK
PART NUMBER: H47300
SERIAL NUMBER: 1181-11111

FOR MOUNTING POSITIONS, MAX. SCREW TIGHTENING IS 4.5nm. USE INSULATED CONNECTORS FOR ALL ISOLATED POINTS. CAPACITOR 1000µF

**TDK-Lambda**  
www.tdk-lambda.com  
part of the lambda.com powers

**Alpha 400W**

**CE**


**RoHS**

**INPUT DETAILS**

Refer to www.tdk-lambda.com for installation manual.  
For Lead Certificate: Refer to http://shop.tdk-lambda.com

Nominal Input Voltage Range: 100 - 240VAC  
Max. Input Voltage Range: 95 - 264VAC  
Input Frequency: 47 - 63Hz  
Maximum Input Current: 7 Arms  
Maximum Output Power: 400W  
F.T.F. (MAX 150V)  
DATE: 22-JAN-15

**II Z III**



<b>Test item particulars :</b>	
Equipment mobility .....	for building-in
Connection to the mains .....	no direct connection to the mains
Operating condition .....	continuous
Access location .....	for building-in
Over voltage category (OVC) .....	OVC II
Mains supply tolerance (%) or absolute mains supply values .....	90 - 264VAC max
Tested for IT power systems .....	No
IT testing, phase-phase voltage (V) .....	N/A
Class of equipment .....	Class I (earthed)
Considered current rating of protective device as part of the building installation (A) .....	-
Pollution degree (PD) .....	PD 2
IP protection class .....	IP X0
Altitude of operation (m) .....	3000
Altitude of test laboratory (m) .....	64
Mass of equipment (kg) .....	2.5kg
<b>Possible test case verdicts:</b>	
- test case does not apply to the test object .....	N / A
- test object does meet the requirement .....	P(Pass)
- test object does not meet the requirement .....	F(Fail)
<b>Testing:</b>	
Date(s) of receipt of test item .....	2012-06-27
Date(s) of Performance of tests .....	2012-06-28
<b>General remarks:</b>	
<p>"(see Enclosure #)" refers to additional information appended to the report.  "(see appended table)" refers to a table appended to the report.</p> <p>Throughout this report a point is used as the decimal separator.</p>	
<b>Manufacturer's Declaration per Sub Clause 4.2.5 of IEC60950-1:</b>	
Yes	
<p>The application for obtaining a CB Test Certificate includes more than one factory and a declaration from the Manufacturer stating that the sample(s) submitted for evaluation is (are) representative of the products from each factory has been provided .....</p> <p>When differences exist, they shall be identified in the General Product Information section.</p>	
<b>Name and address of Factory(ies):</b>	<p>TDK-LAMBDA UK LTD  KINGSLEY AVE  ILFRACOMBE  EX34 8ES UNITED KINGDOM</p> <p>PANYU TRIO MICROTRONICS CO LTD</p>

SHIJI INDUSTRIAL ESTATE  
DONGYONG  
NANSHA  
GUANGZHOU  
GUANGDONG 511453 CHINA

## GENERAL PRODUCT INFORMATION:

### Report Summary

All applicable tests according to the referenced standard(s) have been carried out.

### Product Description

The subject units are switch mode power supply sub-assemblies incorporating semiconductor components. They are provided with isolating transformers and associated circuitry mounted on printed wiring boards, in addition to input connectors for connection to mating connectors or wiring within the end equipment.

### Model Differences

The Alpha 400, CA 400 and MA 400 Series Power Supplies are electrically and mechanically identical.

The system build is further specified by additional suffixes, described as follows:

may be followed by A, LL, RL, ML, TL or no letter; where

A=Class A input filter

LL=Low Leakage Input Filter

RL=Reduced Leakage Input filter

TL= Tiny Leakage Input filter

ML = Medium Leakage input filter

No letter = Class B input filter

may be followed by LSF, QF or RA; where

LSF=Low Speed Fan

QF=Quiet Fan

RA=Reverse Air Fan

followed by up to five of the following:

@ followed by AA, A, AL, BB, B, CC, C, CL, CM, CH, DD, D, FF, F, GG, G, JJ, J, KK, K, LL, L, MM, M, NN, N, QQ, Q, RR, R, SS, S, TT, T, UU, U, WW, W, ZZ or Z.

or B/S

optionally followed by: \_X, \_MF, MFE, MFU, MFV or \_MFV, MFPF, \_PA, \_IN, \_PP, MJ, RJ, PJ, IJ, \_RP,

RPA, RPB, RPC, RPD, \_MG or \_D

@/@ or @\_@ followed by: E, EB, EQ, EL, EH, H, P or PL:

where @ and @/@ or @\_@ = applicable voltage range and the following one or two letters are the module type

\_MF, MFE = Mains fail option (may also be called X)

MFU = Mains fail option with uncommitted output connections

MFV or \_MFV = Mains fail option with VME bus

\_PA, \_PP, \_IN, \_RP = Secondary module options

B/S = blanking slot which occupies one 23 mm slot.

Only up to five 23 mm slots may be filled up per unit, noting that all modules occupy one 23 mm slot except

for AA, A, F, G, J, K, R, S and T modules which occupy two 23 mm slots. All primary MF options can only be fitted in slot 1.

Valid voltage ranges for @ and @/@ or @\_@ for each module are as follows:

Module	Voltage Range
A	@ = 4.5 - 6V
AA	@ = 4.5 - 7V
AL	@ = 4.75 - 5.3V
BB	@ = 4.5 - 7V
B	@ = 4.5 - 6V
C, CC	@ = 5 - 16V
CL	@ = 4.6 - 5.6V
CM	@ = 5 - 7V
CH	@ = 11.4 - 13.5V
D, DD	@ = 18 - 29V
E	@/@ or @_@ = 5 - 16V / 5 - 16V
EL	@/@ or @_@ = 5 - 7V / 11 - 13V
EH	@/@ or @_@ = 11 - 13V / 11 - 13V
EB	@/@ or @_@ = 4.5 - 5.5V / 4.5 - 5.5V
EQ	@/@ or @_@ = 4.5 - 5.5V / 2.7 - 3.9V
F	@ = 9 - 16V
G, GG	@ = 17.5 - 29V
H	@/@ or @_@ = 18 - 32V / 18 - 32V
J, JJ	@ = 30 - 48V
K, KK	@ = 18 - 31V
L, LL	@ = 1.8 - 3.2V
M, MM	@ = 5 - 16V
N, NN	@ = 18 - 32V
P	@/@ or @_@ = 18 - 29V / 5 - 16V
PL	@/@ or @_@ = 22 - 26V / 5 - 7V
Q, QQ	@ = 2.7 - 3.9V
R, RR	@ = 2.7 - 3.9V
S, SS	@ = 1 - 5.7V
T, TT	@ 1.8V - 3.2V
U, UU	@ 10 - 21V
W, WW	@ 4.5 - 5.5V
Z, ZZ	@ 4.5 - 5.7V

#### Secondary Options:

Option	Description
_MG	Provides a module good signal which indicates output voltage is within limits
_PA, RJ	Forces paralleled modules to share load current. Additionally it also provides the module good signal
_PP, PJ	Provides either of the following functions: a) Reduces module current limit and caters for paralleled modules with bus bar linking. For use with modules providing a max output of up to 16V only; or b) Identical to _PA except that the module is paralleled at the output of the module with bus bar linking
_IN, IJ	Provides an external signal which may be used to inhibit the output of the module
_RP	Provides remote programming of the module output voltage
RPA	Provides voltage programming of the module output voltage only
RPB	Provides voltage programming of the module output voltage and has an output VA limiting circuit



RPC Provides an output VA limiting circuit  
 RPD Provides voltage programming of the module output voltage and has an output VA limiting circuit  
 \_D Provides a delay to the turn on time of the output

**Note:**

The RPA option can only be used on modules with output voltages rated up to 32V

The RP, RPB, RPC and RPD options can only be used on modules with output voltages rated up to 16V.

Not for use with a module voltage range of 18-29V or twin output modules.

- a) A, AA & AL modules can be used in slots 1-5 up to 60A/channel
- b) BB & B modules can be used in slots 1-4 up to 25A/channel and in slot 5 up to 20A/channel
- c) C, CC, CL, CM & CH modules can be used in slots 1-5 up to 16A/channel if o/p is limited to 12V. At 15 to 16V C modules can be used up to 12A/channel. Module derates linearly between 12 and 15V
- d) D & DD modules can be used in slots 1-5 up to 8A/channel
- e) E, EL & EH modules can be used in slots 1-3 up to 8A/channel and in slots 4 and 5 up to 6A/channel
- f) EB modules can be used in slots 1-5 up to 9A/channel
- g) EQ modules can be used in slots 1-3 up to 9A/channel and in slots 4 and 5 up to 6.75A/channel
- h) F & FF modules can be used in slots 1-5 up to 33A/channel
- i) G & GG modules can be used in slots 1-5 up to 20A/channel
- j) H modules can be used in slots 1-3 up to 5A/channel and in slots 4 and 5 up to 4A/channel. For output voltages 30.01 to 32V maximum rated current is 1A
- k) J & JJ modules can be used in slots 1-5 at 30-41V at 10A max. For output of 48V at 8A max. For voltages between 41 and 48V the current is linearly interpolated
- l) K & KK modules can be used in slots 1-5 up to 15A
- m) M & MM modules can be used in slots 1-5 up to 8A/channel
- n) L & LL modules can be used in slots 1-4 up to 25A/channel and in slot 5 up to 20A per channel
- o) N & NN modules can be used in slots 1-5 up to 5A/channel for output voltages up to 29V. For output voltages 29.01 to 32V maximum rated current is 1A
- p) P & PL modules 18-29V outputs can be used in slots 1-3 up to 5A and in slots 4-5 at up to 4A. 5-16V outputs can be used in slots 1-3 up to 8A and in slots 3-4 at up to 6A
- q) Q & QQ modules can be used in slots 1-5 up to 25A/channel
- r) R & RR modules can be used in slots 1-5 up to 60A/channel
- s) S & SS modules can be used in slots 1/2 up to 75A, slots 2/3 up to 71A, slots 3/4 up to 69A & slots 4/5 up to 66A
- t) T & TT modules can be used in slots 1-5 up to 60A
- u) U & UU modules can be used in slots 1-3 up to 16A, slot 4 up to 15A and slot 5 up to 13A
- v) W & WW modules can be used in slots 1-5 up to 15A/channel
- w) Z & ZZ modules can be used in slots 1-4 up to 25A/channel and in slot 5 up to 20A per channel.

The following limitations also apply:

(a) For power supplies having one or more A, AA, AL, R, RR, T and/or TT modules and mounted vertically with the airflow downwards, the output is limited to 350W.

(b) For power supplies having one or more F or FF modules, the output is limited to 375W, only when operated in a vertical position with the fan on top of the power supply

(c) For power supplies fitted with an LSF option fan, the output is limited to 300W and 60AT. Operation in a vertical orientation with the fan at the top is not permitted

(d) For power supplies fitted with the fan reversed (RA option), the output is limited to 300W and 60AT. Operation in a vertical orientation is not permitted

(e) For power supplies having input or output connector housings fitted the total output is limited as follows:

PSU Orientation	Total Power Output
Vertical with no fan	$P = 14.7 + 3.67 \cdot V_{in}$
All other orientations	$P = 80 + 3.2 \cdot V_{in}$

subject to a maximum total power output of 400W and a minimum mains input voltage of 90Vac. Where P = maximum total output power and  $V_{in}$  = mains input voltage

An example of product would be: CA400 @B @B @C @/@E or @\_@E, @M where @ and @/@ or @\_@ would be written on the product label as numbers representing the voltage of the module eg. 5B

#### Additional Module limitations:

When using remote sense, the max output voltage will be reduced by 0.5V for L, S, T, Q and R modules, and by 1.0V for C, D, F, G, J, M, K, N, U Modules.

Ampere turns for J module is calculated as  $AT = (\text{output current} + 15A) \times 4$

Adjusting output voltage beyond the stated range may cause overvoltage protection (OVP) to operate, whereby all outputs will turn off. To reset OVP, turn back output voltage adjustment and remove the mains supply for 30 seconds.

#### Additional Information

The schematics are kept on file at the CBTL and can be provided by the manufacturer upon request by NCB's/CBTL's.

The label sample represents all Models in the Series.

The original testing was carried out on the basis of 5 slots being filled, each slot being one 23mm module space wide. This is the maximum number of module slots allowed under this approval, and provides the worst case situation. Heating tests were carried out with the maximum number of slots filled, but with numerous loading conditions to cover any condition of loading in any slot position. Also, the models tested represent the least efficient, highest current module configurations. Abnormals were carried out on the expected worst case situation for that abnormal, and on as many configurations as considered necessary to represent the entire range of products covered by this approval. For the other tests, the conditions and configurations used were the expected worst case.

These products use optional coatings which are normally applied with a brush and are used within the primary area of the power supply on limited surface therefore deemed as non-safety critical. The coatings are not used for any safety purpose.

This report is a reissue of CBTR Ref. No.: E135494-A55-CB-2 dated 2012-08-02, CB Test Certificate Ref. No. DK-27403-UL dated 2012-08-02. Based on previously conducted testing and the review of product technical documentation including photos, schematics, wiring diagrams and similar, it has been determined that the product continues to comply with the standard.

No testing was deemed necessary to include the following changes/additions:-

1. Correction/addition to critical component list
2. Enclosures updated to include revised handbook, drawings and CCL certificates
3. Assessed to IEC60950-1 2nd ed. + amendment 2:2013
4. New marking plate label added
5. Revised factory

#### Technical Considerations

- Clearances and Creepage Distances have additionally been assessed for suitability up to 3000 m elevation. --
- The product was submitted and evaluated for use at the maximum ambient temperature (T<sub>ma</sub>) permitted by the manufacturer's specification of: 50°C --
- The product is intended for use on the following power systems: TT TN --
- The equipment disconnect device is considered to be: provided in end product --
- The following were investigated as part of the protective earthing/bonding: Printed wiring board trace

(refer to Enclosure - Schematics + PWB for layouts) --

- The means of connection to the mains supply is: to be determined in end-product --
- The product was investigated to the following additional standards: BS EN 60950-1:2006 + A2:2013 (which includes all European national differences, including those specified in this test report). --

#### **Engineering Conditions of Acceptability**

When installed in an end-product, consideration must be given to the following:

- These products were considered to be a component part of a larger piece of Class 1 equipment. Full compliance with the standards will therefore depend on the installation in the final application. Some modules could present an energy hazard. Additionally, outputs can be connected in series thus producing non-SELV levels, or in parallel thus producing new energy hazards, and this must be taken into account in the end-use application. When non-seriesed outputs are earthed in the end use equipment they are SELV. If the outputs are not earthed they must be considered hazardous, as a single fault in the secondary may make them exceed the SELV limits between output and earth. If any output is non-SELV then all outputs become non-SELV. --
- These units are internally forced-air cooled. They require a minimum of 50mm clearance in the vicinity of the ventilation holes. Whilst relatively orientation insensitive, operation of these units when mounted vertically with the air flow in a downward direction is affected by convection acting against the cooling airflow, and results in slightly hotter temperatures (2 to 5 degrees) than if operated in the horizontal position. As a consequence of this, heating tests were carried out in the vertical orientation with airflow downwards to give the worst case temperatures, unless otherwise stated. No additional air flow during tests was applied, only the internal fans were used. --
- Additional requirement may apply if product used in end application in Restricted Access Location. --
- Additional requirements may apply if fuse is replaceable in end product --
- Consideration should be given to measuring the temperatures on power electronic components and transformer windings, when the power supply is installed in the end-use equipment. --
- For limitations of using Alpha 400 - see model differences --
- The power supply terminals and/or connectors are: Suitable for factory wiring only --
- The investigated Pollution Degree is: 2 --
- Proper bonding to the end-product main protective earthing termination is: Required. The power supply chassis shall be properly bonded to earth in the end-use product, as the units were investigated for Class 1 construction. The grounding pin at the input terminal is connected to a printed wiring board. The grounding path on the printed wiring board has not been investigated as a protective earthing conductor. An additional evaluation shall be made, if the power supply is intended for use in other than Class I equipment. --
- The following magnetic devices (e.g. transformers or inductor) are provided with an OBJY3 insulation system with the indicated rating greater than Class A (105°C): see critical components table for details. --
- The following end-product enclosures are required: Electrical , Fire --
- The following Production-Line tests are conducted for this product: Earthing Continuity , Electric Strength --
- The end-product Electric Strength Test is to be based upon a maximum working voltage of: Primary-Earthed Dead Metal: 291 Vrms, 400 Vpk Primary-SELV: 336 Vrms, 864 Vpk --
- The maximum investigated branch circuit rating is: 20 A --
- An investigation of the protective bonding terminals has: Not been conducted --

- The following input terminals/connectors must be connected to the end-product supply neutral: input terminal marked "N" --
- The following secondary output circuits are SELV: See information in Additional Information. --
- The following secondary output circuits are at hazardous energy levels: modules A, AA, AL, C, CC, CH, D, DD, F, FF, G, GG, J, JJ, K, KK, R, RR, S, SS, T, TT, U and UU --
- The following secondary output circuits are at non-hazardous energy levels: modules B, BB, CL, CM, E, EB, EH, EL, EQ, H, L, LL, M, MM, N, NN, P, PL, Q, QQ, W, WW, Z and ZZ --
- Fans: The fan provided in this sub-assembly is provided with a fan guard to reduce the risk of operator contact with the fan. --

Abbreviations used in the report:

- normal condition .....	N.C.	- single fault condition .....	S.F.C
- operational insulation .....	OP	- basic insulation .....	BI
- basic insulation between parts of opposite polarity:	BOP	- supplementary insulation .....	SI
- double insulation .....	DI	- reinforced insulation .....	RI

Indicate used abbreviations (if any)