



TDK-Lambda

Points clés produit

- Suppression des surtensions DO-160 & MIL-STD
- Filtrage compatible avec la norme MIL-STD-461F
- Options de filtrage standard ou amélioré
- Idéal pour être utilisé avec nos convertisseurs DC-DC série HQA

Specifications essentielles

- Taille ¼ brique
- Rating 20A 40Vcc
- Qualification MIL-STD-883F and MIL-STD-202G
- Gamme de température de -40°C ou -55°C à +115°C

Applications typiques

- Electroniques embarqué es véhicule / en vol
- Radar et Communications
- Environnements sévères COTS
- Architecture de puissance distribuée dans l'aéronautique

Product Highlights

- DO-160 & MIL-STD Spike / Surge Suppression
- Filtering for Compliance to MIL-STD-461F
- Standard or Enhanced Screening Options
- Ideal for use with HQA DC-DC Converters

Key Specifications

- Quarter Brick Size
- 20A 40Vdc Rating
- MIL-STD-883F and MIL-STD-202G qualification
- -40°C or -55°C to +115°C Temperature Range

Typical Applications

- Airborne / Vehicle Mounted Electronics
- Radar and Communications
- Harsh Environment COTS
- Aircraft Distributed Power Architecture