HFE2500 IEC 61000 TEST DATA

DWG: IA689-58-01						
APPD	DWG					
Dovan P.	Di P	MICHAEL G. 27.10.2011				
Dec-18-11	9- NOV-2011	27.10.6011				

HFE2500

INDEX	PAGE
1.Electrostatic Discharge Immunity Test (IEC61000-4-2)	R-1
2.Radiated Radio-Frequency Electromagnrtic	
Field Immunity Test (IEC61000-4-3)	R-2
3.Electrical Fast Transient / Burst Immunity Test (IEC61000-4-4)	R-3
4.Surge Immunity Test (IEC61000-4-5)	R-4
5.Conducted Disturbances Induced by Radio-Frequency	
Field Immunity Test (IEC61000-4-6)	R-5
6.Power Frequency Magnetic Field Immunity Test (IEC61000-4-8)	R-6
7. Voltage Dips, Short Interruptions Immunity Test (IEC61000-4-11)	R-7
8.Input Current Harmonics Test (IEC61000-3-2)	R-8

Test results are tupical data. Nevertheless the following results are considered to be actual capability data because all units have nearly the same characteristics.

1.Electrostatic Discharge Immunity Test (IEC61000-4-2)

(1)Equipment used NOISEKEN ESS-2000


Discharge resistance: 330 Ohm Capacity: 150pF

(2)Test conditions

Input voltage: Rated Output voltage: Rated
Output current: 100% Polarity: -,+
Number of tests: 10 times Discharge interval: >1 Second

(3)Test method and Device test point Contact discharge: FG,Case screw

Air discharge: Input and Output terminal



(4) Acceptable conditions

- 1.Output voltage regulation not to exceed \pm 5% of initial (before test) value during test.
- 2. Output voltage to be within regulation specification after the test.
- 3. Along with 1 and 2, no discharge of fire or smoke, as well as no output failure.

Contact Discharge (Kv)	HFE2500	Air Discharge (Kv)	HFE2500
4	PASS	8	PASS

2.Radiated Radio-Frequency Electromagnrtic Field Immunity Test (IEC61000-4-3)


(1) Equipment used

Test Laboratory: Hermon Laboratories Ltd.

(2)Test conditions

Input voltage:RatedOutput voltage:RatedOutput current:100%Amplitude Modulated:80%,1kHzElectromagnetic Frequency:80~1000MHzAmbient temperature:25 ℃Distance:2.4mWave Angel: Horisontal and Vertical

Sweep condition: 1.0% Step Up,2.0 second Hold Test Angle: Top/Botton,Both Sides,Front/Back



(3)Acceptable conditions

- 1.Output voltage regulation not to exceed \pm 5% of initial (before test) value during test.
- 2. Output voltage to be within regulation specification after the test.
- 3. Along with 1 and 2, no discharge of fire or smoke, as well as no output failure.

Radiated Field Strength (V/m)	HFE2500		
3	PASS		

3. Electrical Fast Transient / Burst Immunity Test (IEC61000-4-4)

(1) Equipment used

EFT/B Generator: SCHAFFNER NSG2025

(2)Test conditions

Number of tests: 3 times

(3)Test method and Device test point: Neutral (N),Line (L), Ground (FG)
Apply pulses from EFT/B Generator to N,L,FG separately,as well as,all at the same time.

Oscilloscope AC N,L **INPUT** E.U.T. Load Aluminum Plate FG EFT/B 0.8m Generator Wood made Table -AC FG **GND Plane**

(4)Acceptable conditions

- 1.Output voltage regulation not to exceed \pm 5% of initial (before test) value during test.
- 2. Output voltage to be within regulation specification after the test.
- 3. Along with 1 and 2, no discharge of fire or smoke, as well as no output failure.

Test Voltage (kV) Repitition Rate (kHz)		HFE2500		
2	5	PASS		

4.Surge Immunity Test (IEC61000-4-5)

(1) Equipment used

Surge Generator: SCHAFFNER-NSG651 Coupling impedance: Common - 12 OHm Normal - 2 OHm

0------ 0--E


Coupling capacitance: Common - 9 uF

Normal - 18 uF

Coupling network: SCHAFFNER-CDN110

(2)Test method and devise test point

Input voltage: Rated Output voltage: Rated Output current: 100% Number of tests: 5 times Polarity: -,+ Mode: Common, Normal Phase: 0,90 DEG. Ambient temperature: 25°C



(3)Acceptable conditions

- 1.Output voltage regulation not to exceed \pm 5% of initial (before test) value during test.
- 2. Output voltage to be within regulation specification after the test.
- 3. Along with 1 and 2, no discharge of fire or smoke, as well as no output faiulre.

Test Voltage (kV) Common	HFE2500	Test Voltage (kV) Normal	HFE2500
2.0	PASS	2.0	PASS
4.0	PASS		

5.Conducted Disturbances Induced by Radio-Frequency Field Immunity Test (IEC61000-4-6)

(1) Equipment used

RF Signal Generator 10kHz-1050MHz: Fluke,6061A

RF Amplifier 10kHz-220MHz,150W: Amplifier Research,150L

Coupling/Decoupling Network: HL CDN 801-M3

(2) Test Condition:

Input voltage: Rated Output voltage: Rated


Output current: 100% Electromagnetic

Frequency: 150kHz~80MHz

Sweep Condition: 1.0% Step Up, 2.0 Seconds Hold

Ambient temperature:25 °C

(3)Test Method:



^{*}Used Analog Voltage Meter

(4) Acceptable conditions

- 1.Output voltage regulation not to exceed \pm 5% of initial (before test) value during test.
- 2. Output voltage to be within regulation specification after the test.
- 3. Along with 1 and 2, no discharge of fire or smoke, as well as no output failure.

Voltage Level (V)	HFE2500		
3	PASS		

6. Power Frequency Magnetic Field Immunity Test (IEC61000-4-8)

(1) Equipment used

AC High Current Generator for

Magnetic Field immunity tests: HL, MFG-130A

(2) Test Condition:


Input voltage: Rated Output voltage: Rated

Output current: 100% Frequency: 50Hz

Magnetic Field Strength: 30A/m Ambient temperature:25 ℃

Duration Time: 10min.

(3)Test Method:



(4) Acceptable conditions

- 1.Output voltage regulation not to exceed \pm 5% of initial (before test) value during test.
- 2. Output voltage to be within regulation specification after the test.
- 3. Along with 1 and 2, no discharge of fire or smoke, as well as no output failure.

EUT positions	Result
Х	PASS
Y	PASS
Z	PASS

7. Voltage Dips, Short Interruptions Immunity Test (IEC61000-4-11)

(1) Equipment used

Voltage Dips Generator: CI, 5001ix

Oscilloscope: Yokogawa, DL1740EL

(2)Test Condition:


Input voltage: Rated Output voltage: Rated

Output current: 100% Frequency: 50Hz

Repetition: 0.1Hz Ambient temperature:25°C

Number of pulse: 3

(3)Test Method:



(4)Acceptable conditions

- 1. Output voltage to be within output voltage regulation specification after the test
- 2.No discharge of fire or smoke

Dip rate	Continue time	Result	
30% vol.dip	500ms	PASS	
60% vol.dip	200ms	PASS	
>95% vol.dip	20ms; 5,000ms	PASS	

Vin=115VAC

8.Input Current Harmonics Test (IEC61000-3-2)

Model:

Harmonic Current (A)

(1) Equipment used

AC Power Analyzer:

PACS-1(California Instruments)

AC Source:

5001 IX (California Instruments)


(2)Test conditions:

Input voltage: 115VAC;230VAC


Output current: 100%

(3)Test Method:





Harmonic Number



Harmonic Number

Vin	HARMONICS								
	3	5	7	9	11	13	15	17	19
115	4.6	2.28	1.54	0.8	0.66	0.42	0.3	0.264	0.236
VAC	0.21	0.05	0.02	0.04	0.05	0.05	0.05	0.05	0.05
230	2.3	1.14	0.77	0.4	0.33	0.21	0.15	0.132	0.118
VAC	0.58	0.14	0.17	0.07	0.06	0.05	0.05	0.06	0.06

Input Current Harmonics EN61000-3-2 Limit

Input Current Harmonics-Measurment