

DEMKO CERTIFICATE

Certificate No. D-04215-A2
Page 1/3
Date of Issue 2016-03-09

Certificate Holder TDK-LAMBDA CORP
NAGAOKA TECHNICAL CENTER R&D DIV
2704-1 SETTAYA-MACHI NAGAOKA-SHI NIIGATA 940-1195
JAPAN

Manufacturer TDK-LAMBDA CORP
NAGAOKA TECHNICAL CENTER R&D DIV
2704-1 SETTAYA-MACHI NAGAOKA-SHI NIIGATA 940-1195
JAPAN

Production site TDK-LAMBDA CORP
2704-1 SETTAYA-MACHI NAGAOKA-SHI NIIGATA-KEN 940-1195
JAPAN

See Page 2

Certified Product Model Switching Power Supply
EVS36-16R7, EVS57-10R6, RWS600B-12, RWS600B-15,
RWS600B-24, RWS600B-36, See Page 2

Trademark

TDK-Lambda

Rated Voltage / Frequency

See Page 2

Rated Current / Power

See Page 2

Insulation Class

I

Degree of protection (IP)

X0

Tested acc. to

EN 60950-1:2006/A11:2009, EN 60950-1:2006/A12:2011, EN
60950-1:2006/A1:2010, EN 60950-1:2006/A2:2013,
EN 60950-1:2006

Test Report No.

E122103-A147-CB-2 issued on 2016-03-08

Additional

for building-in; See page 2

Expire date

2025-05-27

Certification Manager
Jan-Erik Storgaard

This is to certify that representative sample(s) of the Product described herein ("Certified Product") have been investigated and found in compliance with the Standard(s) indicated on this Certificate, in accordance with the D Mark Requirements. The Designated Certificate holder is entitled to use the d or for cables <DEMKO> for the Certified Product manufactured at the production site(s) identified above, in accordance with the D Mark Service Agreement, including without limitation the D Mark Testing and Certification Services Service Terms. Only those Products bearing the D Mark should be considered as being covered by UL's D Mark Service. This Certificate shall remain valid through the expiration date, unless terminated earlier in accordance with the Service Agreement including without limitation if the Standard identified on this Certificate is amended or withdrawn prior to the expiration date.

Certification Body

UL International Demko A/S, Borupvang 5A, DK-2750
Ballerup, Denmark, Tel. +45 44 85 65 65,
info.dk@ul.com
www.ul-europe.com



Appendix DEMKO CERTIFICATE

Certificate No. D-04215-A2
Page 2/3
Date of Issue 2016-03-09

Model Details:

EVS36-16R7,EVS57-10R6,RWS600B-12,RWS600B-15,RWS600B-24,RWS600B-36,RWS600B-48,
RWS600B-5 Maybe followed by suffix "abcdefg" (a is /, b is R, c is CO2, d is FG, e is FO, f is H, g is
RF only for RWS600B-24; and "abcdefg" may be blank).

Production Sites:

TDK-LAMBDA MALAYSIA SDN BHD
LOT 2 & 3, BATU 9 3/4 KAWASAN PERINDUSTRIAN BANDAR BARU JAYA GADING 26070 KUANTAN
MALAYSIA

WUXI TDK-LAMBDA ELECTRONICS CO LTD
NO 6 XING CHUANG ER LU WUXI JIANGSU 214028
CHINA

Ratings:

Input:

100-240 Vac, 50-60 Hz, 6.5 A (for Model RWS600B-5) and 7.0 A (for Models RWS600B-12, RWS600B-15,
RWS600B-24, RWS600B-36, RWS600B-48, EVS36-16R7, EVS57-10R6)

Additional Information:

This certificate replaces the certificate No. D-04215-A1, dated 2015-09-16 due to

- Addition of new model RWS600B-24 suffixed g:"RF".
- Addition of Alternate Transformer (T1), Type A23104x (x=A to Z, or blank).

Certification Body

UL International Demko A/S, Borupvang 5A, DK-2750
Ballerup, Denmark, Tel. +45 44 85 65 65, info.dk@ul.com
www.ul-europe.com



Appendix DEMKO CERTIFICATE

Certificate No. D-04215-A2
Page 3/3
Date of Issue 2016-03-09



Certification Body

UL International Demko A/S, Borupvang 5A, DK-2750
Ballerup, Denmark, Tel. +45 44 85 65 65, info.dk@ul.com
www.ul-europe.com

