

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)
CB SCHEME

CB TEST CERTIFICATE

Product	AC-DC Power Supply
Name and address of the applicant	TDK-LAMBDA UK LTD KINGSLEY AVE ILFRACOMBE, EX34 8ES United Kingdom
Name and address of the manufacturer	TDK-LAMBDA UK LTD KINGSLEY AVE ILFRACOMBE, EX34 8ES United Kingdom
Name and address of the factory <i>Note: When more than one factory, please report on page 2</i>	TDK-LAMBDA UK LTD KINGSLEY AVE ILFRACOMBE EX34 8ES UNITED KINGDOM <input checked="" type="checkbox"/> Additional Information on page 2
Ratings and principal characteristics	See Page 2 TDK-Lambda
Trademark (if any)	
Type of Customer's Testing Facility (CTF) Stage used	
Model / Type Ref.	CUS100ME, CUS150M See Page 2
Additional information (if necessary may also be reported on page 2)	Additionally evaluated to EN 60950-1: 2006 / A11: 2009 / A1: 2010 / A12: 2011 / A2:2013; National Differences specified in the CB Test Report. <input checked="" type="checkbox"/> Additional Information on page 2
A sample of the product was tested and found to be in conformity with	IEC 60950-1(ed.2), IEC 60950-1(ed.2);am1, IEC 60950-1(ed.2);am2
As shown in the Test Report Ref. No. which forms part of this Certificate	E135494-A113-CB-1 issued on 2018-03-16

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2018-03-16

Original Issue Date: 2017-05-04

Signature:

Jan-Erik Storgaard



Model Details:

CUS100ME,CUS150M (see test report model differences for details of nomenclature)

Factories:

PANYU TRIO MICROTRONIC CO LTD
SHIJI INDUSTRIAL ESTATE DONGYONG NANSHA GUANGZHOU GUANGDONG
CHINA

Ratings:

Input AC rated models:

100-240Vac; 47-63Hz or 47-440Hz; 2.2Arms max.

Input DC rated models (CUS150M only):

133 - 318Vdc; 1.8A max.

Output:

12, 15, 18, 24, 28, 36 or 48Vdc nominal, max. 100 or 150W (see test report model differences for full details)

Additional Information:

For Class I

The original report was modified to include the following changes/additions:

technical amendment

- Added CUS100ME models.
- Added CUS150M with the following output voltages: 15, 18, 28 and 36Vdc.
- Added DC input rating option for CUS150M models.
- Critical component list updated to include the new models.

Additional information (if necessary)



UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA

UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK

UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2018-03-16

Original Issue Date: 2017-05-04

Signature:

Jan-Erik Storgaard