

UL TEST REPORT AND PROCEDURE

Standard:	UL 62368-1, 2nd Ed, 2014-12-01 (Audio/video, information and communication technology equipment Part 1: Safety requirements) CAN/CSA C22.2 No. 62368-1-14, 2nd Ed-(Audio/video, information and communication technology equipment Part 1: Safety requirements)
Certification Type:	Component Recognition
CCN:	QQJQ2, QQJQ8 (Power Supplies for Use in Audio/Video, Information and Communication Technology Equipment)
Complementary CCN:	N/A
Product:	Switch mode power supply
Model:	NVM175 or NVM-175 models as described (See Model Differences)
Rating:	100-240Vac nom. 45-440Hz, 3A rms max. (See Model Differences)
Applicant Name and Address:	TDK-LAMBDA UK LTD KINGSLEY AVE ILFRACOMBE EX34 8ES UNITED KINGDOM

This is to certify that representative samples of the products covered by this Test Report have been investigated in accordance with the above referenced Standards. The products have been found to comply with the requirements covering the category and the products are judged to be eligible for Follow-Up Service under the indicated Test Procedure. The manufacturer is authorized to use the UL Mark on such products which comply with this Test Report and any other applicable requirements of UL LLC ('UL') in accordance with the Follow-Up Service Agreement. Only those products which properly bear the UL Mark are considered as being covered by UL's Follow-Up Service under the indicated Test Procedure.

The applicant is authorized to reproduce the referenced Test Report provided it is reproduced in its entirety.

UL authorizes the applicant to reproduce the latest pages of the referenced Test Report consisting of the first page of the Specific Technical Criteria through to the end of the Conditions of Acceptability.

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL.

Prepared By: Robert Dmitruk / Handler

Reviewed By: Hubert Koszewski / Reviewer

Supporting Documentation

The following documents located at the beginning of this Procedure supplement the requirements of this Test Report:

A. Authorization - The Authorization page may include additional Factory Identification Code markings.

B. Generic Inspection Instructions -

- i. Part AC details important information which may be applicable to products covered by this Procedure. Products described in this Test Report must comply with any applicable items listed unless otherwise stated in the body of this Test Report.
- ii. Part AE details any requirements which may be applicable to all products covered by this Procedure. Products described in this Test Report must comply with any applicable items listed unless otherwise stated in the body of each Test Report.
- iii. Part AF details the requirements for the UL Certification Mark which is not controlled by the technical standard used to investigate these products. Products are permitted to bear only the Certification Mark(s) corresponding to the countries for which it is certified, as indicated in each Test Report.

Product Description

The NVM-175 Series are switched mode power supplies for building into host equipment.

Model Differences

NVM175 or NVM-175 models as described below:

Units may be marked with a Product Code: X5x or NVM1x where x may be any number of characters.

Unit Configuration Code (Description): may be prefixed by NS # followed by / or - (where # may be any number of characters indicating non- safety related model differences).

Unit Configuration Code:

NVMxy-abcdefghijklm

Where:

x = 1 for 175 or 1D (1D for Double insulated or Class II unit)

y = Blank for Y2 capacitors from output to earth (except 1D models)

P for Y1 capacitors from output to earth (except 1D models)

a = Number of Outputs: 1.

b = Channel 1 Output Voltage where: T is for 12V, F is for 15V and G is for 24V.

c = O (for omit).

d = O (for omit).

e = O (for omit).

f = Standby supply:

Blank for no standby and no remote on/off (enable) or '-' followed by

S for 12V version with power good, logic level high enables main output.

S1 for 12V version with power good, logic level low enables main output.

S2 for 12V version with Channel 1 good, logic level high enables main output.

S3 for 12V version with Channel 1 good, logic level low enables main output.

S4 for 12V 0.8A version with power good, logic level low enables main output.

S5 for 5V 0.5A version with power good, logic level low enables main output.

S6 for 5V 0.5A version with power good, logic level high enables main output.

0 for no standby and no remote on/off (enable).

g = Blank for Open Frame or '-' followed by U for U chassis, C for U chassis with cover, K for custom chassis with cover and IEC inlet.

h = Blank for standard upright output connector or '-' followed by R for the right angle output connector, S for the screw terminal.

i = Blank for standard leakage or '-' followed by L for low leakage, Zx for custom leakage which is less than standard leakage and x is a number between 1 and 9 for different custom leakage current options.

jkl = Blank for standard output setting or '-' followed by three numbers from 0 to 9 which denotes various output voltages and currents within the specified range of channel 1 output for a particular unit.

m = Blank for dual fuse input or -FL for single fuse input in the Live line

Output Parameters

There are three NVM1 standard models with various options, and 3 non-standard models with output parameters shown in the tables below:

Output Channel	Voltage Designation	Vout Nom.	Adjustment Range (V)	Output Current (A)	Maximum Power (W)
Channel 1	T	12	12 - 15.5	15	180
	F	15	12 - 15.5	15	180
	G	24	24 - 28.5	7.5	180
Standby output	S	12	Fixed	0.2	2.4
	S1	12	Fixed	0.2	2.4
	S2	12	Fixed	0.2	2.4
	S3	12	Fixed	0.2	2.4
	S4	12	12 - 13	0.8	10.4
	S5	5	Fixed	0.5	2.5
	S6	5	Fixed	0.5	2.5

Variations and limitations of use:

NVM175 PSUs can output 180W from channel 1 plus 10.4W maximum from the standby output.

Component temperatures must be monitored in the end use application as described in the "COOLING FOR UNIT" section.

All ratings apply for ambient temperatures up to 50°C. From 50 to 70°C the total output power and current ratings are both derated at 2.5% per deg C.

Non- Standard model:

X50015# (where # can be any letter except A, B, C, D, E or F):

Factory fitted output loom
 Earth connection made via ring tag and screw

X50007# - NVM1D - 1G-f-g-h-j

may be any letter where this indicates any of the options described in the nomenclature table above for f, g, h and j and where g will always be blank (open frame). D indicates that the product is double insulated (no earth connections). This product has 18-way output connector.

Maximum storage temperature 65°C.

For ambient temperature requirements see Conditions of Acceptability and user manual (Enclosure 6-01).

Input Parameters

Parameter 62368-1
 Nominal input voltage 100 - 240 Vac
 Input voltage range 90 - 264Vac
 Input frequency range 45 - 63Hz
 Maximum input current 3A rms

Environmental Specifications:

Description	Operation	Storage & Transportation
Use	Indoor	-
Temperature	0°C - +70°C (See O/P tables for deratings)	-40°C - +85°C
Humidity	5 - 95% RH, non-condensing	5 - 95% RH, non-condensing
Altitude	-200m - 5000m	-200m - 5000m
Pressure	63kPa - 106kPa	54kPa - 106kPa

Orientation The unit may be mounted on either side, vertical with input lowest and horizontal. (Customer Air versions can be mounted in any orientation).

Test Item Particulars

Classification of use by	Skilled person
Supply Connection	AC Mains
Supply % Tolerance	+10%, -10%
Supply Connection – Type	mating connector Connection to mains to be determined in end use.
Considered current rating of protective device as part of building or equipment installation	20 A; building;
Equipment mobility	for building-in
Over voltage category (OVC)	OVC II
Class of equipment	Class I Class II
Access location	N/A

Pollution degree (PD)	PD 2
Manufacturer's specified maximum operating ambient (°C)	50°C (full load), 70°C (Output power decreased linearly by 2.5%/°C above 50°C)
IP protection class	IPX0
Power Systems	TN
Altitude during operation (m)	5000 m
Altitude of test laboratory (m)	64 m
Mass of equipment (kg)	Less than 1 kg

Technical Considerations

- The product was submitted and evaluated for use at the maximum ambient temperature (T_{ma}) permitted by the manufacturer's specification of : 50°C (full load); 70°C (power and output current, decreasing linearly by 2.5%/°C above 50°C). Model X50001x, 60°C (full load); 65°C (power and, output current decreasing linearly by 2.5%/°C above 60°C) NVM1D max temp 65°C.
- The product is intended for use on the following power systems : TN, IT (Norway only)
- Considered current rating of protective device as part of the building installation (A) : 20
- Mains supply tolerance (%) or absolute mains supply values : +10%/-10%
- The equipment disconnect device is considered to be : provided by the end equipment
- The following were investigated as part of the protective earthing/bonding : Printed wiring board trace (refer to Enclosure - Schematics + PWB for layouts)
- The following are available from the Applicant upon request : Installation (Safety) Instructions / Manual including French for Canada
- The product was investigated to the following additional standards : EN 62368-1:2014 + A11:2017
- 1.3 The means of connection to the mains supply is: To be determined in the end-use product

Engineering Conditions of Acceptability

For use only in or with complete equipment where the acceptability of the combination is determined by UL LLC. When installed in an end-product, consideration must be given to the following:

- The following product-line tests are conducted for this product : Electric Strength, Earthing Continuity (except NVM1D model)
- The end-product Electric Strength Test is to be based upon a maximum working voltage of : Primary-Secondary: 410 Vrms, 697 Vpk, Primary-Earthed Dead Metal: 398 Vrms, 662 Vpk
- The following output circuits are at ES1 energy levels : All
- The following output circuits are at PS3 energy levels : All
- The maximum investigated branch circuit rating is : 20 A
- The investigated Pollution Degree is : 2
- Proper bonding to the end-product main protective earthing termination is : Required (except for NVM1D model)
- An investigation of the protective bonding terminals has : been conducted
- The following end-product enclosures are required : Electrical, Fire, Mechanical
- The following magnetic devices (e.g. transformers or inductor) are provided with an OBJY2 insulation system with the indicated rating greater than Class A (105°C) : Transformer T1, T2 and T3 (Class F) - See table 4.1.2 for details of insulation systems used
- The following components require special consideration during end-product Thermal (Heating) tests due to the indicated maximum temperature measurements during component-level testing : Refer to enclosure Manuals ID 6-01 Cooling for units table.
- The power supply was evaluated to be used at altitudes up to : "5,000 m"
- • The following output terminals were referenced to earth during performance testing: All outputs and their return lines individually referenced to earth to obtain maximum working voltage.

- • The power supply terminals and/or connectors are: Suitable for factory wiring only

Additional Information

Cooling for units:

The following method must be used for determining the safe operation of PSUs. The components listed in the following table must not exceed the temperatures given. To determine the component temperatures the heating tests must be conducted in accordance with the requirements of the standard in question. Consideration should also be given to the requirements of other safety standards. Test requirements include: PSU to be fitted in its end-use equipment and operated under the most adverse conditions permitted in the end-use equipment handbook/specification and which will result in the highest temperatures in the PSU. To determine the most adverse conditions consideration should be given to the end use equipment maximum operating ambient, the PSU loading and input voltage, ventilation, end use equipment orientation, the position of doors & covers, etc.. Temperatures should be monitored using type K fine wire thermocouples (secured with cyanoacrylate adhesive or similar) placed on the hottest part of the component (out of any direct airflow) and the equipment should be run until all temperatures have stabilised.

Cooling for unit temperature table:

Circuit Ref.	Description	Max. Temperature (°C)
L3, L7	Common mode choke winding	115 (155)
C1, C4	X capacitors	100
C6	Capacitor	105
C12	Resonant capacitor	105
T3	Aux trx windings	130
L2	Boost choke winding	120 (155)
C7	Electrolytic capacitor	70 (105)
T1, T2	Transformer winding	130
L1	Primary choke (24V channel 1 only)	140
XU3, XU4, XU106	Opto-couplers on control board	100
U1, U2	Opto-couplers on base board	100


L5	Channel 1 output choke	125 (140)	
L4	Standby output choke	85	
J2	Input connector	105	
J1	Output connector		105
Various	All other electrolytic capacitors	90 (105)	

Higher temperature limits (in brackets) may be used but product life may be reduced.

Additional Standards

The product fulfills the requirements of: EN 62368-1:2014 + A11:2017
 UL 62368-1 2nd Edition, Issued December 1, 2014
 CSA CAN/CSA-C22.2 No. 62368-1 2nd Edition, Issued December 1, 2014

Markings and Instructions

Clause Title	Marking or Instruction Details
Equipment identification marking – Manufacturer identification	Listees or Recognized companys name, Trade Name, Trademark or File Number
Equipment identification marking – model identification	Model Number
Equipment rating marking – ratings	"Input Ratings (voltage, frequency/dc, current/power)", "Output Ratings (voltage, frequency/dc, current/power)"
Fuses – replaceable by ordinary or instructed person	(component ID:____), Ratings (____A), "Ratings (____A, ____V)", and (symbol of required characteristics) located on or adjacent to fuse or fuseholder
Terminals for external primary power supply conductors	Capital letter "N" located adjacent to a terminal intended exclusively for connection of the primary power neutral conductor
Class II Equipment with functional earth	Symbol for Class II with functional earth construction  (IEC 60417-5092)

Special Instructions to UL Representative

N/A