

UL TEST REPORT AND PROCEDURE

Standard:	UL 62368-1, 2nd Ed, 2014-12-01 (Audio/video, information and communication technology equipment Part 1: Safety requirements) CAN/CSA C22.2 No. 62368-1-14, 2nd Ed-(Audio/video, information and communication technology equipment Part 1: Safety requirements)
Certification Type:	Component Recognition
CCN:	QQJQ2, QQJQ8 (Power Supplies for Use in Audio/Video, Information and Communication Technology Equipment)
Complementary CCN:	N/A
Product:	Switch Mode Power Supply
Model:	CFE400M or CFE-400M series (See Model Differences for details of nomenclature)
Rating:	100 -240Vac nom, 6.1A rms max, 47 -440Hz (see Model Differences for details)
Applicant Name and Address:	TDK-LAMBDA UK LTD KINGSLEY AVE ILFRACOMBE EX34 8ES UNITED KINGDOM

This is to certify that representative samples of the products covered by this Test Report have been investigated in accordance with the above referenced Standards. The products have been found to comply with the requirements covering the category and the products are judged to be eligible for Follow-Up Service under the indicated Test Procedure. The manufacturer is authorized to use the UL Mark on such products which comply with this Test Report and any other applicable requirements of UL LLC ('UL') in accordance with the Follow-Up Service Agreement. Only those products which properly bear the UL Mark are considered as being covered by UL's Follow-Up Service under the indicated Test Procedure.

The applicant is authorized to reproduce the referenced Test Report provided it is reproduced in its entirety.

UL authorizes the applicant to reproduce the latest pages of the referenced Test Report consisting of the first page of the Specific Technical Criteria through to the end of the Conditions of Acceptability.

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL.

Prepared By: Mark John De Sagun / Project
Handler

Reviewed By: Dennis Butcher / Reviewer

Supporting Documentation

The following documents located at the beginning of this Procedure supplement the requirements of this Test Report:

A. Authorization - The Authorization page may include additional Factory Identification Code markings.

B. Generic Inspection Instructions -

- i. Part AC details important information which may be applicable to products covered by this Procedure. Products described in this Test Report must comply with any applicable items listed unless otherwise stated in the body of this Test Report.
- ii. Part AE details any requirements which may be applicable to all products covered by this Procedure. Products described in this Test Report must comply with any applicable items listed unless otherwise stated in the body of each Test Report.
- iii. Part AF details the requirements for the UL Certification Mark which is not controlled by the technical standard used to investigate these products. Products are permitted to bear only the Certification Mark(s) corresponding to the countries for which it is certified, as indicated in each Test Report.

Product Description

CFE400M or CFE-400M series switch mode power supplies for building into host equipment. (see Model Differences for nomenclature and details).

Model Differences

CFE400M or CFE-400M series as described below:

Units may be marked with a Product Code: U7x or Y7x where x may be any number of letters and/or numbers 0 to 9.

Unit Configuration (Description) Code may be prefixed by NS # followed by / or - (where # may be any number of characters indicating non- safety related model differences). Code may alternatively be prefixed by SP followed by / or - (SP represents a sales code).

Unit Configuration Code:

CFE400Mx-a-bc-defg-hi-j-k-lmn-o

Where:

x = Blank for Y2 capacitors from output to earth

P for Y1 capacitors from output to earth

a = Channel 1 output Voltage (see Ch1 in the table below, adjustment range column).

b = Standby voltage (see standby in the table below, adjustment range column).

N for no supply

c = N no for supply.

C for 0.1A.

H for 1A.

d = NN for no fan, no fan supply

N1 for 12V nom / 0.25A fan supply. (V varies with Ch1 output voltage)

TF for chassis with fan fitted to cover.

e = U for chassis only.

C for chassis with perforated or top fan cover.

S for chassis with cover.

f = M for Molex KK type 41791 input connector or equivalent.

S for screw terminal input connector.

g = S for standard Leakage,

L for low Leakage,

R for reduced Leakage

T for tiny Leakage*

h = Y for Oring FET included.

N for no Oring FET.

i = N for no inhibit or enable.

T for inhibit.

E for enable.

j = Omit for standard channel 1 output voltage with no droop.

Dx where D is for units with programmed negative load regulation,

x is the voltage of the regulation in 100mVolts and is within the Output Adjustment range (example, D5 = 0.5V of negative load regulation).

k = Omit for no secondary comms.

lmn = Blank for standard output settings or three numbers from 0 to 9 which denotes various output voltage/current settings within the specified ranges of each output for a particular unit. (may define non-safety related parameters/feature, e.g. reduced primary current limit, reduced OVP)

o = Blank for dual fuse input or -FL for single fuse input in the live line

* S >300 μ A Leakage, L <300 μ A Leakage, R <150 μ A Leakage and T <75 μ A Leakage

Input Parameters

Standard	62368-1
Nominal input voltage	100 - 240 Vac
Input voltage range	85 - 264 Vac
Input frequency range	47 - 440 Hz

Maximum input current 6.1A rms (6.4A rms 450W peak)

All ratings apply for ambient temperatures up to 50°C. (see variations and limitations below)

Output Parameters

There are three CFE400M standard models with various options and output parameters shown in the tables below.

Standard models:

Standard models at 50°C maximum ambient in forced air and top fan models:

Output Channel	Vout Nom.	Adjustment Range (V)	Maximum Output Current (A)	Maximum Power (W)
Channel 1	12	9 - 14.4	33.33 (35.7†)	400 (450†)
	15	14.4 - 15.5	24.67	370
	24	18 - 28.8	16.67 (18.75†)	400 (450†)
	48	36 - 54	8.34 (9.38†)	400 (450†)
Fan output (optional)	12	9 - 12	0.25	3
Standby output (optional)	5	5 - 5.5*	1	5.5
Standby output (optional)	5	5	0.1	0.5

Variations and limitations of use for Standard models at 50°C maximum ambient in forced air and fan models:

- * Can be adjusted at the factory only.
- Maximum continuous power output 400W.
- † Peak power of 450W for 10 seconds maximum, maximum rms power of 400W.
- See Cooling for customer air below for forced air and convection cooled models.
- Channel 1 output de-rated 10W/°C from 50°C - 70°C.

Standard model at 50°C maximum ambient convection cooled:

Output Channel	Vout Nom.	Adjustment Range (V)	Maximum Output Current (A)	Maximum Power (W)
Channel 1	12	9 - 14.4	20.83 (35.7†)	250 (450†)
	15	14.4 - 15.5	15.4	231
	24	18 - 28.8	10.41 (18.75†)	250 (450†)
	48	36 - 54	5.21 (9.38†)	250 (450†)
Fan output (optional)	12	9 - 12	0.25	3
Standby output (optional)	5	5 - 5.5*	1	5.5
Standby output (optional)	5	5	0.1	0.5

Variations and limitations of use for Standard models at 50°C maximum ambient convection cooled:

1. * Can be adjusted at the factory only.
2. Maximum continuous power output 250W.
3. † Peak power of 450W for 10 seconds maximum, maximum rms power of 250W.
4. See Cooling for customer air below for convection cooled models.
5. Channel 1 output de-rated 10W/°C from 50°C - 60°C.

Standard model at 40°C maximum ambient convection cooled:

Output Channel	Vout Nom.	Adjustment Range (V)	Maximum Output Current (A)	Maximum Power (W)
Channel 1	12	9 - 14.4	25 (35.7†)	300 (450†)
	15	14.4 - 15.5	18.46	277
	24	18 - 28.8	12.5 (18.75†)	300 (450†)
	48	36 - 54	6.25 (9.38†)	300 (450†)
Fan output (optional)	12	9 - 12	0.25	3
Standby output (optional)	5	5 - 5.5*	1	5.5
Standby output (optional)	5	5	0.1	0.5

Variations and limitations of use for Standard models at 40°C maximum ambient convection cooled:

1. * Can be adjusted at the factory only.
2. Maximum continuous power output 300W.
3. † Peak power of 450W for 10 seconds maximum, maximum rms power of 300W.
4. See Cooling for customer air below for convection cooled models.
5. Channel 1 output de-rated 5W/°C from 40°C - 50°C.

Standard model at 40°C maximum ambient convection cooled:

Output Channel	Vout Nom.	Adjustment Range (V)	Maximum Output Current (A)	Maximum Power (W)
Channel 1	48	38 - 42	6.25 (15†)	300 (630†)
Standby output (optional)	5	5	0.1	0.5

Variations and limitations of use for Standard models at 40°C maximum ambient convection cooled:

1. Maximum continuous power output 300W.
2. † Peak power of 630W with Ch1: 10ms saw-tooth current waveform of 42V at 15A to 5A for 10s followed by 42V at 1A for 30s minimum. Standby at 5V, 0.1A continuous.
3. See Cooling for customer air below for convection cooled models.

Output Limitations

All outputs are ES1 except 48V which is ES2.

Series outputs are not allowed without further evaluation in end-use equipment.

All outputs have basic spacings to earth rated for mains - 250Vac, and due consideration must be given to this in the end product design.

Environmental parameters

Description	Operation	Storage
Use	Indoor	-
Temperature	0°C - +70°C *	-40°C - +70°C
Humidity	5 - 95% RH, non-condensing	5 - 95% RH, non-condensing
Altitude	-200m - 5000m	-200m - 5000m
Pressure	54kPa - 106kPa	54kPa - 106kPa
Orientation	Sides, vertical with input lowest, horizontal (customer air versions: all)	All
Material Group	IIIb	
Pollution Degree	2	
Overvoltage Category	II	
Class	I	

* See variations and limitations of use for each model above.

Test Item Particulars

Classification of use by	Skilled person
Supply Connection	AC Mains
Supply % Tolerance	+10%/-10%
Supply Connection – Type	mating connector
Considered current rating of protective device as part of building or equipment installation	20 A; building;
Equipment mobility	for building-in
Over voltage category (OVC)	OVC II
Class of equipment	Class I
Access location	N/A
Pollution degree (PD)	PD 2
Manufacturer's specified maximum operating ambient (°C)	50 (full load), 70°C (de-ratings apply)
IP protection class	IPX0
Power Systems	TN
Altitude during operation (m)	5000 m
Altitude of test laboratory (m)	2000 m or less
Mass of equipment (kg)	1

Technical Considerations

- The product was submitted and evaluated for use at the maximum ambient temperature (T_{ma}) permitted by the manufacturer's specification of : 50°C (full load), 70°C (de-ratings apply) (see Product differences for limitations)
- The product is intended for use on the following power systems : TN
- Considered current rating of protective device as part of the building installation (A) : 20
- Mains supply tolerance (%) or absolute mains supply values : +10%/-10%
- The equipment disconnect device is considered to be : provided by the end equipment
- The following were investigated as part of the protective earthing/bonding : Printed wiring board trace (refer to Enclosure - Schematics + PWB for layouts)
- The following are available from the Applicant upon request : Installation (Safety) Instructions / Manual
- The product was investigated to the following additional standard : CSA CAN/CSA-C22.2 NO. 62368-1 2nd Ed, Issued December 1, 2014, EN 62368-1:2014 + A11:2017
- Multilayer PWB's accepted under CBTR Ref. No. E349607-A23 dated 2014-07-31 and letter report in Enclosure 8-01 of this report.
See enclosure 7-03 for rationale for waived test.

Engineering Conditions of Acceptability

For use only in or with complete equipment where the acceptability of the combination is determined by UL LLC. When installed in an end-product, consideration must be given to the following:

- The following product-line tests are conducted for this product : Earthing Continuity, Electric Strength
- The end-product Electric Strength Test is to be based upon a maximum working voltage of : Primary-Secondary: 384 Vrms, 614 Vpk; Primary-Earthed Dead Metal: 340 Vrms, 614 Vpk
- The following output circuits are at ES1 energy levels : all except 48V, CH1 which is ES2.
- The following output circuits are at ES2 energy levels : 48V, CH1
- The following output circuits are at PS3 energy levels : All outputs (by the Manufacturers declaration)
- The maximum investigated branch circuit rating is : 20 A
- The investigated Pollution Degree is : 2
- Proper bonding to the end-product main protective earthing termination is : Required
- An investigation of the protective bonding terminals has : been conducted
- The following end-product enclosures are required : Electrical, Fire, Mechanical
- The following magnetic devices (e.g. transformers or inductor) are provided with an OBJ2 insulation system with the indicated rating greater than Class A (105°C) : TX1, TX3 and TX5 (Class F) - see table 1.5.1 for details of insulation systems used
- The following components require special consideration during end-product Thermal (Heating) tests due to the indicated maximum temperature measurements during component-level testing : Models without a fan require component temperatures monitored as detailed in Additional Information
- The power supply was evaluated to be used at altitudes up to : "5,000 m"
- The following output terminals were referenced to earth during performance testing: All secondary outputs and their return lines individually referenced to obtain maximum working voltage.
- Fans: The fan provided in this sub-assembly is provided with a fan guard to reduce the risk of operator contact with the fan. The fan provided in this sub-assembly is not intended for operator access.
- When operated at a frequency greater than 63Hz, evaluation of the end equipment against the requirements of clause 5.7 must be considered.

Additional Information

Marking label is representative of entire series

Customer Air Cooling:

The following method must be used for determining the safe operation of PSUs when NN, U or S options (Customer Air) are fitted, i.e. fan not fitted to PSU. The minimum permitted airflow for customer air cooling is 0.5m/s.

For PSUs and assemblies cooled by customer supplied airflow the components listed in the following table must not exceed the temperatures given. Additionally ratings specified for units with an internal fan shall still be complied with, eg. mains input voltage range, maximum output power, module voltage / current ratings and maximum ambient temperature. To determine the component temperatures the heating tests shall be conducted in accordance with the requirements of IEC60950-1. Consideration should also be given to the requirements of other safety standards.

Test requirements include: PSU/assembly to be fitted in its end-use equipment and operated under the most adverse conditions permitted in the end-use equipment handbook/specification and which will result in the highest temperatures in the PSU/assembly. To determine the most adverse conditions consideration shall be given to the end use equipment maximum operating ambient, the PSU/assembly loading and input voltage, ventilation, end use equipment orientation, the position of doors & covers, etc. Temperatures shall be monitored using type K fine wire thermocouples (secured with cyanoacrylate adhesive, or similar) placed on the hottest part of the component (out of any direct airflow) and the equipment shall be run until all temperatures have stabilised.

Circuit Ref.	Description	Max. Temperature (°C) †
J1	Input connector	105
C7, C8	X capacitor	100
L1, L2	Common mode choke winding	110
L9	Series mode choke winding	120 (130)
TX1††, TX3	Standby trx winding	110 (130)
U2, U7	Opto-coupler	100
ASY4-B	PFC FET	120
ASY4-C	Boost diode	120
L3, L5	Boost choke winding	110 (140)
C9	Boost capacitor	83 (105)
ASY5	Bridge	125 (130)
RLY1	Relay	100
L6 winding	Primary resonant choke winding	125 (145)
TX5-A	Primary winding	110 (130)
TX5-B	Channel 1 winding	110 (130)
TX5-C	Sec aux winding	110 (130)
XQ18	HS Ch1 synchronous rectifier	120 (130)
XL1	Channel 1 output choke	110 (130)
ASY7-C (††)	Standby switch	120
ASYF4-F (††)	Oring FET	120
C1, C3, C5, C16, C17, C21 (††)	Electrolytic capacitors	82.5 (105)
C6, C18 (††)	Electrolytic capacitors	91 (105)

† The higher temperatures limits in brackets may be used but product life may be reduced.


†† When fitted.

Additional Standards

The product fulfills the requirements of: EN 62368-1:2014 + A11:2017, CSA CAN/CSA-C22.2 No. 62368-1 2nd Edition, Issued December 1, 2014

Markings and Instructions

Clause Title	Marking or Instruction Details
--------------	--------------------------------

Equipment identification marking – Manufacturer identification	Listee's or Recognized companys name, Trade Name, Trademark or File Number
Equipment identification marking – model identification	Model Number
Equipment rating marking – ratings	"Input Ratings (voltage, frequency/dc, current/power)", "Output Ratings (voltage, frequency/dc, current/power)"
See Installation Instructions	The symbol 
Special Instructions to UL Representative N/A	