


IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)  
CB SCHEME

## CB TEST CERTIFICATE

Product	AC-DC Power Supply for DIN rail
Name and address of the applicant	TDK-LAMBDA UK LTD KINGSLEY AVE ILFRACOMBE, EX34 8ES United Kingdom
Name and address of the manufacturer	TDK-LAMBDA UK LTD KINGSLEY AVE ILFRACOMBE, EX34 8ES United Kingdom
Name and address of the factory <i>Note: When more than one factory, please report on page 2</i>	TDK-LAMBDA MALAYSIA SDN BHD LOT 2 & 3, BATU 9 3/4 KAWASAN PERINDUSTRIAN BANDAR BARU JAYA GADING 26070 KUANTAN PAHANG MALAYSIA <input type="checkbox"/> Additional Information on page 2
Ratings and principal characteristics	See Page 2
Trademark / Brand (if any)	TDK LAMBDA 
Type of Customer's Testing Facility (CTF) Stage used	
Model / Type Ref.	DRB50-12-1-xyz, DRB50-15-1-xyz, DRB50-24-1-xyz, DRB50-48-1-xyz, DRB50-5-1-xyz See Page 2
Additional information (if necessary may also be reported on page 2)	Additionally evaluated to EN 62368-1:2014 / A11: 2017; National Differences specified in the CB Test Report. <input type="checkbox"/> Additional Information on page 2
A sample of the product was tested and found to be in conformity with	IEC 62368-1:2014
As shown in the Test Report Ref. No. which forms part of this Certificate	E135494-A6013-CB-1 issued on 2019-09-27

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see [www.ul.com/ncbnames](http://www.ul.com/ncbnames)

Date: 2019-09-27

Signature:

Jan-Erik Storgaard



Ref. Certif. No.

**DK-88169-UL**

**Model Details:**

DRB50-12-1-xyz, DRB50-15-1-xyz, DRB50-24-1-xyz, DRB50-48-1-xyz, DRB50-5-1-xyz where x, y and z can be any alphanumeric character or blank, not safety relevant.

**Ratings:**

**Input:**

All models: 100-240 Vac, 2.4 A max, 50/60 Hz

**Output:**

DRB50-5-1-xyz: 5-5.5 Vdc / 6-5.4 A, max 30 W.

DRB50-12-1-xyz: 12-15 Vdc / 3.4 A, max. 51 W.

DRB50-15-1-xyz: 15 Vdc / 3.4 A, max. 51 W.

DRB50-24-1-xyz: 24-28 Vdc / 2.1-1.8 A, max. 50.4 W.

DRB50-48-1-xyz: 48-52.8 Vdc / 1.05-0.95 A, max. 50.4 W.

**Additional information (if necessary)**



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see [www.ul.com/ncbnames](http://www.ul.com/ncbnames)

Date: 2019-09-27

Signature:   
Jan-Erik Storgaard