

	Test Report issued under the responsibility of:	
---	--	---

<b>TEST REPORT</b> <b>IEC 60950-1</b> <b>Information technology equipment - Safety -</b> <b>Part 1: General requirements</b>	
<b>Report Reference No</b> .....	4787000011-2
Date of issue .....	2015-11-10
Total number of pages .....	98
<b>CB Testing Laboratory</b> .....	UL Japan, Inc.
Address .....	4383-326 Asama-cho, Ise-shi, Mie, 516-0021, Japan
<b>Applicant's name</b> .....	TDK-LAMBDA CORP
Address .....	NAGAOKA TECHNICAL CENTER R&D DIV 2704-1 SETTAYA-MACHI NAGAOKA-SHI NIIGATA 940-1195 JAPAN
<b>Test specification:</b>	
Standard .....	IEC 60950-1:2005 (Second Edition); Am1:2009 + Am2:2013
Test procedure .....	CB Scheme
Non-standard test method .....	N/A
<b>Test Report Form No.</b> .....	IEC60950_1F
Test Report Form originator .....	SGS Fimko Ltd
Master TRF .....	Dated 2014-02
<b>Copyright © 2014 Worldwide System for Conformity Testing and Certification of Electrotechnical Equipment and Components (IECEE), Geneva, Switzerland. All rights reserved.</b>	
This publication may be reproduced in whole or in part for non-commercial purposes as long as the IECEE is acknowledged as copyright owner and source of the material. IECEE takes no responsibility for and will not assume liability for damages resulting from the reader's interpretation of the reproduced material due to its placement and context.	
If this test Report is used by non-IECEE members, the IECEE/IEC logo and the reference to the CB Scheme procedure shall be removed.	
<b>This report is not valid as a CB Test Report unless signed by an approved CB Testing Laboratory and appended to a CB Test Certificate issued by an NCB in accordance with IECEE 02.</b>	
<b>General disclaimer</b>	
The test results presented in this report relate only to the object tested. This report shall not be reproduced, except in full, without the written approval of the Issuing CB Testing Laboratory. The authenticity of this Test Report and its contents can be verified by contacting the NCB, responsible for this Test Report.	

<b>Test item description</b> .....	: Switching Power Supply
Trade Mark .....	: TDK-Lambda
Manufacturer .....	: TDK-LAMBDA CORP NAGAOKA TECHNICAL CENTER R&D DIV 2704-1 SETTAYA-MACHI NAGAOKA-SHI NIIGATA 940-1195 JAPAN
Model/Type reference .....	: 1) KWS15-5 2) KWS15-12 3) KWS15-15
Ratings .....	: Input: AC 100 – 240V, 0.4A, 50 / 60Hz  Output: KWS15-5      DC +5V/3.0A KWS15-12     DC +12V/1.3A KWS15-15     DC +15V/1.0A

<b>Testing procedure and testing location:</b>	
<input checked="" type="checkbox"/> <b>CB Testing Laboratory</b>	Testing location / address ..... : UL Japan, Inc. 4383-326 Asama-cho, Ise-shi, Mie, 516-0021, Japan
<input type="checkbox"/> <b>Associated CB Test Laboratory</b>	Testing location / address ..... : Tested by (name + signature) ..... : Ayano Matsumoto
	<i>A. Matsumoto</i>
	Approved by (name + signature) .... : Tetsuo Iwasaki
	<b>Tetsuo Iwasaki</b>
<input type="checkbox"/> <b>Testing Procedure: TMP/CTF Stage 1</b>	Testing location / address ..... : Tested by (name + signature) ..... : Approved by (name + signature) .... :
<input type="checkbox"/> <b>Testing Procedure: WMT/CTF Stage 2</b>	Testing location / address ..... : Tested by (name + signature) ..... : Witnessed by (name + signature) .. : Approved by (name + signature) .... :
<input type="checkbox"/> <b>Testing Procedure: SMT/CTF Stage 3 or 4</b>	Testing location / address ..... : Tested by (name + signature) ..... : Approved by (name + signature) .... : Supervised by (name + signature) . :
<input type="checkbox"/> <b>Testing Procedure: RMT</b>	Testing location / address ..... : Tested by (name + signature) ..... : Approved by (name + signature) .... : Supervised by (name + signature) . :

<b>List of Attachments</b>
National Differences ( 24 pages) Enclosures ( 22 pages)
<b>Summary Of Testing</b>
Unless otherwise indicated, all tests were conducted at UL Japan, Inc. 4383-326 Asama-cho, Ise-shi, Mie, 516-0021, Japan.

Tests performed (name of test and test clause)	Testing location / Comments
Input: Single-Phase (1.6.2)	
Energy Hazard Measurements (2.1.1.5, 2.1.2, 1.2.8.10)	
SELV Reliability Test Including Hazardous Voltage Measurements (2.2.2, 2.2.3, 2.2.4)	
Humidity (2.9.1, 2.9.2, 5.2.2)	
Determination of Working Voltage; Working Voltage Measurement (2.10.2)	
Transformer and Wire /Insulation Electric Strength (2.10.5.13)	
Heating (4.5.1, 1.4.12, 1.4.13)	
Ball Pressure (4.5.5, 4.5)	
Touch Current (Single-Phase; TN/TT System) (5.1, Annex D)	
Electric Strength (5.2.2)	
Component Failure (5.3.1, 5.3.4, 5.3.7)	
Abnormal Operation (5.3.1 - 5.3.9)	
Transformer Abnormal Operation (5.3.3, 5.3.7b, Annex C.1)	
<p><b>Summary of Compliance with National Differences:</b>  Countries outside the CB Scheme membership may also accept this report.  List of countries addressed: CA, DE, DK, EU, FI, GB, KR, SE, SI, US  The product fulfills the requirements of: EN 60950-1:2006 + A1:2010 + A11:2009 + A12:2011 + A2:2013</p>	

**Copy of Marking Plate** - Refer to Enclosure titled Marking Plate for copy.

<b>Test item particulars :</b>	
Equipment mobility .....	for building-in
Connection to the mains .....	not directly connected to the mains
Operating condition .....	continuous
Access location .....	restricted access location
Over voltage category (OVC) .....	OVC II
Mains supply tolerance (%) or absolute mains supply values .....	+6%, -10%
Tested for IT power systems .....	No (only for Norway)
IT testing, phase-phase voltage (V) .....	N/A
Class of equipment .....	Class I
Considered current rating of protective device as part of the building installation (A) .....	16A (for Europe)
Pollution degree (PD) .....	PD 1
IP protection class .....	Not rated, indoor use only
Altitude of operation (m) .....	Up to 2000
Altitude of test laboratory (m) .....	< 1000 m
Mass of equipment (kg) .....	Approximately 0.075 kg
<b>Possible test case verdicts:</b>	
- test case does not apply to the test object .....	N/A
- test object does meet the requirement .....	P(Pass)
- test object does not meet the requirement .....	F(Fail)
<b>Testing:</b>	
Date(s) of receipt of test item .....	2005-03-18, 2010-08-22
Date(s) of Performance of tests .....	2005-03-18, 2010-09-23, 2010-09-24
<b>General remarks:</b>	
<p>"(see Enclosure #)" refers to additional information appended to the report.                  "(see appended table)" refers to a table appended to the report.</p> <p>Throughout this report a point is used as the decimal separator.</p>	
<b>Manufacturer's Declaration per Sub Clause 4.2.5 of IEC 60950-1:</b>	
The application for obtaining a CB Test Certificate includes more than one factory and a declaration from the Manufacturer stating that the sample(s) submitted for evaluation is (are) representative of the products from each factory has been provided .....	Yes
When differences exist, they shall be identified in the General Product Information section.	
<b>Name and address of Factory(ies):</b>	VIETTRONICS BINH HOA JOINT STOCK COMPANY 204 NO TRANG LONG ST

BINH THANH  
HO CHI MINH CITY VIET NAM

TDK-LAMBDA MALAYSIA SDN BHD  
PLO33 KAWASAN PERINDUSTRIAN SENAI  
81400 SENAI MALAYSIA

## GENERAL PRODUCT INFORMATION:

### Report Summary

All applicable tests according to the referenced standard(s) have been carried out.

### Product Description

Switching power supply for use in general office equipment (host equipment is not specified).

### Model Differences

All the models are identical, except output voltage and output current.

### Additional Information

This report is a reissue of CBTR Ref. No.:18004382 001, CB Test Certificate Ref. No.JPTUV-046090. Based on the previously conducted testing and the review of product technical documentation including photos, schematics, wiring diagrams and similar, has been determined that the product continues to comply with the standard.

Abbreviations used in the report.

- built-in application: B/I

In this Test Report, CENELEC mark license indicating compliance to EN standard was used to verify component compliance to IEC standard because the standards are technically equivalent.

It was considered that UL Standard has requirements that meet or exceed the relevant IEC requirements.

### Technical Considerations

- The product was submitted and evaluated for use at the maximum ambient temperature (T<sub>ma</sub>) permitted by the manufacturer's specification of: 50°C
- The product is intended for use on the following power systems: TN
- The product was investigated to the following additional standards: EN 60950-1:2006 + A11:2009 + A1:2010 + A12:2011 + A2:2013 (which includes all European national differences, including those specified in this test report).

### Engineering Conditions of Acceptability

When installed in an end-product, consideration must be given to the following:

- The end-product Electric Strength Test is to be based upon a maximum working voltage of: max working voltage: 265 V<sub>rms</sub>, 492 V<sub>pk</sub>

- The following secondary output circuits are SELV: All output
- The maximum investigated branch circuit rating is: 16 A
- The investigated Pollution Degree is: 2
- Proper bonding to the end-product main protective earthing termination is: Required
- An investigation of the protective bonding terminals has: Not been conducted
- The following magnetic devices (e.g. transformers or inductor) are provided with an OBJY2 insulation system with the indicated rating greater than Class A (105°C): T1 (Class B)
- The following end-product enclosures are required: Fire, Electrical

Abbreviations used in the report:

- normal condition .....	N.C.	- single fault condition.....	S.F.C
- operational insulation .....	OP	- basic insulation .....	BI
- basic insulation between parts of opposite polarity:	BOP	- supplementary insulation .....	SI
- double insulation .....	DI	- reinforced insulation .....	RI

Indicate used abbreviations (if any)