



TDK-Lambda UK Limited
Kingsley Avenue, Ilfracombe
Devon, EX34 8ES, United Kingdom
Tel: +44 (0) 1271 856600
Fax: +44 (0) 1271 864894
www.uk.tdk-lambda.com

EU DECLARATION OF CONFORMITY

CUS100ME and CUS150M Series

We, TDK-Lambda UK Limited, of Kingsley Avenue, Ilfracombe, Devon, EX34 8ES declare under our sole responsibility that the TDK-Lambda CUS100ME and CUS150M series of power supplies, as detailed on the attached products covered sheets, complies with the provisions of the following European Directives and is eligible to bear the CE mark:

Low Voltage Directive	2014/35/EU
EMC Directive	2014/30/EU
RoHS 2 Directive	2011/65/EU

Assurance of conformance of the described product with the provisions of the stated EC Directive is given through compliance to the following standards:

Electrical Safety (LVD)	EN60950-1:2006 + A2:2013
Electromagnetic Compatibility (EMC)	EN61000-6-3:2007 + A1:2011 EN61000-6-2:2005 EN61204-3:2001 EN55024:2010 EN55032:2015

Our European Representative in the EU is TDK-Lambda UK Limited, located at Kingsley Avenue, Ilfracombe, Devon, EX34 8ES, UK.

Note: The EMC performance of a component power supply will be affected by the final installation, compliance to the stated EMC standards and conformance to the EMC Directive must be confirmed after installation by the final equipment manufacturer.
For guidance with respect to test conditions please visit our website at https://emea.tdk-lambda.com/EMC_Guidance or contact your local TDK-Lambda sales office.

Name of Authorized Signatory	Martin Southam
Signature of Authorized Signatory	
Position of Authorized Signatory	Marketing Director, TDK-Lambda EMEA
Date	18 th April 2018
Date when first CE marked	9 th May 2017
Place where signed	Ilfracombe, Devon, England

CUS100ME and CUS150M SERIES PRODUCTS COVERED

The CUS has two ranges of 100W and 150W each with seven nominal output voltages of 12, 15, 18, 24, 28, 36 and 48 Volt. Each output has a range shown in the table below which is factory configurable only.

CUS models as described below:

Units may be marked with a Product Code: CUSZ-xxVx/yyyy where Z is 100ME or 150M and x may be any number of numbers or left blank to indicate the output voltage. V represents a decimal place when required or can left be left blank. y can be any number of numbers or letters (excluding M, E, U, A, F, B, H) when indicating non-safety related model differences. y can be M, E, U, A, F, B, H when indicating the standard options as listed below.

Unit Product Code may be prefixed by K, SP # and/or NS # followed by / or - (where # may be any number of characters indicating non-safety related model differences).

Unit Product Code:

CUSZ-xxVx/yyyy

Where

- Z = 150M for 150W model (May be followed by 'D' for DC input)
100ME for 100W model
- xxVx = Channel 1 output voltage from within the output voltage adjustment range from the Output Parameters Table below.
- yyyy = Unit options from list of standard unit options below, or non-safety related model differences
 - /M = Molex connectors
 - /E = Single fuse in the live line
 - /U = U chassis
 - /A = Cover and U chassis
 - /F = Top fan, cover and U chassis (CUS150M model only)
 - /B = Baseplate
 - /H = alternate link wire and discharge resistors (60335-1 compliant, 60950-1 approved only)

Non standards

KCUSZ-xx-yyyy/H

Where:

- Z = 150M for 150W model (May be followed by 'D' for DC input)
100ME for 100W model
- xxVx = Channel 1 output voltage from within the output voltage adjustment range from the Output Parameters Table below.
- yyyy = Unit options from list of standard unit options below, or non-safety related model differences
 - /M = Molex connectors
 - /E = Single fuse in the live line
 - /U = U chassis
 - /A = Cover and U chassis
 - /F = Top fan, cover and U chassis (CUS150M model only)
 - /B = Baseplate

Followed by

- /H = alternate link wire and discharge resistors (60335-1 compliant, 60950-1 approved only)

Input Parameters

Standard	60601-1	60950-1/61010-1	60950-1/61010-1/60601-1*
Nominal input voltage	100 - 240Vac	100 - 240Vac	133 - 318Vdc
Input voltage range	85 - 264Vac	85 - 264Vac	120 - 350Vdc
Input frequency range	47 - 63Hz	47 - 440Hz	DC
Maximum input current	2.2A rms	2.2A rms	1.8A

* 60601-1 2nd ed, 300Vdc input max.

All ratings apply for ambient temperatures up to 50°C. (See Variations and Limitations below)

Output power is reduced linearly by 10% for input voltages from 90 to 85Vac

Output Parameters

There are seven CUS150M and CUS100ME standard models as shown in the tables below. All of these models may be fan (CUS150M model only), forced air, conduction or convection cooled. The output parameters are shown in the tables below. Outputs are not user adjustable but can be factory set.

CUS150M

Model	Vout Range (V)	*Fan Vnom (V)	Max Iout (A)	Max Pout (W)	*Fan Output ratings	
					Inom (A)	Pnom (W)
12	12-13.2	11.6	12.5	150	0.5	5.8
15	15-16.5	9.8	10	150	0.5	4.9
18	18-19.8	11.6	8.33	150	0.5	5.8
24	24-26.4	11.6	6.25	150	0.5	5.8
28	28-30.8	10.8	5.4	150	0.5	5.4
36	36-39.6	11.6	4.2	150	0.5	5.8
48	48-50	11.6	3.125	150	0.5	5.8

* Fan output tracks Vout Range

Variation and Limitations:

Customer Forced Air Cooling max ambient 85°C (note 1)

Convection and conduction/cold plate Cooling (U chassis with lid-Option A) max ambient 75°C (note 1)

Convection and conduction/cold plate Cooling (U chassis and open frame) max ambient 80°C (note 1)

Fan supplied ratings/Option F max ambient 70°C, from 50°C to 70°C the output power is de-rated by 0.5°C per watt

Note 1: Maximum output power and current ratings are dependent on the ambient used in the end equipment.

CUS100M

Model	Vout Range (V)	Max Iout (A)	Max Pout (W)
12	12-13.2	8.33	100
15	15-16.5	6.66	100
18	18-19.8	5.55	100
24	24-26.4	4.16	100
28	28-30.8	3.57	100
36	36-39.6	2.77	100
48	48-50	2.08	100

Variation and Limitations:

Customer Forced Air Cooling max ambient 85°C (note 1)

Convection and conduction/cold plate Cooling (U chassis with lid-Option A) max ambient 75°C (note 1)

Convection and conduction/cold plate Cooling (U chassis and open frame) max ambient 80°C (note 1)

Note 1: Maximum output power and current ratings are dependent on the ambient used in the end equipment.