



Medical

160W to 165W Medical AC-DC External Power Supplies



Features	Benefits
• CEC, ErP and EISA ⁽¹⁾ Level V Compliant	• Easier System Approvals
• Wide Range AC Input	• Global Operation
• 60601-1 Medical Certification /2xMoPP	• Simplifies Equipment Design
• >87% Average Efficiency	• Consumes Less Energy

Notes: (1) EISA - Energy Independence and Security Act of 2007

Specification		
Model	DTM165PWxxx-C	
Input Voltage Range	VAC	90 - 264VAC (47 - 63Hz)
Inrush Current	A	<130A at 230VAC input, 25°C ambient cold start
Input Current	A	2.5A at 90VAC, Full Load
Power Factor	-	Meets EN61000-3-2. >0.9 PF
Leakage Current (264VAC 60Hz)	uA	<300uA
Hold Up Time (Typ)	ms	>10ms
Temperature Coefficient	%/°C	±0.05%/°C
Voltage Accuracy	%	±1%
Adjustment Range	V	None
Minimum Load	A	None
Total Regulation	%	12V to 19V Models:±5%, >19V models ±3%
Ripple & Noise	%	1%
Short Circuit Protection	-	<160% - hiccup mode
Overvoltage Protection	V	120 - 150% of nominal (Cycle input power to reset)
Efficiency	%	>87% average efficiency
Operating Temperature	°C	0°C to 60°C, derate linearly 50% load from 40°C to 60°C
Storage Temperature	°C	-10°C to 80°C
Humidity (non condensing)	%RH	0 - 90%RH
Cooling	-	Convection
Withstand Voltage	VAC	Input to Ground 1.5kVAC, Input to Output 4kVAC (Reinforced) (2 x MOPPs) ⁽¹⁾
Vibration (non operating)	-	23.52m/s ² (10 - 55Hz: constant sweep 1 min X, Y, Z for 1 hour)
Shock	-	< 196.1 m/s ² (20G)
Safety Agency Certification	-	UL60601-1, EN60601-1, IEC60601-1, CE Mark
Efficiency Level	-	CEC, ErP, EISA level V
Offload Power Consumption	W	< 0.5W
Conducted & Radiated EMI	-	EN55022, FCC Part 18 Class B
Immunity	-	EN55011:2007+A2:2007
Weight (Typ)	g	790
Size (WxLxH)	mm	85 x 170 x 44
Cable Length	mm	1050
AC Input Connector	-	IEC 320-C14 (Accepts IEC 320-C13)
Output Connector	-	Kycon KPPx-4P or equivalent Pins 1 & 2: -Vout, Pins 3 & 4: +Vout
Warranty	yrs	3

Note: (1) Output isolated and output grounded options available, see model selector


Model Selector

Model	Output (V)	Maximum Output (A)	Maximum Power (W)
DTM165PW120C	12	13.333	160
DTM165PW150C	15	10.67	160
DTM165PW190C	19	8.42	160
DTM165PW240C	24	6.88	165
DTM165PW280C	28	5.89	165
DTM165PW360C	36	4.58	165
DTM165PW480C	48	3.44	165

Standard model - output isolated from GND

Option: add suffix **-G** (DTM165PWxxxC-G) for output connected to GND

Outline Drawing DTM165-C Series



Other External AC-DC Products

DTM65-C	40W to 65W Medical Adapters
DTM65-C8	40W to 65W Medical Adapters
DTM110-C	90W to 110W Medical Adapters



TDK-Lambda France SAS

3 Avenue du Canada
 Parc Technopolis
 Bâtiment Sigma
 91940 les Ulis
 France
 Tel: +33 1 60 12 71 65
 Fax: +33 1 60 12 71 66
france@fr.tdk-lambda.com
www.emea.lambda.tdk.com/fr



Italy Sales Office

Via Giacomo Matteotti 62
 20092 Cinisello Balsamo (MI)
 Italy
 Tel: +39 02 61 29 38 63
 Fax: +39 02 61 29 09 00
info.italia@it.tdk-lambda.com
www.emea.lambda.tdk.com/it



Netherlands

info@nl.tdk-lambda.com
www.emea.lambda.tdk.com/nl



TDK-Lambda Germany GmbH

Karl-Bold-Strasse 40
 77855 Achern
 Germany
 Tel: +49 7841 666 0
 Fax: +49 7841 5000
info.germany@de.tdk-lambda.com
www.emea.lambda.tdk.com/de



Austria Sales Office

Aredstrasse 22
 2544 Leobersdorf
 Austria
 Tel: +43 2256 655 84
 Fax: +43 2256 645 12
info@at.tdk-lambda.com
www.emea.lambda.tdk.com/at



Switzerland Sales Office

Eichtalstrasse 55
 8634 Hombrechtikon
 Switzerland
 Tel: +41 44 850 53 53
 Fax: +41 44 850 53 50
info@ch.tdk-lambda.com
www.emea.lambda.tdk.com/ch



Nordic Sales Office

Haderslevvej 36B
 DK-6000 Kolding
 Denmark
 Tel: +45 8853 8086
info@dk.tdk-lambda.com
www.emea.lambda.tdk.com/dk



TDK-Lambda UK Ltd.

Kingsley Avenue
 Ilfracombe
 Devon EX34 8ES
 United Kingdom
 Tel: +44 (0) 12 71 85 66 66
 Fax: +44 (0) 12 71 86 48 94
info@uk.tdk-lambda.com
www.emea.lambda.tdk.com/uk



TDK-Lambda Ltd.

1 Alexander Yanai
 Segula
 Petah-Tikva
 Israel
 Tel: +9 723 902 4333
 Fax: +9 723 902 4777
info@tdk-lambda.co.il
www.emea.lambda.tdk.com/il



C.I.S.

Commercial Support:
 Tel: +7 (495) 665 2627
Technical Support:
 Tel: +7 (812) 658 0463
info@tdk-lambda.ru
www.emea.lambda.tdk.com/ru

Local Distribution

