

UL TEST REPORT AND PROCEDURE

Standard:	UL 60950-1, 2nd Edition, 2007-03-27 (Information Technology Equipment - Safety - Part 1: General Requirements) CAN/CSA C22.2 No. 60950-1-07, 2nd Edition, 2007-03 (Information Technology Equipment - Safety - Part 1: General Requirements)
Certification Type:	Component Recognition
CCN:	QQGQ2, QQGQ8 (Power Supplies for Information Technology Equipment Including Electrical Business Equipment)
Complementary CCN:	QQJQ2, QQJQ8 (Power Supplies for Use in Audio/Video, Information and Communication Technology Equipment)
Product:	Switching Power Supply
Model:	ZWS100BAF-abcdefgh a = 3, 5, 12, 15, 24, 36 or 48 b = "/" or blank c = "R" or blank d = "A", "L" or blank e = "CO2" or blank f = "FG" or blank g = "FV" or blank h = "FGM" or blank
Rating:	Input: Model ZWS100BAF-3: 100-240 Vac, 50/60 Hz, 1.0A Models ZWS100BAF-5, -12, -15, -24, -36, -48 100-240 Vac, 50/60 Hz, 1.3A Output: 3.3 Vdc, 20A: ZWS100BAF-3 (2.64 - 3.63V, max. 20A, max. 66W) 5 Vdc, 20A: ZWS100BAF-5 (4.0 - 5.5V, max. 20A, max. 100W) 12 Vdc, 8.5A: ZWS100BAF-12 (9.6 - 13.2V, max. 8.5A, max. 102W) 15 Vdc, 6.7A: ZWS100BAF-15 (12.0 - 16.5V, max. 26.7, max. 105W) 24 Vdc, 4.3A: ZWS100BAF-24 (19.2 - 26.4V, max. 4.3A, max. 103.2W) 36 Vdc, 2.8A: ZWS100BAF-36 (32.4 - 39.6V, max. 2.8A, max. 100.8W) 48 Vdc, 2.1A: ZWS100BAF-48 (38.4 - 52.8V, max. 2.1A, max. 100.8W)
Applicant Name and Address:	TDK-LAMBDA CORP NAGAOKA TECHNICAL CENTER R&D DIV 2704-1 SETTAYA-MACHI NAGAOKA-SHI NIIGATA 940-1195 JAPAN

Issue Date: 2010-08-11
2018-05-21

Page 2 of 13

Report Reference #

E122103-A84-UL

This is to certify that representative samples of the products covered by this Test Report have been investigated in accordance with the above referenced Standards. The products have been found to comply with the requirements covering the category and the products are judged to be eligible for Follow-Up Service under the indicated Test Procedure. The manufacturer is authorized to use the UL Mark on such products which comply with this Test Report and any other applicable requirements of UL LLC ('UL') in accordance with the Follow-Up Service Agreement. Only those products which properly bear the UL Mark are considered as being covered by UL's Follow-Up Service under the indicated Test Procedure.

The applicant is authorized to reproduce the referenced Test Report provided it is reproduced in its entirety.

UL authorizes the applicant to reproduce the latest pages of the referenced Test Report consisting of the first page of the Specific Technical Criteria through to the end of the Conditions of Acceptability.

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL.

Prepared by: Tomoko Fujii

Reviewed by: Tetsuo Iwasaki

Supporting Documentation

The following documents located at the beginning of this Procedure supplement the requirements of this Test Report:

- A. Authorization - The Authorization page may include additional Factory Identification Code markings.
- B. Generic Inspection Instructions -
 - i. Part AC details important information which may be applicable to products covered by this Procedure. Products described in this Test Report must comply with any applicable items listed unless otherwise stated in the body of this Test Report.
 - ii. Part AE details any requirements which may be applicable to all products covered by this Procedure. Products described in this Test Report must comply with any applicable items listed unless otherwise stated in the body of each Test Report.
 - iii. Part AF details the requirements for the UL Certification Mark which is not controlled by the technical standard used to investigate these products. Products are permitted to bear only the Certification Mark(s) corresponding to the countries for which it is certified, as indicated in each Test Report.

Product Description

The product is a switching power supply intended for building in to an end product.

Model Differences

All models are identical except for input rating of Model ZWS100BAF-3, output ratings, and the following suffixes:

ZWS100BAF-abcdefgh

(a = 3, 5, 12, 15, 24, 36 or 48. b = "/" or blank. c = "R" or blank. d = "A", "L" or blank. e = "CO2" or blank, f = "FG" or blank, g = "FV" or blank, h = "FGM" or blank)

a: output voltage as above

b: (separator)

c: R = remote ON/OFF control function.

d: A = L shaped metal chassis and cover.

L = L shaped metal chassis mounted solder side of unit.

e: CO2 = coating on both side of PCB. (not for reduce required spacing)

f: FG = low leakage current.

g: FV = fixed output voltage without adjustable volume.

h: FGM = low leakage current, with or without coating on both side of PCB. (coating is not for reduce required spacing)

Technical Considerations

- Equipment mobility : for building-in
- Connection to the mains : not directly connected to the mains
- Operating condition : continuous
- Access location : For building in
- Over voltage category (OVC) : OVC II
- Mains supply tolerance (%) or absolute mains supply values : +10%, -10%
- Tested for IT power systems : No
- IT testing, phase-phase voltage (V) : -
- Class of equipment : Not classified
- Considered current rating (A) : 20A
- Pollution degree (PD) : PD 2
- IP protection class : IP X0
- Altitude of operation (m) : Up to 3000 m
- Altitude of test laboratory (m) : <1000 m
- Mass of equipment (kg) : 0.3 kg approx.
- The product was submitted and evaluated for use at the maximum ambient temperature (T_{ma}) permitted by the manufacturer's specification of: For Model Series ZWS100BAF with all suffixes except /A: , 100% load @ 30°C ambient for Mounting position D, F with convection cooling; , 100% load @ 40°C ambient for Mounting positions C, E with convection cooling; , 100% load @ 50°C ambient for Mounting positions A, B with convection cooling; , See Enclosure Miscellaneous ID 7-01 for complete Output Derating Curves. , , For Model Series ZWS100BAF with suffix /A: , 100% load @ 20°C ambient for Mounting position D, F with convection cooling; , 100% load @ 30°C ambient for Mounting positions C, E with convection cooling; , 100% load @ 40°C ambient for Mounting positions A, B with convection cooling; , See Enclosure Miscellaneous ID 7-02 for complete Output Derating Curves. , , Repeat of Heating test should be considered in the end product application.

- Secondary Circuits are separated from primary by double/ reinforced insulation.
- Primary circuits are separated from earth by at least basic insulation.

Engineering Conditions of Acceptability

For use only in or with complete equipment where the acceptability of the combination is determined by UL LLC. When installed in an end-product, consideration must be given to the following:

- The following secondary output circuits are SELV: All
- The following secondary output circuits are at non-hazardous energy levels: All
- The power supply terminals and/or connectors are: Not investigated for field wiring
- The maximum investigated branch circuit rating is: 20 A
- The investigated Pollution Degree is: 2
- Proper bonding to the end-product main protective earthing termination is: Required
- An investigation of the protective bonding terminals has: Been conducted
- The following magnetic devices (e.g. transformers or inductor) are provided with an OBJ2 insulation system with the indicated rating greater than Class A (105°C): T2 (Class 155(F))
- The following end-product enclosures are required: Electrical, Fire, Mechanical
- Heating Tests shall be repeated in the end product evaluation.
- The following secondary output circuits are ES1: 3.3 Vdc Output, 5 Vdc Output, 12 Vdc Output, 15 Vdc Output, 24 Vdc Output, 36 Vdc Output and 48 Vdc Output
- The following secondary output circuits are at PS3: 3.3 Vdc Output, 5 Vdc Output, 12 Vdc Output, 15 Vdc Output, 24 Vdc Output, 36 Vdc Output and 48 Vdc Output
- Humidity conditioning has been conducted by tropical condition.
- Classification of PIS has not been conducted. Therefore, all electrical components and conductors including printed wirings were assumed to be arcing/resistive PIS.
- This component has been evaluated in 'control of fire spread' method assuming appropriate fire enclosure is provided in end product. Unless the fire enclosure is made of non-combustible or V-0 material, the separation from the PIS shall be considered.

Additional Information

N/A

Additional Standards

The product fulfills the requirements of: The product fulfills the requirements of: The product fulfills the requirements of: UL 62368-1, 2nd Edition, 2014-12-01, CAN/CSA C22.2 No. 62368-1-14, 2nd Edition, 2014-12.

Markings and instructions

Clause Title	Marking or Instruction Details
Power rating - Ratings	Ratings (voltage, frequency/dc, current)
Power rating - Company identification	Listee's or Recognized company's name, Trade Name, Trademark or File Number

Issue Date: 2010-08-11
2018-05-21

Page 6 of 13

Report Reference #

E122103-A84-UL

Power rating - Model	Model Number
Fuses - Rating	Rated current and voltage and type located on or adjacent to fuse or fuseholder.