

DEMKO CERTIFICATE

Certificate No. D-06972
Page 1/3
Date of Issue 2018-12-13

Certificate Holder TDK-LAMBDA CORP
NAGAOKA TECHNICAL CENTER
R&D DIV
2704-1 SETTAYA-MACHI
NAGAOKA-SHI
NIIGATA 940-1195 JAPAN

Manufacturer TDK-LAMBDA CORP
NAGAOKA TECHNICAL CENTER
R&D DIV
2704-1 SETTAYA-MACHI
NAGAOKA-SHI
NIIGATA 940-1195 JAPAN

Production site TDK-LAMBDA CORP
2704-1 SETTAYA-MACHI NAGAOKA-SHI NIIGATA-KEN 940-1195
JAPAN

See Page 2

Certified Product Model DC-DC Power Module
PH100A280-12, PH100A280-24, PH100A280-3.3, PH100A280-48,
PH100A280-5, PH150A280-12, See Page 2

Trademark

TDK-Lambda

Rated Voltage / Frequency

See Page 2

Rated Current / Power

See Page 2

Insulation Class

Not Classified

Degree of protection (IP)

IPX0

Tested acc. to

EN 62368-1:2014/A11:2017, EN 62368-1:2014

Test Report No.

E122103-A6036-CB-1 issued on 2018-12-12

Additional

for building-in

Expire date

2028-12-12

Certification Manager
Jan-Erik Storgaard

This is to certify that representative sample(s) of the Product described herein ("Certified Product") have been investigated and found in compliance with the Standard(s) indicated on this Certificate, in accordance with the D Mark Requirements. The Designated Certificate holder is entitled to use the d or for cables <DEMKO> for the Certified Product manufactured at the production site(s) identified above, in accordance with the D Mark Service Agreement, including without limitation the D Mark Testing and Certification Services Service Terms. Only those Products bearing the D Mark should be considered as being covered by UL's D Mark Service. This Certificate shall remain valid through the expiration date, unless terminated earlier in accordance with the Service Agreement including without limitation if the Standard identified on this Certificate is amended or withdrawn prior to the expiration date.

Certification Body

UL International Demko A/S, Borupvang 5A, DK-2750
Ballerup, Denmark, Tel. +45 44 85 65 65,
info.dk@ul.com
www.ul-europe.com



Appendix DEMKO CERTIFICATE

Certificate No. D-06972
Page 2/3
Date of Issue 2018-12-13

Model Details:

PH50A280-5, PH50A280-12, PH50A280-24, PH50A280-48
PH75A280-3.3, PH75A280-5, PH75A280-12, PH75A280-15, PH75A280-24, PH75A280-28, PH75A280-48
PH100A280-3.3, PH100A280-5, PH100A280-12, PH100A280-24, PH100A280-48
PH150A280-5, PH150A280-12, PH150A280-15, PH150A280-24, PH150A280-28, PH150A280-48
All models maybe followed by no safety relevant suffix "abcdef" (a is /, b is H, c is T, d is V, e is 2 or 3, f is CO, and "a", "b", "c", "d", "e", "f" may be blank)

Production Sites:

TDK-LAMBDA MALAYSIA SDN BHD
PLO33 KAWASAN PERINDUSTRIAN SENAI 81400 SENAI
MALAYSIA

TDK-LAMBDA MALAYSIA SDN BHD
LOT 2 & 3, BATU 9 3/4 KAWASAN PERINDUSTRIAN BANDAR BARU JAYA GADING 26070 KUANTAN
MALAYSIA

WUXI TDK-LAMBDA ELECTRONICS CO LTD
NO 6 XING CHUANG ER LU WUXI JIANGSU 214028
CHINA

ZHANGJIAGANG HUA YANG ELECTRONICS CO LTD
TONGXIN RD ZHAOFENG ECONOMIC DEVELOPMENT ZONE LEYU TOWN ZHANGJIAGANG JIANGSU 215622
CHINA

ALPS LOGISTICS FACILITIES CO LTD
593-1 NISHIOHASHI TSUKUBA-SHI IBARAKI-KEN 305-0831
JAPAN

SENDAN ELECTRONICS MFG CO LTD
1010 HABUSHIN NANTO-SHI TOYAMA-KEN 939-1756
JAPAN

Ratings:

Input Voltage: 200-425 Vdc

Input Current:

0.33A (PH50A280 series)
0.5A (PH75A280 series)
0.66A (PH100A280 series)
1.0A (PH150A280 series)

Output: See test report for details.

Certification Body

UL International Demko A/S, Borupvang 5A, DK-2750
Ballerup, Denmark, Tel. +45 44 85 65 65, info.dk@ul.com
www.ul-europe.com



Appendix DEMKO CERTIFICATE

Certificate No. D-06972
Page 3/3
Date of Issue 2018-12-13



Certification Body

UL International Demko A/S, Borupvang 5A, DK-2750
Ballerup, Denmark, Tel. +45 44 85 65 65, info.dk@ul.com
www.ul-europe.com

