




Ref. Certif. No.

DK-107093-UL

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	Switch mode power supply
Name and address of the applicant	TDK-LAMBDA UK LTD KINGSLEY AVE ILFRACOMBE, EX34 8ES United Kingdom
Name and address of the manufacturer	TDK-LAMBDA UK LTD KINGSLEY AVE ILFRACOMBE, EX34 8ES United Kingdom
Name and address of the factory	TDK-LAMBDA UK LTD KINGSLEY AVE ILFRACOMBE EX34 8ES UNITED KINGDOM
Note: <i>When more than one factory, please report on page 2</i>	
Ratings and principal characteristics	See Page 2
Trademark / Brand (if any)	TDK-Lambda 
Type of Customer's Testing Facility (CTF) Stage used	CTF Stage 3
Model / Type Ref.	XMS-350, XMS-500, XMS-500A, XMS-500AP, XMS-500P, XMS350, See Page 2
Additional information (if necessary may also be reported on page 2)	<input checked="" type="checkbox"/> Additional Information on page 2
A sample of the product was tested and found to be in conformity with	IEC 60950-1:2005/AMD1:2009, IEC 60950-1:2005/AMD2:2013, IEC 60950-1:2005
As shown in the Test Report Ref. No. which forms part of this Certificate	E135494-A103-CB-3 issued on 2020-12-11

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2020-12-11

Signature:

Jan-Erik Storgaard



Ref. Certif. No.

DK-107093-UL

Model Details:

XMS350 or XMS-350, XMS500 or XMS-500, XMS500P or XMS-500P,
XMS500A or XMS-500A, XMS500AP or XMS-500AP series switch

Factories:

PANYU TRIO MICROTRONICS CO LTD
SHIJI INDUSTRIAL ESTATE DONGYONG NANSHA GUANGZHOU GUANGDONG 511453
CHINA

TRIO-TRONICS (THAILAND) LTD

7/295 MU. 6 MAP YANG PHON SUB-DISTRICT PLUAK DAENG DISTRICT RAYONG PROVINCE
THAILAND

Ratings:

XMS350, XMS-350: 100-240Vac nom, 47-63Hz, 5.3A rms max.
XMS500, XMS-500, XMS500P, XMS-500P, XMS500A, XMS-500A,
XMS500AP, XMS-500AP: 100-240Vac nom, 47-63Hz, 7A rms max.
(see report Model Differences for details and variations)

Additional Information:

Additionally evaluated to EN 60950-1: 2006 / A11: 2009 / A1: 2010 / A12: 2011 / A2: 2013; National Differences specified in the CB Test Report.

For class II variants

Additional information (if necessary)



- UL (US), 333 Pfinqsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2020-12-11

Signature: 
Jan-Erik Storgaard