File E227701 Vol. 1 Sec. 8 Page 1 Issued: 2005-12-05 and Report Revised: 2012-01-01

DESCRIPTION

PRODUCTS COVERED:

*USL, CNL - Switching power supplies, **Models** HWS300-5, HWS300-12, HWS300-24, HWS300-24/RY, HWS300-48.

GENERAL:

These devices are open-type switching power supplies, employing an Isolating-Type, Step-down Transformer and related circuitry enclosed within a metallic cover. These power supplies are intended for use in industrial control applications, in a pollution degree 2 environment.

ELECTRICAL RATINGS:

Electrical Ratings:

	Input, ac/dc			Output, ac/dc	
Model	V (ac)	Hz	А	V (dc)	А
HWS300-5	100-240	50/60	4.1	5	60
HWS300-12	100-240	50/60	4.1	12	27
HWS300-24	100-240	50/60	4.1	24	14
HWS300-24/RY	100-240	50/60	4.1	24	14
HWS300-48	100-240	50/60	4.1	48	7

*TECHNICAL CONSIDERATIONS (NOT FOR UL REPRESENTATIVE'S USE):

USL - Indicates Investigated To UL 508, Standard for Industrial Control

Equipment.

Note: CNL = Canadian National Standards - Listed USL = United States Standards - Listed