



TDK-Lambda

Caratteristiche del prodotto

- Approvazioni medicali IEC/EN 60601-1 (3rd Edition)
- Isolamento ingresso - uscita 4kV AC
- Corrente di dispersione a terra inferiore a 300 μ A
- Conforme ai requisiti CEC, ErP e EISA "Efficiency Level V"

Caratteristiche Principali

- Potenza 160/165 W, in base alla tensione di uscita
- Ampia tensione d'ingresso universale 90 ... 264 VAC, connettore IEC60320-C14
- Modelli singola uscita 12, 15, 19, 24, 28, 36 e 48 V DC
- Cavo di uscita con connettore 4 pin Power-DIN

Applicazioni tipiche

- Attrezzature ospedaliere, cliniche, dentali e sanitarie
- Monitoraggio
- Imaging
- Applicazioni diagnostiche

Product Highlights

- Medical approval IEC/EN 60601-1 (3rd Edition)
- Input - Output Isolation 4kV AC
- Earth leakage current less than 300 μ A
- Compliant to CEC, ErP and EISA Efficiency Level V requirements

Key Specifications

- 160/165 W, depending on output voltage
- 90...264 VAC Wide universal input voltage, IEC60320-C14 connector
- 12, 15, 19, 24, 28, 36 and 48 V DC Single Output Voltage models
- Output Cable terminated with 4-pin Power-DIN connector

Typical Applications

- Hospital, Dental, Clinical and Healthcare Equipment
- Monitoring
- Imaging
- Diagnostic applications