



Test Report issued under
the responsibility of:



TEST REPORT
IEC 60950-1
Information technology equipment - Safety -
Part 1: General requirements

Report Reference No: 4786910621-1

Date of issue: 2015-06-25

Total number of pages: 113

CB Testing Laboratory: UL Japan, Inc.

Address: 4383-326 Asama-cho, Ise-shi, Mie, 516-0021, Japan

Applicant's name: TDK-LAMBDA CORP

Address: NAGAOKA TECHNICAL CENTER

R&D DIV

2704-1 SETTAYA-MACHI

NAGAOKA-SHI

NIIGATA 940-1195 JAPAN

Test specification:

Standard: IEC 60950-1:2005 (Second Edition); Am1:2009 +
Am2:2013

Test procedure: CB Scheme

Non-standard test method: N/A

Test Report Form No.: IEC60950_1F

Test Report Form originator: SGS Fimko Ltd

Master TRF: Dated 2014-02

Copyright © 2014 Worldwide System for Conformity Testing and Certification of Electrotechnical Equipment and Components (IECEE), Geneva, Switzerland. All rights reserved.

This publication may be reproduced in whole or in part for non-commercial purposes as long as the IECEE is acknowledged as copyright owner and source of the material. IECEE takes no responsibility for and will not assume liability for damages resulting from the reader's interpretation of the reproduced material due to its placement and context.

If this test Report is used by non-IECEE members, the IECEE/IEC logo and the reference to the CB Scheme procedure shall be removed.

This report is not valid as a CB Test Report unless signed by an approved CB Testing Laboratory and appended to a CB Test Certificate issued by an NCB in accordance with IECEE 02.

General disclaimer

The test results presented in this report relate only to the object tested. This report shall not be reproduced, except in full, without the written approval of the Issuing CB Testing Laboratory. The authenticity of this Test Report and its contents can be verified by contacting the NCB, responsible for this Test Report.

Test item description	Power supply
Trade Mark	TDK·Lambda
Manufacturer	TDK-LAMBDA CORP NAGAOKA TECHNICAL CENTER R&D DIV 2704-1 SETTAYA-MACHI NAGAOKA-SHI NIIGATA 940-1195 JAPAN
Model/Type reference	ZWS30-xyz x = 3, 5, 12, 15, 24, 36 or 48. y = "/" or blank z = J, A, JA, JEZ or blank
Ratings	Input: AC 100-240V, 50/60Hz, 0.83A Output: ZWS30-3 DC 3.3V, 6.0A ZWS30-5 DC5V, 6.0A ZWS30-12 DC 12V, 2.5A ZWS30-15 DC 15V, 2.0A ZWS30-24 DC24V, 1.3A ZWS30-36 DC36V, 0.9A ZWS30-48 DC48V, 0.7A

Testing procedure and testing location:	
<input type="checkbox"/>	CB Testing Laboratory Testing location / address
<input type="checkbox"/>	Associated CB Test Laboratory Testing location / address Tested by (name + signature)..... Approved by (name + signature) ...
<input checked="" type="checkbox"/>	Testing Procedure: TMP/CTF Stage 1 Testing location / address : TDK-LAMBDA CORPORATION, NAGAOKA TECHNICAL CENTER 2704-1 SETTAYA-MACHI, NAGAOKA-SHI, NIIGATA-KEN, 940-1195 JAPAN Tested by (name + signature)..... : Masatomo Takiyama <i>M. Takiyama</i> Approved by (name + signature) ... : Tetsuo Iwasaki Tetsuo Iwasaki
<input type="checkbox"/>	Testing Procedure: WMT/CTF Stage 2 Testing location / address : Tested by (name + signature)..... : Witnessed by (name + signature).. : Approved by (name + signature) ... :
<input type="checkbox"/>	Testing Procedure: SMT/CTF Stage 3 or 4 Testing location / address : Tested by (name + signature)..... : Approved by (name + signature) ... : Supervised by (name + signature). :
<input type="checkbox"/>	Testing Procedure: RMT Testing location / address : Tested by (name + signature)..... : Approved by (name + signature) ... : Supervised by (name + signature). :

List of Attachments National Differences (19 pages) Enclosures (26 pages)
Summary Of Testing

Unless otherwise indicated, all tests were conducted at TDK-LAMBDA CORPORATION, NAGAOKA TECHNICAL CENTER, 2704-1 SETTAYA-MACHI, NAGAOKA-SHI, NIIGATA-KEN, 940-1195 JAPAN.	
Tests performed (name of test and test clause)	Testing location / Comments
Input: Single-Phase (1.6.2)	
Energy Hazard Measurements (2.1.1.5, 2.1.2, 1.2.8.10)	
Capacitance Discharge (2.1.1.7)	
SELV Reliability Test Including Hazardous Voltage Measurements (2.2.2, 2.2.3, 2.2.4)	
Humidity (2.9.1, 2.9.2, 5.2.2)	
Determination of Working Voltage; Working Voltage Measurement (2.10.2)	
Transformer and Wire /Insulation Electric Strength (2.10.5.13)	
Heating (4.5.1, 1.4.12, 1.4.13)	
Ball Pressure (4.5.5, 4.5)	
Touch Current (Single-Phase; TN/TT System) (5.1, Annex D)	
Electric Strength (5.2.2)	
Component Failure (5.3.1, 5.3.4, 5.3.7)	
Abnormal Operation (5.3.1 - 5.3.9)	
Transformer Abnormal Operation (5.3.3, 5.3.7b, Annex C.1)	
<p>Summary of Compliance with National Differences:</p> <p>Countries outside the CB Scheme membership may also accept this report.</p> <p>List of countries addressed: DE, DK, EU, FI, GB, KR, SE, SI</p> <p>The product fulfills the requirements of: EN 60950-1:2006 + A1:2010 + A11:2009 + A12:2011 + A2:2013</p>	

Copy of Marking Plate - Refer to Enclosure titled Marking Plate for copy.

Test item particulars :	
Equipment mobility	for building-in
Connection to the mains	not directly connected to the mains
Operating condition	continuous
Access location	N/A
Over voltage category (OVC)	OVC II
Mains supply tolerance (%) or absolute mains supply values	+10%, -10%
Tested for IT power systems	No
IT testing, phase-phase voltage (V)	N/A
Class of equipment	Class I (earthed)
Considered current rating of protective device as part of the building installation (A)	N/A
Pollution degree (PD)	PD 2
IP protection class	IP X0
Altitude of operation (m)	<2000 m
Altitude of test laboratory (m)	less than 1000 meters
Mass of equipment (kg)	0.3kg (approx.)
Possible test case verdicts:	
- test case does not apply to the test object	N / A
- test object does meet the requirement	P(Pass)
- test object does not meet the requirement	F(Fail)
Testing:	
Date(s) of receipt of test item	N/A
Date(s) of Performance of tests	2009-05-14 to 2009-05-22, 2011-03-29, 2012-09-21 to 2012-09-25
General remarks:	
<p>"(see Enclosure #)" refers to additional information appended to the report. "(see appended table)" refers to a table appended to the report.</p> <p>Throughout this report a point is used as the decimal separator.</p>	
Manufacturer's Declaration per Sub Clause 4.2.5 of IEC60950 02:	
The application for obtaining a CB Test Certificate includes more than one factory and a declaration from the Manufacturer stating that the sample(s) submitted for evaluation is (are) representative of the products from each factory has been provided	Yes

When differences exist, they shall be identified in the General Product Information section.

Name and address of Factory(ies):	<p>TDK-LAMBDA CORP NAGAOKA TECHNICAL CENTER R&D DIV 2704-1 SETTAYA-MACHI NAGAOKA-SHI NIIGATA 940-1195 JAPAN</p> <p>TDK-LAMBDA MALAYSIA SDN BHD PLO33 KAWASAN PERINDUSTRIAN SENAI 81400 SENAI MALAYSIA</p> <p>TDK-LAMBDA MALAYSIA SDN BHD LOT 2 & 3, BATU 9 3/4 KAWASAN PERINDUSTRIAN BANDAR BARU JAYA GADING 26070 KUANTAN MALAYSIA</p> <p>WUXI TDK-LAMBDA ELECTRONICS CO LTD NO 6 XING CHUANG ER LU WUXI JIANGSU 214028 CHINA</p> <p>ZHANGJIAGANG HUA YANG ELECTRONICS CO LTD TONGXIN RD ZHAOFENG ECONOMIC DEVELOPMENT ZONE LEYU TOWN ZHANGJIAGANG JIANGSU 215622 CHINA</p> <p>SENDAN ELECTRONICS MFG CO LTD 1010 HABUSHIN NANTO-SHI TOYAMA-KEN 939-1756 JAPAN</p> <p>ALPS LOGISTICS FACILITIES CO LTD 593-1 NISHIOHASHI TSUKUBA-SHI IBARAKI-KEN 305-0831 JAPAN</p>
--	--

GENERAL PRODUCT INFORMATION:**Report Summary**

All applicable tests according to the referenced standard(s) have been carried out.

Product Description

The product is a switching power supply intended for building in to an ITE end product.

Output:

ZWS30-3 DC 3.3V, 6.0A

ZWS30-5 DC5V, 6.0A

ZWS30-12 DC 12V, 2.5A

ZWS30-15 DC 15V, 2.0A

ZWS30-24 DC24V, 1.3A

ZWS30-36 DC36V, 0.9A

ZWS30-48 DC48V, 0.7A

Model Differences

Each model is identical, except for model designation, output voltage, transformer (turns of secondary windings)

ZWS30 series maybe followed by suffix "xyz"

x = 3, 5, 12, 15, 24, 36 or 48.

y = "/" or blank

z = J, A, JA, JEZ or blank

J: denotes type of input and output connector, manufactured by Japan Solderless Terminal Mfg., Co., Ltd. See table 1.5.1.

A: denotes models with optional cover and chassis provided

JA: denotes combination of suffix "/A" and "/J"

JEZ: denotes models that are identical to the original models with components differences:

- Electrolytic Capacitor (C2): rating 420V, 120 μ F, 105°C
- Y-Capacitor (C4): not provided
- Y-Capacitor (C20): manufactured by Murata Mfg. Co., Ltd. type KH, rating 250Vac, 3300pF

Additional Information

This report is a reissue of CBTR Ref. No.: 12028144 001, CB Test Certificate Ref. No.JPTUV-046543. Based on the previously conducted testing and the review of product technical documentation including photos, schematics, wiring diagrams and similar, has been determined that the product continues to comply with the standard.

Sample Received date is 2012-09-27.

Construction review was conducted on 2012-10-01.

Abbreviations used in the report.

- built-in application: B/I

Technical Considerations

- The product was submitted and evaluated for use at the maximum ambient temperature (Tma) permitted by the manufacturer’s specification of: 50°C (100% Load), 60°C (70% Load) without optional cover and chassis, 40°C (100% Load), 50°C (70% Load) with optional cover and chassis
- The product is intended for use on the following power systems: TN
- The product was investigated to the following additional standards: EN 60950-1:2006 + A11:2009 + A1:2010 + A12:2011 + A2:2013 (which includes all European national differences, including those specified in this test report).

Engineering Conditions of Acceptability

When installed in an end-product, consideration must be given to the following:

- The end-product Electric Strength Test is to be based upon a maximum working voltage of: max working voltage: 279 Vrms, 517 Vpk
- The following secondary output circuits are SELV: All output
- The following secondary output circuits are at non-hazardous energy levels: All output
- The power supply terminals and/or connectors are: Suitable for factory wiring only
- The maximum investigated branch circuit rating is: 16 A
- The investigated Pollution Degree is: 2
- Proper bonding to the end-product main protective earthing termination is: Required
- An investigation of the protective bonding terminals has: Not been conducted
- The following magnetic devices (e.g. transformers or inductor) are provided with an OBJ2 insulation system with the indicated rating greater than Class A (105°C): T1 (Class B)
- The following end-product enclosures are required: Fire, Electrical

Abbreviations used in the report:

- normal condition	N.C.	- single fault condition	S.F.C
- operational insulation	OP	- basic insulation	BI
- basic insulation between parts of opposite		- supplementary insulation	SI

polarity:	BOP	
- double insulation	DI	- reinforced insulation RI
Indicate used abbreviations (if any)		