

CB TEST CERTIFICATE CERTIFICAT D'ESSAI OC

Product
ProduitName and address of the applicant
Nom et adresse du demandeurName and address of the manufacturer
Nom et adresse du fabricantName and address of the factory
Nom et adresse de l'usineNote: When more than one factory, please report
on page 2

Note: Lorsque il y plus d'une usine, veuillez utiliser la deuxième page

Ratings and principal characteristics
Valeurs nominales et caractéristiques principalesTrademark (if any)
Marque de fabrique (si elle existe)Model / Type Ref.
Ref. De typeAdditional information (if necessary may also be
reported on page 2)
Les informations complémentaires (si nécessaire,
peuvent être indiqués sur la deuxième pageA sample of the product was tested and found
to be in conformity with
Un échantillon de ce produit a été essayé et a été
considéré conforme à laAs shown in the Test Report Ref. No. which forms part
of this Certificate
Comme indiqué dans le Rapport de tests numéro de
référence qui constitue partie de ce Certificat

DC/DC Converter

TDK-Lambda Corp.

2701 Togawa, Settaya, Nagaoka-Shi, Niigata 940-1195
Japan

TDK-Lambda Corp.

2701 Togawa, Settaya, Nagaoka-Shi, Niigata 940-1195
Japan

TDK Yuri-Honjo Corporation, Head Office / Honjo Factory

16-57 Aza-Yamanokami, Ishiwaki, Yuri-Honjo-Shi, Akita-Ken 015-0014
Japan Additional information on page 21.90A 18-36V (for models CC30-24.....-E) or 0,92A 36-76V (for models
CC30-48.....-E)

DC/DC Converter, for building-in, DC-output: Please see page 2

The first dot "." in model name can be 24 or 48 denoting input voltage. 2nd
dot can be 03, 3R3, 3.3, 05, 5R0, 5.0, 12, 12R, 15 or 15R denoting output
voltage. 3rd dot can be S denoting numbers of output. 4th dot can be F or
R denoting terminal construction. 5th dot can be P or H denoting with or
without case. The last dot can be A to Z or blank for customers
identification

CC30-.....-E

 Additional information on page 2

IEC 60950-1(ed.2)

112817

This CB Test Certificate is issued by the National Certification Body
Ce Certificat de test OC est établi par l'Organisme National de CertificationGautstadalleen 30
NO-0373 Oslo, Norway*Knut Mathisen*

Date: 14-09-2009

Signature: Knut Mathisen
Certification Department

Additional information (if necessary)**Information complémentaire (si nécessaire)****Model names with output rating:**

For Models CC30-24.....-E

CC30-2403SFP-E: 3.3Vdc 9.00A 29.70W
CC30-2405SFP-E: 5.0Vdc 6.00A 30.00W
CC30-2412SFP-E: 12.0Vdc 2.50A 30.00W
CC30-2415SFP-E: 15.0Vdc 2.00A 30.00W
CC30-2403SRP-E: 3.3Vdc 9.00A 29.70W
CC30-2405SRP-E: 5.0Vdc 6.00A 30.00W
CC30-2412SRP-E: 12.0Vdc 2.50A 30.00W
CC30-2415SRP-E: 15.0Vdc 2.00A 30.00W
CC30-2403SFH-E: 3.3Vdc 9.00A 29.70W
CC30-2405SFH-E: 5.0Vdc 6.00A 30.00W
CC30-2412SFH-E: 12.0Vdc 2.50A 30.00W
CC30-2415SFH-E: 15.0Vdc 2.00A 30.00W
CC30-2403SRH-E: 3.3Vdc 9.00A 29.70W
CC30-2405SRH-E: 5.0Vdc 6.00A 30.00W
CC30-2412SRH-E: 12.0Vdc 2.50A 30.00W
CC30-2415SRH-E: 15.0Vdc 2.00A 30.00W

For Models CC30-48.....-E

CC30-4803SFP-E: 3.3Vdc 9.00A 29.70W
CC30-4805SFP-E: 5.0Vdc 6.00A 30.00W
CC30-4812SFP-E: 12.0Vdc 2.50A 30.00W
CC30-4815SFP-E: 15.0Vdc 2.00A 30.00W
CC30-4803SRP-E: 3.3Vdc 9.00A 29.70W
CC30-4805SRP-E: 5.0Vdc 6.00A 30.00W
CC30-4812SRP-E: 12.0Vdc 2.50A 30.00W
CC30-4815SRP-E: 15.0Vdc 2.00A 30.00W
CC30-4803SFH-E: 3.3Vdc 9.00A 29.70W
CC30-4805SFH-E: 5.0Vdc 6.00A 30.00W
CC30-4812SFH-E: 12.0Vdc 2.50A 30.00W
CC30-4815SFH-E: 15.0Vdc 2.00A 30.00W
CC30-4803SRH-E: 3.3Vdc 9.00A 29.70W
CC30-4805SRH-E: 5.0Vdc 6.00A 30.00W
CC30-4812SRH-E: 12.0Vdc 2.50A 30.00W
CC30-4815SRH-E: 15.0Vdc 2.00A 30.00W



Gaustadalléen 30
NO-0373 Oslo, Norway

Date: 14-09-2009**Signature:** Knut Mathisen
Certification Department

CB TEST CERTIFICATE CERTIFICAT D'ESSAI OC

Product
ProduitName and address of the applicant
Nom et adresse du demandeurName and address of the manufacturer
Nom et adresse du fabricantName and address of the factory
Nom et adresse de l'usineNote: When more than one factory, please report
on page 2

Note: Lorsque il y plus d'une usine, veuillez utiliser la deuxième page

Ratings and principal characteristics
Valeurs nominales et caractéristiques principalesTrademark (if any)
Marque de fabrique (si elle existe)Model / Type Ref.
Ref. De typeAdditional information (if necessary may also be
reported on page 2)
Les informations complémentaires (si nécessaire,
peuvent être indiqués sur la deuxième pageA sample of the product was tested and found
to be in conformity with
Un échantillon de ce produit a été essayé et a été
considéré conforme à laAs shown in the Test Report Ref. No. which forms part
of this Certificate
Comme indiqué dans le Rapport desais numéro de
référence qui constitue partie de ce CertificatThis CB Test Certificate is issued by the National Certification Body
Ce Certificat desais OC est établi par l'Organisme National de Certification

DC/DC Converter

TDK-Lambda Corp.

2701 Togawa, Settaya, Nagaoka-Shi, Niigata 940-1195
Japan

TDK-Lambda Corp.

2701 Togawa, Settaya, Nagaoka-Shi, Niigata 940-1195
JapanTDK Yuri-Honjo Corporation, Head Office / Honjo Factory
16-57 Aza-Yamanokami, Ishiwaki, Yuri-Honjo-Shi, Akita-Ken 015-0014
Japan Additional information on page 21.90A 18-36V (for models CC30-24.....-E) or 0.92A 36-76V (for models
CC30-48.....-E)

DC/DC Converter, building-in. DC-ratings see tables page 2.

The first dot "." in model name can be 24 or 48 denoting input voltage. 2nd
dot can be 03, 3R3, 3.3, 05, 5R0, 5.0, 12, 12R, 15 or 15R denoting output
voltage. 3rd dot can be S denoting numbers of output. 4th dot can be F or
R denoting terminal construction. 5th dot can be P or H denoting with or
without case. The last dot can be A to Z or blank for customers
identification**TDK-Lambda**

CC30-.....-E

 Additional information on page 2

IEC 60950-1(ed.2)

112817

NemkoGaustadalléen 30
NO-0373 Oslo, Norway*Knut Mathisen*

Date: 14-09-2009

Signature: Knut Mathisen
Certification Department

Additional information (if necessary)

Information complémentaire (si nécessaire)

Model names with output rating:

For Models CC30-24.....-E

CC30-2403SFP-E: 3.3Vdc 9.00A 29.70W
CC30-2405SFP-E: 5.0Vdc 6.00A 30.00W
CC30-2412SFP-E: 12.0Vdc 2.50A 30.00W
CC30-2415SFP-E: 15.0Vdc 2.00A 30.00W
CC30-2403SRP-E: 3.3Vdc 9.00A 29.70W
CC30-2405SRP-E: 5.0Vdc 6.00A 30.00W
CC30-2412SRP-E: 12.0Vdc 2.50A 30.00W
CC30-2415SRP-E: 15.0Vdc 2.00A 30.00W
CC30-2403SFH-E: 3.3Vdc 9.00A 29.70W
CC30-2405SFH-E: 5.0Vdc 6.00A 30.00W
CC30-2412SFH-E: 12.0Vdc 2.50A 30.00W
CC30-2415SFH-E: 15.0Vdc 2.00A 30.00W
CC30-2403SRH-E: 3.3Vdc 9.00A 29.70W
CC30-2405SRH-E: 5.0Vdc 6.00A 30.00W
CC30-2412SRH-E: 12.0Vdc 2.50A 30.00W
CC30-2415SRH-E: 15.0Vdc 2.00A 30.00W

For Models CC30-48.....-E

CC30-4803SFP-E: 3.3Vdc 9.00A 29.70W
CC30-4805SFP-E: 5.0Vdc 6.00A 30.00W
CC30-4812SFP-E: 12.0Vdc 2.50A 30.00W
CC30-4815SFP-E: 15.0Vdc 2.00A 30.00W
CC30-4803SRP-E: 3.3Vdc 9.00A 29.70W
CC30-4805SRP-E: 5.0Vdc 6.00A 30.00W
CC30-4812SRP-E: 12.0Vdc 2.50A 30.00W
CC30-4815SRP-E: 15.0Vdc 2.00A 30.00W
CC30-4803SFH-E: 3.3Vdc 9.00A 29.70W
CC30-4805SFH-E: 5.0Vdc 6.00A 30.00W
CC30-4812SFH-E: 12.0Vdc 2.50A 30.00W
CC30-4815SFH-E: 15.0Vdc 2.00A 30.00W
CC30-4803SRH-E: 3.3Vdc 9.00A 29.70W
CC30-4805SRH-E: 5.0Vdc 6.00A 30.00W
CC30-4812SRH-E: 12.0Vdc 2.50A 30.00W
CC30-4815SRH-E: 15.0Vdc 2.00A 30.00W



Gaustadalléen 30
NO-0373 Oslo, Norway

Date: 14-09-2009**Signature:** Knut Mathisen
Certification Department