

Certificate



Certificate no.

T 72201183 01

License Holder:

TDK-Lambda Ltd.
Karmiel Industrial Zone
56 Haharoshet St., P.O.B. 500
2161401 Karmiel
Israel

Manufacturing Plant:

TDK-Lambda Ltd.
Karmiel Industrial Zone
56 Haharoshet St., P.O.B. 500
2161401 Karmiel
Israel

Test report no.: USA-PM 31781623 302

Client Reference: Boris Gorinshtein

Tested to: IEC 61010-1:2010+A1
EN 61010-1:2010+A1

Certified Product: Programmable Power Supply

License Fee - Units

Model Designation: see CDF (Constr. Data form)

7

Rated Voltage:

1), 2), 3), 6), 7) Option 1: AC 190-240V; 3W + PE, 50/60Hz;
1), 2), 3), 6), 7) Option 2: AC 380-415V; 3W + PE, 50/60Hz;
1), 2), 3), 6), 7) Option 3: AC 380-480V; 3W + PE, 50/60Hz;
4), 5), 8), 9) Option 4: AC 100-240V; 50/60Hz;
6), 7) Option 5: AC 190-240V; 50/60Hz

contd.

7

Appendix: 1, 1-83

Licensed Test mark:



Date of Issue
(day/mo/yr)

15/06/2020

Certificate



Certificate no.

T 72201183 02

License Holder:

TDK-Lambda Ltd.
Karmiel Industrial Zone
56 Haharoshet St., P.O.B. 500
2161401 Karmiel
Israel

Manufacturing Plant:

TDK-Lambda Ltd.
Karmiel Industrial Zone
56 Haharoshet St., P.O.B. 500
2161401 Karmiel
Israel

Test report no.: USA-PM 31781623 302

Client Reference: Boris Gorinshtein

Tested to: IEC 61010-1:2010+A1
EN 61010-1:2010+A1

Certified Product: Programmable Power Supply

License Fee - Units

contd.

Rated Current:

Option 1: 1) 18.5A max., 2) 37A max., 3) 55.5A max.,
6) 10A max., 7) 12.5A max.;
Option 2,3: 1) 9.2A max., 2) 18.4A max., 3) 27.6A max.,
6) 5.5A max., 7) 6.5A max.;
Option 4: 4) 20A max., 5) 18.5A max., 8),9) 12.5A max.;
Option 5: 6) 16.5A max., 7) 21A max.
Protection Class: I

contd.

Licensed Test mark:



Date of Issue
(day/mo/yr)

15/06/2020

Certificate



Certificate no.

T 72201183 03

License Holder:

TDK-Lambda Ltd.
Karmiel Industrial Zone
56 Haharoshet St., P.O.B. 500
2161401 Karmiel
Israel

Manufacturing Plant:

TDK-Lambda Ltd.
Karmiel Industrial Zone
56 Haharoshet St., P.O.B. 500
2161401 Karmiel
Israel

Test report no.: USA-PM 31781623 302

Client Reference: Boris Gorinshtein

Tested to: IEC 61010-1:2010+A1
EN 61010-1:2010+A1

Certified Product: Programmable Power Supply

License Fee - Units

contd.

Output Ratings DC:

- 1) 0-10V/500A to 0-600V/8.5A, 5200W max.
- 2) 0-10V/1000A to 0-600V/17A, 10400W max.
- 3) 0-10V/1500A to 0-600V/25.5A, 15600W max.
- 4) 0-10V/170A to 0-600V/2.8A, 1700W max.
- 5) 0-10V/150A to 0-600V/2.6A, 1560W max..
- 6) 0-10V/265A to 0-600V/4.5A, 2720W max..
- 7) 0-10V/340A to 0-600V/5.6A, 3450W max.
- 8), 9) 0-10V/100A to 0-600V/1.7A, 1050W max.

Special Remarks: Solely assessed to standards listed above.

Licensed Test mark:



Date of Issue
(day/mo/yr)

15/06/2020