



Ref. Certif. No.

US-TUVR-8430

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST
CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)
CB SCHEME

SYSTEME CEI D' ACCEPTATION MUTUELLE DE
CERTIFICATS D'ESSAIS DES EQUIPEMENTS
ELECTRIQUES (IECEE) METHODE OC

CB TEST CERTIFICATE

CERTIFICAT D'ESSAI OC

Product
Produit

Programmable Power Supply

Name and address of the applicant
Nom et adresse du demandeur

TDK-Lambda Ltd.
Karmiel Industrial Zone
56 Haharoshet St., P.O.B. 500
Karmiel 2161401 ISRAEL

Name and address of the manufacturer
Nom et adresse du fabricant

same as applicant

Name and address of the factory
Nom et adresse de l'usine

same as applicant

Note: When more than one factory, please report on page 2
Note: Lorsque il y plus d'une usine, veuillez utiliser la 2^{ème} page

Ratings and principal characteristics
Valeurs nominales et caractéristiques principales

Additional Information, see page 2

Trademark (if any)
Marque de fabrique (si elle existe)

TDK-Lambda

Model / Type Ref.
Ref. De Type

Additional Information, see page 2

Additional information (if necessary, may also be reported on page 2)
Les informations complémentaires (si nécessaire, peuvent être indiqués sur la 2^{ème} page)

Complies with requirements as well as group and national differences where applicable for CA, CH and US. Replaces Certificate US-TUVR-7420. (SMT)

A sample of the product was tested and found to be in conformity with IEC
Un échantillon de ce produit a été essayé et a été considéré conforme à la CEI


IEC 61010-1

3rd Edition (2010)

As shown in the Test Report Ref. No. which forms part of this Certificate
Comme indiqué dans le Rapport d'essais numéro de référence qui constitue partie de ce Certificat

31183682.011

This CB Test Certificate is issued by the National Certification Body
Ce Certificat d'essai OC est établi par l'Organisme **National de Certification**



Date: May 30, 2014

Page 1 of 2

Signature:

Martin Glagla
Martin Glagla

Additional Information:**Model / Type Ref.:**

- 1) Z200 series: Zxxx-yyy-o-p,
- 2) Z400 series: Zxxx-yyy-o-p,
- 3) Z600 series: Zxxx-yyy-o-p,
- 4) Z800 series: Zxxx-yyy-o-p

(xxx = 010-650; yyy = 0.32-72;
o = blank, L, L2, IEEE, IS420, IS510, LAN;
p = blank, E, I, U)

Ratings and principal characteristics:

AC 100-240V, 50/60Hz
1) 3A; 2) 6A; 3) 9A; 4) 12A

Class I

Output Ratings:

- 1) DC 0-10V/0-20A to DC 0-650V/0-0.32A; 220W max.;
- 2) DC 0-10V/0-40A to DC 0-650V/0-0.64A; 432W max.;
- 3) DC 0-10V/0-60A to DC 0-650V/0-1A; 682W max.;
- 4) DC 0-10V/0-72A to DC 0-650V/0-1.25A; 864W max.

This CB Test Certificate is issued by the National Certification body
Ce Certificat d'essai OC est établi par l'Organisme National de Certification



TÜVRheinland®
Precisely Right.

May 30, 2014

Date:

Page 2 of 2

Signature:


Martin Glagla