



Test Report issued under the responsibility of:



TEST REPORT
IEC 60950-1
Information technology equipment – Safety –
Part 1: General requirements

Report Number: 210282-CI3-2 CB DE1- 56459
Date of issue: 2015-11-19
Total number of pages..... 160

Applicant's name.....: TDK-Lambda Americas Inc.
Address: 3320 Matrix Drive; Suite 100; RICHARDSON TX 75082; USA

Test specification:

Standard: IEC 60950-1:2005 (Second Edition) + Am 1:2009 + Am 2:2013
Test procedure: VDE, CB Scheme
Non-standard test method.....: DIN EN 60950-1 (VDE 0805-1):2014-08
EN 60950-1:2006 +A11:2009 +A1:2010 +A12:2011+A2:2013

Test Report Form No.....: IEC60950_1F
Test Report Form(s) Originator.....: SGS Fimko Ltd
Master TRF: Dated 2014-02

Copyright © 2014 IEC System of Conformity Assessment Schemes for Electrotechnical Equipment and Components (IECEE System). All rights reserved.


This publication may be reproduced in whole or in part for non-commercial purposes as long as the IECEE is acknowledged as copyright owner and source of the material. IECEE takes no responsibility for and will not assume liability for damages resulting from the reader's interpretation of the reproduced material due to its placement and context.




If this Test Report Form is used by non-IECEE members, the IECEE/IEC logo and the reference to the CB Scheme procedure shall be removed.

This report is not valid as a CB Test Report unless signed by an approved CB Testing Laboratory and appended to a CB Test Certificate issued by an NCB in accordance with IECEE 02.

General disclaimer:

The test results presented in this report relate only to the object tested.
This report shall not be reproduced, except in full, without the written approval of the Issuing CB Testing Laboratory. The authenticity of this Test Report and its contents can be verified by contacting the NCB, responsible for this Test Report.

Test item description :	Power supply for IT-Equipment / DC/DC-Converter
Trade Mark :	 and/or TDK-Lambda
Manufacturer	TDK-Lambda Americas Inc.; 3320 Matrix Drive; Suite 100; RICHARDSON TX 75082; USA
Model/Type reference	iAD series (see model matrix – Appendix 3)
Ratings	The DC-DC Converters are not internally fused. An external input line normal blow fuse with a max. value of 30 A is required.
10003893 Rated voltage.....:	DC 6 V– 14 V (SELV)
10004017 Rated current.....:	max. 18 A
10003951 Output voltages and currents.....:	DC 0.8 – 5.5 V, max. 16 A, max. 80 W
10004092 Max. ambient temperature...:	Max. 105 °C at Q1
Supplementary information:	
The above listing was introduced only for internal VDE administration process.	

Testing procedure and testing location:		
<input checked="" type="checkbox"/>	CB Testing Laboratory:	VDE Prüf- und Zertifizierungsinstitut GmbH VDE <i>Testing and Certification Institute</i>
Testing location/ address.....:		Merianstrasse 28, D-63069 Offenbach, Germany
<input type="checkbox"/>	Associated CB Testing Laboratory:	
Testing location/ address.....:		
Tested by (name + signature).....:		(authorization of test report)
Approved by (name + signature).....:		
<hr/>		
<input type="checkbox"/>	Testing procedure: TMP/CTF Stage 1:	
Testing location/ address.....:		
Tested by (name + signature).....:		(authorization of test report)
Approved by (name + signature).....:		
<hr/>		
<input checked="" type="checkbox"/>	Testing procedure: WMT/CTF Stage 2:	
Testing location/ address.....:		TDK Innoveta Inc. 3320 Matrix Drive, Suite 100, Richardson, Texas 75082, USA CTF Stage 2 (TDAP under File No. 2520400-9501-0001)
Tested by (name + signature).....:		Steve McKitrick 
Witnessed by (name + signature).....:		Thomas Dankesreiter (authorization of test report) 
Approved by (name + signature).....:		Holger Kreuzer 
<hr/>		
<input type="checkbox"/>	Testing procedure: SMT/CTF Stage 3 or 4:	
Testing location/ address.....:		
Tested by (name + signature).....:		
Witnessed by (name + signature).....:		
Approved by (name + signature).....:		
Supervised by (name + signature).....:		

List of Attachments (including a total number of pages in each attachment):		
Appendix No.	Description	Page(s)
1	Photos	148
2	Rating Label	149
3	Model martrix	150
4	Schematics	151
5	Layout	152 – 158
6	Data sheet	159 – 160
Summary of testing:		
Tests performed (name of test and test clause):		Testing location:
1.5 Components 1.6 Power interface 1.7 Marking and instructions 2.2 SELV circuits 2.9 Electrical insulation 2.10 Clearances, creepage distances and distances through insulation 4.1 Stability 4.2 Mechanical strength 4.3 Design and construction 4.5 Thermal requirements 4.7 Resistance to fire 5.2 Electric strength 5.3 Abnormal operating and fault conditions Tests were done under VDE File 2520400-3336-0021		TDK Innoveta Inc. 3320 Matrix Drive, Suite 100, Richardson, Texas 75082, USA WMT / CTF Stage 2 (TDAP under File No. 2520400-9501-0001)

Summary of compliance with National Differences:				
List of countries addressed				
The product has been tested according to standard IEC 60950-1:2005 (2 nd Edition); am1:2009; am2:2013 / EN 60950-1:2006; A11:2009; A1:2010; A12:2011; A2:2013 and those deviations taken into account of				
<input checked="" type="checkbox"/> CENELEC common modifications	<input checked="" type="checkbox"/> United Kingdom	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>
<input checked="" type="checkbox"/> Finland	<input checked="" type="checkbox"/> Denmark	<input checked="" type="checkbox"/> Ireland	<input type="checkbox"/>	<input type="checkbox"/>
<input checked="" type="checkbox"/> Sweden	<input checked="" type="checkbox"/> Germany	<input checked="" type="checkbox"/> Spain	<input type="checkbox"/>	<input type="checkbox"/>
<input checked="" type="checkbox"/> Norway	<input checked="" type="checkbox"/> Switzerland	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>
<input checked="" type="checkbox"/> CB Bull. NATIONAL DIFFERENCES IEC 60950-1:2005 (2nd Edition)				
<input checked="" type="checkbox"/> Switzerland	<input checked="" type="checkbox"/> Finland	<input checked="" type="checkbox"/> Norway	<input checked="" type="checkbox"/> USA	<input checked="" type="checkbox"/> Japan
<input checked="" type="checkbox"/> Germany	<input checked="" type="checkbox"/> United Kingdom	<input checked="" type="checkbox"/> Sweden	<input checked="" type="checkbox"/> Israel	<input type="checkbox"/>
<input checked="" type="checkbox"/> Denmark	<input checked="" type="checkbox"/> Ireland	<input checked="" type="checkbox"/> Group Differences	<input checked="" type="checkbox"/> Australia	<input type="checkbox"/>
<input checked="" type="checkbox"/> Spain	<input checked="" type="checkbox"/> Korea	<input checked="" type="checkbox"/> Canada	<input checked="" type="checkbox"/> New Zealand	<input type="checkbox"/>
<input checked="" type="checkbox"/> The product fulfils the requirements of DIN EN 60950-1 (VDE 0805-1):2014-08 EN 60950-1:2006 +A11:2009 +A1:2010 +A12:2011+A2:2013 IEC 60950-1:2005 (Second Edition) + Am 1:2009 + Am 2:2013				

Copy of marking plate:

The artwork below may be only a draft. The use of certification marks on a product must be authorized by the respective NCBs that own these marks.

Refer to Appendix 2 of report

The label includes: Optional "-R" appended to product code to indicate ROHS compliance.

Test item particulars:	
Equipment mobility:	<input type="checkbox"/> movable <input type="checkbox"/> hand-held <input type="checkbox"/> transportable <input type="checkbox"/> stationary <input checked="" type="checkbox"/> for building-in <input type="checkbox"/> direct plug-in
Connection to the mains:	<input type="checkbox"/> pluggable equipment <input type="checkbox"/> type A <input type="checkbox"/> type B <input type="checkbox"/> permanent connection <input type="checkbox"/> detachable power supply cord <input type="checkbox"/> non-detachable power supply cord <input checked="" type="checkbox"/> not directly connected to the mains
Operating condition:	<input checked="" type="checkbox"/> continuous <input type="checkbox"/> rated operating / resting time:
Access location	<input type="checkbox"/> operator accessible <input type="checkbox"/> restricted access location <input checked="" type="checkbox"/> to be determined in the end use equipment
Over voltage category (OVC)	<input type="checkbox"/> OVC I <input type="checkbox"/> OVC II <input type="checkbox"/> OVC III <input type="checkbox"/> OVC IV <input checked="" type="checkbox"/> other: DC supplied
Mains supply tolerance (%) or absolute mains supply values	N/A; not directly connected to the mains. see page 2 for input voltage range.
Tested for IT power systems	<input type="checkbox"/> Yes <input checked="" type="checkbox"/> No
IT testing, phase-phase voltage (V)	N/A
Class of equipment	<input type="checkbox"/> Class I <input type="checkbox"/> Class II <input type="checkbox"/> Class III <input checked="" type="checkbox"/> Not classified
Considered current rating of protective device as part of the building installation (A)	N/A
Pollution degree (PD)	<input type="checkbox"/> PD 1 <input checked="" type="checkbox"/> PD 2 <input type="checkbox"/> PD 3
IP protection class	N/A
Altitude during operation (m)	≤ 2000 m
Altitude of test laboratory (m)	app. 179 m
Mass of equipment (kg)	< 18 kg

Possible test case verdicts:	
- test case does not apply to the test object.....:	N/A
- test object does meet the requirement.....:	P (Pass)
- test object does not meet the requirement.....:	F (Fail)
Testing:	
Date of receipt of test item	2015-11-10
Date (s) of performance of tests	2015-11-10 (visible check)
General remarks:	
"(See Enclosure #)" refers to additional information appended to the report. "(See appended table)" refers to a table appended to the report.	
Throughout this report a <input type="checkbox"/> comma / <input checked="" type="checkbox"/> point is used as the decimal separator.	

Manufacturer's Declaration per sub-clause 4.2.5 of IEC60950-1:	
The application for obtaining a CB Test Certificate includes more than one factory location and a declaration from the Manufacturer stating that the sample(s) submitted for evaluation is (are) representative of the products from each factory has been provided	<input checked="" type="checkbox"/> Yes <input type="checkbox"/> Not applicable
When differences exist; they shall be identified in the General product information section.	
Name and address of factory (ies)	TDK-Lambda Americas Inc.; 3320 Matrix Drive Suite 100; RICHARDSON TX 75082; USA / Reference 30014661 TDK-Lambda Malaysia Sdn. Bhd.; PLO 33 Kawasan Perindustrian Senai Locked Bag No. 110; 81400 SENAI, JOHOR; Johor; Malaysia / Reference 30017287

General product information:**The label includes:**

Optional "-R" appended to product code to indicate ROHS compliance. eg. iADXXXXXXXXXX-### -R Series

Product Overview:

The Metamere product iAD series are DC-DC power modules intended to be purchased and used as a component in an end-user's power system. The modules currently come in two input voltage ranges; a wide range 6-14 Vdc input, and a narrow range of 9-14Vdc input. The output voltage be adjustable by the customer over a range of 0.75V to 5.5V. The rated output current will be up to 16A. The rated output power will be maximum 80W. (See Appendix 1 for details)

Product Similarities

The design intention is that the modules within a platform consist of a family of units with similar output voltage and current with the exception of the feature option. The major differences between the modules will be as follows.

Remote on/off circuits C17, R12, R13 used in Positive Logic feature design only, C17, R12, R13 used in Negative Logic feature design only.

Sequence circuits IC2, CR2, C19, C24, R6, R18, R20, R21 used in Sequence feature design only.

The manufacturer specified max. Temperature: 125°C at Q1

The Electrical and Fire Enclosures are to be provided by the end product.

The DC-DC Converter series provides functional insulation, between input and output.

Operating Conditions:

If the input meets all requirements for SELV, then the output may be considered SELV


The DC-DC Converters are not internally fused. An external input line normal blow fuse with a max. value of 30 A is required.

Tests were done under VDE File 2520400-3336-0021

Abbreviations used in the report:

- normal conditions	N.C.	- single fault conditions	S.F.C
- functional insulation	OP	- basic insulation	BI
- double insulation	DI	- supplementary insulation	SI
- between parts of opposite polarity	BOP	- reinforced insulation	RI

Indicate used abbreviations (if any)

Information to test report reference No. :	210282-CI3-2		
VDE Test- and Certification Institute GmbH Merianstrasse 28 D - 63069 Offenbach	DIN EN 60950-1 (VDE 0805-1):2014-08 EN 60950-1:2006 +A11:2009 +A1:2010 +A12:2011+A2:2013 IEC 60950-1:2005 (Second Edition) + Am 1:2009 + Am 2:2013		
Test item description:	Power supply for IT-Equipment / DC/DC-Converter		
Made by :	TDK-Lambda Americas Inc.; 3320 Matrix Drive; Suite 100; RICHARDSON TX 75082; USA		
Trade mark :	 and/or TDK-Lambda		
Model/type ref. :	iAD-Series		
Rated :	Input: DC 6 V– 14 V (SELV), max. 18 A Output: DC 0.8 – 5.5 V, max. 16 A, max. 80 W (see model matrix Appendix 3)		
Commission received from	Steve.Mc Kitrick	Date:	2015-10-08
Modification on the appliance:			
1.	DIN EN 60950-1 (VDE 0805-1):2014-08 EN 60950-1:2006 +A11:2009 +A1:2010 +A12:2011+A2:2013 IEC 60950-1:2005 (Second Edition) + Am 1:2009 + Am 2:2013		

Test Report History:			
Date: (jjjj-mm-dd)	VDE-Certificate: CB-Ref. No.:	VDE File No.: Test Report Number	Modifications:
2015-11-19	40022607 DE1-56459	2520400-3336-0021 210282-CI3-2	Origin Test Report DC / DC converters iAD-Series