



TDK-Lambda Germany GmbH
Karl-Bold-Str. 40
D-77855 Achern, Germany
Tel: +49 (0) 7841 6660
Fax: +49 (0) 7841 5000

EU DECLARATION OF CONFORMITY

CSS & CSA series

We, TDK-Lambda Germany GmbH, of Karl-Bold-Str. 40, 77855 Achern, Germany, declare under our sole responsibility that the TDK-Lambda power supplies, as detailed on the attached products covered sheets, complies with the provisions of the following European Directives and is eligible to bear the CE mark:

| | |
|-------------|---|
| Low Voltage | Directive 2014/35/EU |
| EMC | Directive 2014/30/EU |
| RoHS 10 | Directive 2011/65/EU (as amended by 2015/863) |

Assurance of conformance of the described product with the provisions of the stated EC Directive is given through compliance to the following standards:

| | |
|-------------------------------------|---|
| Electrical Safety (LVD) | EN 60950-1:2006 + A2:2013 |
| Electromagnetic Compatibility (EMC) | EN 61000-6-1:2007 EN 55024:2010 EN 55011:2015 |

Note: The EMC performance of a component power supply will be affected by the final installation, compliance to the stated EMC standards and conformance to the EMC Directive must be confirmed after installation by the final equipment manufacturer. For guidance with respect to test conditions please visit our website at 'emea.tdk-lambda.com/EMC_guidance' or contact your local TDK-Lambda sales office.

| | |
|------------------------------------|--|
| Name of Authorized Signatory: | Christopher Haas |
| Signature of Authorized Signatory: |  |
| Position of Authorized Signatory: | Head of Quality & Compliance, TDK-Lambda Germany GmbH |
| Date: | 14 th August 2019 |
| Date when first CE marked: | 4 th November 2010 |
| Place where signed: | Achern, Germany |

The products covered by this declaration are:

CSS65-5, CSS65-12, CSS65-15, CSS65-19, CSS65-24, CSS65-36 and CSS65-48

CSS65A-5, CSS65A-12, CSS65A-15, CSS65A-19, CSS65A-24, CSS65A-28, CSS65A-48 and CSS65A-54

CSS150-12, CSS150-15, CSS150-24, CSS150-28, CSS150-36 and CSS 150-48

CSW65-XYZZZZZ

Where x = 5, 12, 15, 18, 24, 28, 48, 54; y = /A, /D or blank; z = any alphanumeric character or blank (non safety relevant)