



- Low Cost
- 5V to 48V Outputs
- Universal Input
- Compact Size
- NEC Class 2 Compliant
- UL508 Listed
- -10°C to +71°C Operation

DPP15-100 Series

15-100W, 5-48V Output

DIN Rail Mount Power Supplies

Key Market Segments & Applications

- Industrial Controls: Motor Control Systems
- Factory Automation: Process Control, Automotive, Chemical Processing
- Test & Measurement: Burn in & Test, Instrumentation Measurement

DPP15-100 Features and Benefits

Features

- PFC Compliant to EN61000-3-2
- UL508 Approvals
- TS35/7.5 or TS35/15 DIN Rail Mounting

Benefits

- Supports Global Use
- Easier System Configuration
- Easy System Integration

Specifications

ITEMS	MODELS		DPP15	DPP25/30	DPP50	DPP100
	(1)	VAC				
AC Input Voltage range	(1)	VAC	85 - 264VAC			85 - 132VAC 176 - 264VAC
Input Frequency		Hz	47 - 63Hz			
DC Input Voltage range		VDC	90 - 375VDC			210 - 375VDC
Inrush Current (115 / 230VAC)		A	<35A	35 / 45A	35 / 50A	35 / 55A
Power Factor		-	Meets EN61000-3-2 Class A			
Max Input Current (230VAC)		A	0.25	0.4	0.7	1.2
Output Voltage Accuracy		%	±1% (24V outputs preset at 24.5V)			
Line Regulation		%	< 0.5%			
Load Regulation		%	< 0.5%			
Ripple/Noise		mV	<50mV (20MHz Bandwidth)			
Overcurrent Protection (Typ)		-	>120%			
Overvoltage Protection		V	125 - 137.5%			
Hold Up Time (115VAC input)		ms	> 20ms			
Parallel switch		-	No			Yes
LED Indicator		-	Green LED = On			
Operating Temperature		-	-10°C to +71°C (Derate linearly 5%/°C from 61°C to 71°C)			
Storage Temperature		-	-25°C to +85°C			
Operating Humidity		-	20 - 90% RH (non condensing)			
Cooling	(2)	-	Convection			
Withstand Voltage		-	Input to Output 3kVAC for 1 min.			
Shock		-	Half sine wave, 4G, 22ms, 3 times per face, X, Y, Z			
Vibration		-	10-500Hz (20 min sweep) 0.002G ² /Hz, 1Grms acceleration X, Y, Z, 1 hour			
Isolation Resistance		Ω	>100MΩ at 25°C & 70%RH, Output to Ground 500VDC			
Safety Agency Approvals	(4)	-	IEC/UL/CSA/EN60950-1, 60950-1, UL508, UL1310(3) (Class 2), CE Mark			
Emissions		-	EN55011, EN55032 Class B Radiated & Conducted, EN61000-6-3			
Immunity		-	EN61000-6-2, EN61000-4-2 Level 4, EN61000-4-3, EN61000-4-6 Level 3 EN61000-4-4 Level 4 (I/P) Level 3 (O/P), EN61000-4-5 Level 3 L-N, Level 4 L/N-PE, EN61000-4-8, EN61000-4-11			
Weight (Typ)		g	130	260	390	
Size (WxHxD)		mm	23 x 75 x 97	45 x 75 x 91	73 x 75 x 97	
Case material		-	Plastic			
MTBF (MIL-HDBK-217F, GF25)		Hours	287,000	>288,000	273,000	239,000
Warranty		yrs	3			

(1) Auto Select - DPP100 only

(3) Does not include DPP25-5 & DPP100-24 models. Evaluated to NEC NFPA70 Class 2 output per UL1310.

(2) Recommend 25mm clearance on all sides.

(4) Consult Sales Office for use under DC Input conditions

Model Selector						
Model	Output Voltage (V)	Output Adjust (V)	Output Curr. (A)	Max. Output Power (W)	Efficiency at Full Load (%)	
DPP25-5	5	5-6	5	25	78	
DPP30-12	12	9.9-12.1	2.5	30	82	
DPP50-15	15	11.9-15.1	3.4	50	85	
DPP15-24	24	22.5-28.5	0.63	15	80	
DPP30-24	24	22.5-28.5	1.3	30	84	
DPP50-24	24	22.5-28.5	2.1	50	86	
DPP100-24	24	22.5-28.5	4.2	100	87	
DPP50-48	48	48-56	1.05	50	87	

Installation


Snap-on Mounting - snap onto DIN Rail TS35/7.5 or TS35/15 (no tools required)

Cooling - Normal Convection


Clearance - 25mm all sides

Connection - Use copper wire 0.5-2.5mm² (AWG24-12)


Outline Drawing DPP15 Series



Outline Drawing DPP25-DPP50 Series



Outline Drawing DPP100 Series





TDK-Lambda France SAS

3 Avenue du Canada
 Parc Technopolis
 Bâtiment Sigma
 91940 les Ulis
 France
 Tel: +33 1 60 12 71 65
 Fax: +33 1 60 12 71 66
france@fr.tdk-lambda.com
www.emea.lambda.tdk.com/fr



Italy Sales Office

Via Giacomo Matteotti 62
 20092 Cinisello Balsamo (MI)
 Italy
 Tel: +39 02 61 29 38 63
 Fax: +39 02 61 29 09 00
info.italia@it.tdk-lambda.com
www.emea.lambda.tdk.com/it



Netherlands

info@nl.tdk-lambda.com
www.emea.lambda.tdk.com/nl



TDK-Lambda Germany GmbH

Karl-Bold-Strasse 40
 77855 Achern
 Germany
 Tel: +49 7841 666 0
 Fax: +49 7841 5000
info.germany@de.tdk-lambda.com
www.emea.lambda.tdk.com/de



Austria Sales Office

Aredstrasse 22
 2544 Leobersdorf
 Austria
 Tel: +43 2256 655 84
 Fax: +43 2256 645 12
info@at.tdk-lambda.com
www.emea.lambda.tdk.com/at



Switzerland Sales Office

Eichtalstrasse 55
 8634 Hombrechtikon
 Switzerland
 Tel: +41 44 850 53 53
 Fax: +41 44 850 53 50
info@ch.tdk-lambda.com
www.emea.lambda.tdk.com/ch



Nordic Sales Office

Haderslevvej 36B
 DK-6000 Kolding
 Denmark
 Tel: +45 8853 8086
info@dk.tdk-lambda.com
www.emea.lambda.tdk.com/dk



TDK-Lambda UK Ltd.

Kingsley Avenue
 Ilfracombe
 Devon EX34 8ES
 United Kingdom
 Tel: +44 (0) 12 71 85 66 66
 Fax: +44 (0) 12 71 86 48 94
info@uk.tdk-lambda.com
www.emea.lambda.tdk.com/uk



TDK-Lambda Ltd.

1 Alexander Yanai
 Segula
 Petah-Tikva
 Israel
 Tel: +9 723 902 4333
 Fax: +9 723 902 4777
info@tdk-lambda.co.il
www.emea.lambda.tdk.com/il



C.I.S.

Commercial Support:
 Tel: +7 (495) 665 2627
Technical Support:
 Tel: +7 (812) 658 0463
info@tdk-lambda.ru
www.emea.lambda.tdk.com/ru

Local Distribution

