



America


# CERTIFICATE

No. U8V 109510 0008 Rev. 00

**Holder of Certificate:** **TDK-Lambda UK Limited**

Kingsley Avenue  
Ilfracombe, Devon, EX34 8ES  
UNITED KINGDOM

**Certification Mark:**




**Product:**

**Power supplies**  
**( AC-DC Din Rail Mountable Power Supplies )**

This product was voluntarily tested to the relevant safety requirements referenced on this certificate. It can be marked with the certification mark above. The mark must not be altered in any way. This product certification system operated by TÜV SÜD America Inc. most closely resembles system 3 as defined in ISO/IEC 17067. Certification is based on the TÜV SÜD "Testing and Certification Regulations". TÜV SÜD America Inc. is an OSHA recognized NRTL and a Standards Council of Canada accredited Certification body.

**Test report no.:** 081-200858-000

**Date,** 2020-09-23

  
( Watson Yang )



America

# CERTIFICATE

No. U8V 109510 0008 Rev. 00

**Model(s):** DSP100-5, DSP100-12, DSP100-15, DSP100-24, DSP100-24/C2

**Brand Name:** TDK-Lambda

**Brand:** ***TDK-Lambda***

**Tested according to:** UL 62368-1:2014  
CAN/CSA-C22.2 No. 62368-1:2014

**Production Facility(ies):** 004727, 004978

**Parameters:** Rated inputs: See below  
Rated outputs: See below  
Protection class: II  
Max. ambient temperature: 50 °C

- Remarks:
1. When installing the equipment, all requirements of the relevant standards must be fulfilled.
  2. The equipment is evaluated for operating in altitude up to 5,000 m above the sea level.

**The ratings & model description of the models are as below:**

| Model        | Input rating                      | Output Voltage | Output Current | Output Power |
|--------------|-----------------------------------|----------------|----------------|--------------|
| DSP100-5     | 100-240 Vac,<br>47-63 Hz, 1500 mA | 5 Vdc          | 12 A           | 60 W         |
| DSP100-12    | 100-240 Vac,<br>47-63 Hz, 1700 mA | 12 Vdc         | 6 A            | 72 W         |
| DSP100-15    |                                   | 15 Vdc         | 5 A            | 75 W         |
| DSP100-24    | 100-240 Vac,<br>47-63 Hz, 2200 mA | 24 Vdc         | 4.2 A          | 100 W        |
| DSP100-24/C2 |                                   | 24 Vdc         | 3.8 A          | 91 W         |

ZERTIFIKAT ◆ CERTIFICATE ◆ 認證書 ◆ CERTIFICADO ◆ CERTIFICAT



# CERTIFICATE

No. U8V 109510 0008 Rev. 00

## License Condition:

1. This power supply has been judged on the basis of the required spacing is the Standard for Safety of Audio/Video, information and communication technology equipment, including electrical business equipment UL 62368-1:2014 and CAN/CSA-C22.2 No. 62368-1:2014, which covers the end-use product for which this component was designed.
2. The power supply shall be installed in compliance with mounting, spacings, casualty and segregation requirements of the ultimate application.
3. The unit was investigated to material Group III creepage, clearance and material properties requirements.
4. The unit was investigated as pollution degree 2 equipment.
5. The unit is considered acceptable for use in a 50°C ambient. Consideration should be given to the need for reconducting a temperature test in the end-use equipment.
6. Consideration should be given to measuring the temperature on power electronic components, inductors and transformer windings when the power supply is installed in the end product. Transformers T1 employ Class B Insulation Systems.
7. Stability and Mechanical strength must be evaluated in the end product.
8. Language of safety markings/instructions (if user accessible in the end product) must be included in the end product documentation.
9. Evaluated for IT power systems.