


IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)
CB SCHEME

CB TEST CERTIFICATE

Product	Switch Mode Power Supply
Name and address of the applicant	TDK-LAMBDA UK LTD KINGSLEY AVE ILFRACOMBE DEVON EX34 8ES UNITED KINGDOM
Name and address of the manufacturer	TDK-LAMBDA UK LTD KINGSLEY AVE ILFRACOMBE DEVON EX34 8ES UNITED KINGDOM
Name and address of the factory <i>Note: When more than one factory, please report on page 2</i>	TDK-LAMBDA UK LTD KINGSLEY AVE ILFRACOMBE EX34 8ES UNITED KINGDOM <input checked="" type="checkbox"/> Additional Information on page 2
Ratings and principal characteristics	100-240Vac nom, 4.9Arms max, 45-440Hz (optional) 133-318Vdc nom, 3.5Adc max (optional) (See test report model differences for details of ratings)
Trademark (if any)	TDK-Lambda 
Type of Customer's Testing Facility (CTF) Stage used	CTF Stage 3
Model / Type Ref.	EFE-300M Series, EFE300M Series See Page 2
Additional information (if necessary may also be reported on page 2)	The report was revised to include technical modifications <input checked="" type="checkbox"/> Additional Information on page 2
A sample of the product was tested and found to be in conformity with	IEC 60950-1:2005/AMD1:2009, IEC 60950-1:2005/AMD2:2013, IEC 60950-1:2005
As shown in the Test Report Ref. No. which forms part of this Certificate	E135494-A34-CB-5 issued on 2019-09-13

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2019-09-13

Original Issue Date: 2015-04-14

Signature:

Jan-Erik Storgaard



Ref. Certif. No.

DK-44773-M1-UL

Model Details:

EFE-300M Series, EFE300M Series (see test report model differences for details of models and nomenclature)

Factories:

PANYU TRIO MICROTRONIC CO LTD
SHIJI INDUSTRIAL ESTATE DONGYONG NANSHA GUANGZHOU GUANGDONG
CHINA

TDK-LAMBDA CORP
2704-1 SETTAYA-MACHI NAGAOKA-SHI NIIGATA-KEN 940-1195
JAPAN

Additional Information:

Additionally evaluated to EN 60950-1: 2006 / A11: 2009 / A1: 2010 / A12: 2011 / A2: 2013; National Differences specified in the CB Test Report.

The original report was modified to include the following changes/additions:

1. Additional discharge resistors added
2. Adding/removing alternates, making corrections and updating component Certificates in the Critical Components list.
3. Enclosures updated where applicable.

Additional information (if necessary)



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2019-09-13
Original Issue Date: 2015-04-14

Signature:

Jan-Erik Storgaard