

Test Report issued under the responsibility of:



TEST REPORT

IEC 60950-1

Information technology equipment – Safety – Part 1: General requirements

Report Number...... 1017226

Date of issue...... 4 August 2010

Total number of pages...... 73

CB Testing Laboratory Intertek Semko AB

Address....... Torshamnsgatan 43, P.O. Box 1103, SE-164 22 Kista, SWEDEN

Manufacturer's name...... TDK-Lambda Corporation

Address....... 2701 Togawa Settaya Nagaoka-shi, Niigata 940-1195 JAPAN

Test specification:

Standard IEC 60950-1:2005 (2:nd Edition); Am 1:2009

Test procedure...... CB Scheme

Non-standard test method.....: N/A

Test Report Form No...... IEC60950_1B

Test Report Form(s) Originator: SGS Fimko Ltd

Master TRF Dated 2010-04

Copyright © 2010 Worldwide System for Conformity Testing and Certification of Electrotechnical Equipment and Components (IECEE), Geneva, Switzerland. All rights reserved.

This publication may be reproduced in whole or in part for non-commercial purposes as long as the IECEE is acknowledged as copyright owner and source of the material. IECEE takes no responsibility for and will not assume liability for damages resulting from the reader's interpretation of the reproduced material due to its placement and context.

If this Test Report Form is used by non-IECEE members, the IECEE/IEC logo and the reference to the CB Scheme procedure shall be removed.

This report is not valid as a CB Test Report unless signed by an approved CB Testing Laboratory and appended to a CB Test Certificate issued by an NCB in accordance with IECEE 02.

Test item description.....: DC-DC converters

Trade Mark TDK-Lambda

Manufacturer...... TDK-Lambda Corporation

Model/Type reference...... PH300S280-**/***, PH600S280-**/*** (See page 7)

Ratings...... 200-400V---



		Page 2 of 73	Report No.: 1017226	
Test	ing procedure and testing location:			
	CB Testing Laboratory:	Intertek Semko AB		
Testing location/ address		Torshamnsgatan 43, P.O. Box 1103, SE-164 22 Kista, SWEDEN		
	Associated CB Laboratory:			
Testing location/ address:				
	Tested by (name + signature):	Henrik Brolin	Henry Policy	
	Approved by (name + signature):	Kjell Fredriksson	Gelt tredilien	
	Testing procedure: TMP			
Testing location/ address:				
	Tested by (name + signature):			
	Approved by (name + signature):			
П	Testing procedure: WMT			
Testing location/ address:				
, 000				
	Tested by (name + signature):			
	Witnessed by (name + signature) :			
	Approved by (name + signature):			
	Testing procedure: SMT			
Testing location/ address:				
	Tested by (name + signature):			
	Approved by (name + signature):			
	Supervised by (name + signature):			
	Testing procedure: RMT			
Tes	ting location/ address:			
	Tested by (name + signature):			
	Approved by (name + signature):			
	Supervised by (name + signature):			



List of Attachments (including a total number of pages in each attachment):

European group differences and national differences

IEC 60950-1 Test Report.



Page 1-52


Page 63-73


Report No.: 1017226

lon:
ies according to: d.
_

Report No.: 1017226

Copy of marking plate





Note. Manufacture name changed to: TDK-Lambda

Test item particulars			
Equipment mobility	[] movable [] hand-held [] transportable [] stationary [x] for building-in [] direct plug-in		
Connection to the mains:	[] pluggable equipment [] type A [] type B [x] permanent connection [] detachable power supply cord [] non-detachable power supply cord [] not directly connected to the mains		
Operating condition:	[x] continuous [] rated operating / resting time:		
Access location:	[] operator accessible [] restricted access location [x] for building into a host equipment		
Over voltage category (OVC)	[] OVC I [x] OVC II [] OVC III [] OVC IV [] other:		
Mains supply tolerance (%) or absolute mains supply values	Not applicable, Voltage range 200-400Vdc		
Tested for IT power systems	[] Yes [x] No		

TRF No. IEC60950_1B



Page 5	of 73 Report No.: 1017226
IT testing, phase-phase voltage (V)	N/A
Class of equipment:	[x] Class I [] Class II [] Class III [] Not classified
Considered current rating of protective device as part of the building installlation (A)	16
Pollution degree (PD)	[] PD 1 [x] PD 2 [] PD 3
IP protection class:	IPx0
Altitude during operation (m)	<2000
Altitude of test laboratory (m):	<2000
Mass of equipment (kg):	<0.250
Possible test case verdicts:	
- test case does not apply to the test object:	N/A (or N)
- test object does meet the requirement:	P (Pass)
- test object does not meet the requirement	F (Fail)
Testing	
Date of receipt of test item	2 August 2010
Date(s) of performance of tests	-
General remarks:	
The test results presented in this report relate only to the This report shall not be reproduced, except in full, without laboratory. "(see Enclosure #)" refers to additional information apple "(see appended table)" refers to a table appended to the Throughout this report a □ comma / ☒ point is used	out the written approval of the Issuing testing pended to the report. e report.
Manufacturer's Declaration per sub-clause 6.2.5 of	IECEE 02:
The application for obtaining a CB Test Certificate includes more than one factory location and a declaration from the Manufacturer stating that the sample(s) submitted for evaluation is (are) representative of the products from each factory has been provided	Comment: Will be provided by the manufacturer upon requesting by the authorities.
When differences exist; they shall be identified in the G	eneral product information section.
Name and address of factory (ies)::	TDK-Lambda (Malaysia) Sdn. Bhd.
	PLO33 Locked Bag No. 110, Kawasan Perindustrian Senai 81400 Senai Johor, Darul Takzim, MALAYSIA
	TDK-Lambda Corporation Nagaoka Technical Center 2701 Togawa, Settaya, Nagaoka, Niigata, 940-1195, JAPAN
	Wuxi TDK-Lambda Electronics Co., Ltd.
	Lot 107 Wuxi Singapore Ind. Park, Xing Chuang Erlu Wuxi Jiangsu, 214028, CHINA

TRF No. IEC60950_1B



Report No.: 1017226



General product information:

- a) Test results in this report are based on the previously issued test reports from BSI with ref. Nos. 249/4925050/1 of 5. Based on reports from SET Laboratory with report number SMTN0137. A new test report has been issued due to the upgrade of test standard and some minor editorial modifications.
- b) These products shall be installed in accordance with the requirements of IEC 60950-1, EN 60950-1 for the end use application. The DC to DC converters were tested with the heatsink mounted below the baseplate of the converters (worst case).
- c) The DC to DC converter baseplate shall be properly bonded to earth ground in the end use product as this unit was investigated for Class I construction. T101/T102 use triple insulated wire with an insulation class for the transformers of Class H.
- d) These products must be installed in a restricted access location accessible to authorised competent personnel only. These products were assessed for Reinforced insulation between input and output assuming a 250Vac mains supply. These converters may have a mains derived DC supply attached to the input and provide a SELV output. All outputs are an energy hazard except for PH300S280-3.3 unit. To maintain the SELV output under fault conditions, the output must be connected to earth in the final application.
- The operation of these DC to DC converters is subject to the end customer maintaining the baseplate at or below the following values during operation.

PH300S280-3.3, -5:- 100°C at 100% load

PH300S280-12, 15, 24, 28, 48:- 90°C at 100% load, 100°C at 83% load.

PH300S280-48/EM:- 65°C at 100% load, 100°C at 70% load.

PH600S280 series:- 85°C 100% load, 100°C at 80% load.

In accordance with the instructions, the baseplate temperature measurement point is as follows:-

PH300S280 series:- Centre of the baseplate.

PH600S280 series:- 30mm from the input end, along the centre line.

- f) The DC to DC converters have not been assessed for an IT power system.
- g) The input and output connectors are not acceptable for field wiring connections and are only intended for connection to a PCB inside the end use equipment.
- h) The recommended input fuse ratings within the instructions were as follows:-

PH300S280-* = F5AH, 250V

PH600S280-* = F10AH, 250V

The breaking capacity and voltage rating are subject to the end use application.

Summary of Testing:

Testing Environment:

Ambient temperature: 15°C to 30°C Relative humidity: 25% to 75% Air pressure: 86 kPa to 106 kPa

10-06 Strömberg 164234

TRF No. IEC60950_1B

Report No.: 1017226



General product information: (continue)

Models included within the scope of this report

	Inp	Input		Output	
Model	V dc	Α	V dc	Α	
PH300S280-3.3	200-400	1.9	3.3	50	
PH300S280-5	200-400	1.9	5	50	
PH300S280-12	200-400	1.9	12	25	
PH300S280-15	200-400	1.9	15	20	
PH300S280-24	200-400	1.9	24	12.5	
PH300S280-28	200-400	1.9	28	10.8	
PH300S280-48	200-400	1.9	48	6.3	
PH300S280-48/HKM	200-400	1.9	48	6.3	
PH300S280-48/EM	200-400	1.9	48	7.9	
PH600S280-3.3	200-400	3.8	3.3	100	
PH600S280-5	200-400	3.8	5	100	
PH600S280-12	200-400	3.8	12	50	
PH600S280-12/WE	200-400	3.8	12	50	
PH600S280-15	200-400	3.8	15	40	
PH600S280-15/WE	200-400	3.8	15	40	
PH600S280-24	200-400	3.8	24	25	
PH600S280-24/WE	200-400	3.8	24	25	
PH600S280-28	200-400	3.8	28	21.5	
PH600S280-28/WE	200-400	3.8	28	21.5	
PH600S280-28/33	200-400	3.8	33	18.24	
PH600S280-48	200-400	3.8	48	12.5	
PH600S280-48/WE	200-400	3.8	48	12.5	
PH600S280-48/EM	200-400	3.8	48	12.5	
PH600S280-48/HKM	200-400	3.8	48	12.5	

All models may also be marked with /PI after the output voltage marking. The /PI difference being that the corner studs are not threaded and for the standard models the studs are threaded.

All models may include suffix /T, corner studs are not threaded with an inside diameter of 0.1mm less than standard model.