



**TDK-Lambda Corporation**  
2-5-1, Nihonbashi  
Chuo-ku, Tokyo  
103-6128 Japan  
www.tdk-lambda.com

## EU DECLARATION OF CONFORMITY

HWS300-1800 series

We, TDK-Lambda Corporation, of 2-5-1, Nihonbashi, Chuo-ku, Tokyo, 103-6128 Japan, declare under our sole responsibility that the TDK-Lambda power supplies, as detailed on the attached products covered sheets, complies with the provisions of the following European Directives and is eligible to bear the CE mark:


Low Voltage	Directive 2014/35/EU
EMC	Directive 2014/30/EU
RoHS	Directive 2011/65/EU (as amended by 2015/863)

Assurance of conformance of the described product with the provisions of the stated EC Directive is given through compliance to the following standards:

Electrical Safety (LVD)	EN 62368-1:2014 + A11:2017
Electromagnetic Compatibility (EMC)	EN 61000-6-3:2007 + A1:2011 EN 61000-6-2:2005 EN 61204-3:2001 EN 55024:2010 EN 55032:2015

**Note:** The EMC performance of a component power supply will be affected by the final installation, compliance to the stated EMC standards and conformance to the EMC Directive must be confirmed after installation by the final equipment manufacturer. For guidance with respect to test conditions please visit our website at '[www.emea.lambda.tdk.com/uk/KB/EMC-Guidance.pdf](http://www.emea.lambda.tdk.com/uk/KB/EMC-Guidance.pdf)' or contact your local TDK-Lambda sales office.

Our representative in the EU is TDK-Lambda Germany GmbH, located at Karl-Bold-Str. 40, 77855 Achern, Germany.

Name of Authorized Signatory:	Christopher Haas
Signature of Authorized Signatory:	
Position of Authorized Signatory:	Head of Quality & Compliance Europe
Date:	05 <sup>th</sup> November 2020
Date when this declaration issued first:	05 <sup>th</sup> November 2020
Place where signed:	Achern, Germany

The products covered by this declaration are (see next page):

HWS300-acdefgh,  
HWS300P-bcdfh,  
HWS300-24/OR  
HWS300-24/LNTdf

Where: a = 3, 5, 12, 15, 24 or 48  
b = 24, 36 or 48  
c = / or blank  
d = PV or blank  
e = RY, RYLLF (HWS300-24 only) or blank  
f = CO, CO2 or HD or blank  
g = HU (HWS300-24 only) or blank  
h = MF or blank

HWS300-xx/ME,  
HWS300-xx/MEL

Where: xx = 12, 15, 24 or 48

HWS600-adeefghij  
HWS600P-bdefhij  
HWS600PCN-cdefhij  
HWS600-24/LNTeh  
HWS600-48/LNTeh  
HWS600-42/DS  
HWS600-48/PVLNF  
HWS600-24/DC  
HWS600-48/DC

Where: a = 3, 5, 12, 15, 24, 48 or 55  
b = 24, 36 or 48  
c = 24 or 30  
d = / or blank  
e = PV or blank  
f = RY, RYCO, RYLLF or RYHD (HWS600P-24, HWS600PCN-24, HWS600-24 only)  
g = /MESC (HWS600-24) or blank  
h = CO, HD or blank  
i = LLF or blank  
j = MF or blank

HWS600-xx/ME(SC)

Where: xx = 5, 12, 15, 24 or 48  
SC is an optional suffix for the HWS600-24/ME only

HWS1000-xy

Where: x = 3, 5, 6, 7, 12, 15, 24, 36, 48 or 60  
y = /CO, /HD, /RY (for x=24), /RYCO (for x=24), /RYHD (for x=24) or blank

HWS1000-24/ME, HWS1000-36/ME, HWS1000-48/ME

HWS1500-xy

Where: x = 3, 5, 6, 7, 12, 15, 24, 36, 48 or 60  
y = /CO, /HD, /LNF (for x=24, 36, 48), /LNF3K (for x=24) or blank (for all suffix x)

HWS1500-24/ME, HWS1500-36/ME, HWS1500-48/ME

HWS1800T-3, HWS1800T-5, HWS1800T-6, HWS1800T-7, HWS1800T-12, HWS1800T-15, HWS1800T-24  
HWS1800T-36, HWS1800T-48 and HWS1800T-60 may be followed by /CO, /HD or /SB.