



TDK-Lambda

Product Highlights

- High Power density, 109W/inch³
- Wide Range Input > 2:1
- High Efficiency up to 91%
- 50% smaller than previous generation
- Half Brick Package & Footprint

Key Specifications

- 5, 12, 24, 28, 48Vdc Output Models
- 200-425Vdc input Range
- Operation up to 100°C Baseplate Temp.
- Remote Sense, Remote on/off
- -60/+10% Output Adj. Range on all models
- 3kV AC Input/Output Isolation

Typical Applications

- Industrial DPA, Point of Load
- Custom Fanless DC Solutions
- HVDC (High Voltage Direct Current)
- Smart Grid Applications