

HFE1600

EVALUATION DATA

DWG: IA688-53-01		
APPD	CHK	DWG
Doron P.	<i>Doron P.</i>	<i>MICHAEL G.</i>
3-May-2011	3-May-2011	3-May-2011

INDEX PAGE

1.EVALUATION METHOD

1-1. Circuit used for determination T-1~6

- (1) Steady state data
- (2) Warm up voltage drift & long term stability
- (3) Over voltage protection (OVP) characteristics
- (4) Over current protection (OCP) characteristics
- (5) Output rise characteristics
- (6) Output fall characteristics
- (7) Dynamic line response characteristics
- (8) Dynamic load response characteristics
- (9) Inrush current characteristics
- (10) Leakage current characteristics
- (11) Output ripple and noise waveform
- (12) Standby current

1-2. List of equipment used T-7

2.CHARACTERISTICS

2-1. Steady state data

- | | |
|--|---------|
| (1) Regulation-line and load, Temp. drift | T-8~10 |
| (2) Output voltage and ripple voltage v.s. input voltage | T-11~13 |
| (3) Efficiency and input current v.s. input voltage | T-14~16 |

- | | |
|--|---------|
| 2-2. Warm up voltage drift characteristics | T-17 |
| 2-3. Over voltage protection (OVP) characteristics | T-18~20 |
| 2-4. Over current protection (OCP) characteristics | T-21~23 |
| 2-5. Output rise characteristics | T-24~25 |
| 2-6. Output fall characteristics | T-26~27 |
| 2-7. Output rise characteristics with ON/OFF control | T-28~30 |
| 2-8. Output fall characteristics with ON/OFF control | T-31~33 |
| 2-9. Hold up time characteristics | T-34~36 |
| 2-10. Dynamic line response characteristics | T-37~38 |
| 2-11. Dynamic load response characteristics | T-39~41 |
| 2-12. Response to brown out characteristics | T-42~44 |
| 2-13. Inrush current characteristics | T-45~46 |
| 2-14. Inrush current waveform | T-47~48 |
| 2-15. Input current waveforms | T-49 |
| 2-16. Leakage current characteristics | T-50 |
| 2-17. Output ripple & noise waveforms | T-51~52 |
| 2-18. Standby current | T-53 |


TERMINOLOGY USED

Definition


Vin	Input voltage
Vout	Output voltage
Iin	Input current
Iout	Output current
Ta	Ambient Temperature

HFE1600

(1) Steady state data




(3) Over Voltage Protection (OVP) characteristics




(4) Over Current Protection (OCP) characteristics

Same as item (1)


(5) (6) Output Rise & Fall Characteristics



(7) Dynamic line response characteristics




(8) Dynamic load response characteristics




Dynamic load response characteristics

Output current waveform
I_{out} 0% <----> 100%




$t_r = 100\mu s$
 $t_f = 100\mu s$

Output current waveform
I_{out} 50% <----> 100%




$t_r = 100\mu s$
 $t_f = 100\mu s$

(9) Inrush current characteristics




(10) Leakage current characteristics




(11) Output ripple & noise waveform


(a) Normal mode



(b) Normal and common mode -Vo Terminal grounded



(c) Normal and common mode +Vo Terminal grounded



(12) Standby current
Same as Steady state data

1-2 List of equipment used

No	EQUIPMENT USED	MANUFACTURER	MODEL No.
1	Storage oscilloscope	YOKOGAWA	DL7100
2	Storage oscilloscope	YOKOGAWA	DL1740
3	Digital multimeter	AGILENT	34401A
4	Digital power meter	YOKOGAWA	WT110
5	Autotransformer	VOLTAC	B15
6	Autotransformer	METREL	HSN 260/30
7	Electronic load	H&H	ZS6060 SC150
8	Electronic load	H&H	ZS7006
9	Electronic load	H&H	ZS7060
10	Electronic load	CHROMA	63203
11	Electronic load	CHROMA	63206
12	Controlled temp. chamber	THERMOTRON	SM-16-3800
13	Controlled temp. chamber	THERMOTRON	SE-600-6-6
14	AC Source	CHROMA	6590
15	Analyzing AC power supply	TAKASAGO	AA2000XG
16	Inrush current tester	TAKAMISAWA	PSA-210
17	Leakage current tester	HIOKI	3155
18	Current probe	YOKOGAWA	701933

2. CHARACTERISTICS

2-1. Steady state data

(1). Regulation-Line and Load, Temperature drift

12V

1.1 Regulation - Line & Load

CONDITIONS: $T_a = 25^{\circ}\text{C}$
 $I_{aux}=0.5\text{A}$

	Vin (AC)				
Io	85	100	132	Line Regulation	
0%	12.004	12.004	12.004	0	0
50%	12.002	12.002	12.002	0	0
100%	12.008	12.007	12.006	0.002	0.017
Load Regulation	0.006	0.005	0.004	$\Delta V(V)$	(%)
	0.050	0.042	0.033	(%)	

*Note: Load at 85Vac is derated according to specification

	Vin (AC)					
Io	170	200	230	265	Line Regulation	
0%	12.000	12.000	12.001	12.001	0.001	0.008
50%	11.999	11.999	11.999	11.999	0	0
100%	12.007	12.006	12.006	12.005	0.002	0.017
Load Regulation	0.008	0.007	0.007	0.006	$\Delta V(V)$	(%)
	0.067	0.058	0.058	0.050	(%)	

1.2 Temperature drift

	Ta			Drift (V)	PPM/ $^{\circ}\text{C}$
	-10 $^{\circ}\text{C}$	25 $^{\circ}\text{C}$	50 $^{\circ}\text{C}$		
Vo (V)	11.998	11.998	11.983	0.015	21

CONDITIONS: $V_{in}=230\text{VAC}$
 $V_o=12\text{V}$
 $I_o=133\text{A}$
 $I_{aux}=0.5\text{A}$

2-1. Steady state data

(1). Regulation-Line and Load, Temperature drift

24V

1.1 Regulation - Line & Load

CONDITIONS: $T_a = 25^{\circ}\text{C}$
 $I_{\text{aux}} = 0.5\text{A}$

Io	Vin (AC)			Line Regulation	
	85	100	132		
0%	24.005	24.003	24.003	0.002	0.008
50%	23.983	23.983	23.984	0.001	0.004
100%	23.989	23.988	23.989	0.001	0.004
Load Regulation	0.022	0.020	0.019	$\Delta V(\text{V})$	(%)
	0.092	0.083	0.079	(%)	

*Note: Load at 85Vac is derated according to specification

Io	Vin (AC)				Line Regulation	
	170	200	230	265		
0%	24.003	24.003	24.003	24.003	0	0
50%	23.987	23.988	23.988	23.988	0.001	0.004
100%	23.999	24.001	24.002	24.003	0.004	0.017
Load Regulation	0.016	0.015	0.015	0.015	$\Delta V(\text{V})$	(%)
	0.067	0.063	0.063	0.063	(%)	

1.2 Temperature drift

Vo (V)	Ta			Drift (V)	PPM/ $^{\circ}\text{C}$
	-10 $^{\circ}\text{C}$	25 $^{\circ}\text{C}$	50 $^{\circ}\text{C}$		
23.983	23.971	23.943	0.040	28	

CONDITIONS: $V_{\text{in}} = 230\text{VAC}$
 $V_o = 24\text{V}$
 $I_o = 67\text{A}$
 $I_{\text{aux}} = 0.5\text{A}$

2-1. Steady state data

(1). Regulation-Line and Load, Temperature drift

48V

1.1 Regulation - Line & Load

CONDITIONS: $T_a = 25^{\circ}\text{C}$
 $I_{\text{aux}} = 0.5\text{A}$

Io	Vin (AC)			Line Regulation	
	85	100	132		
0%	47.998	47.998	47.998	0	0
50%	48.011	48.011	48.01	0.001	0.002
100%	48.018	48.017	48.015	0.003	0.006
Load Regulation	0.020	0.019	0.017	$\Delta V(\text{V})$	(%)
	0.042	0.040	0.035	(%)	

*Note: Load at 85Vac is derated according to specification

Io	Vin (AC)				Line Regulation	
	170	200	230	265		
0%	47.989	47.989	47.988	47.988	0.001	0.002
50%	48.019	48.018	48.017	48.017	0.002	0.004
100%	48.041	48.04	48.039	48.038	0.003	0.006
Load Regulation	0.052	0.051	0.051	0.050	$\Delta V(\text{V})$	(%)
	0.108	0.106	0.106	0.104	(%)	

1.2 Temperature drift


Vo (V)	Ta			Drift (V)	PPM/ $^{\circ}\text{C}$
	-10 $^{\circ}\text{C}$	25 $^{\circ}\text{C}$	50 $^{\circ}\text{C}$		
48	48.243	48.180	48.052	0.191	66

CONDITIONS: $V_{\text{in}} = 230\text{VAC}$
 $V_o = 48\text{V}$
 $I_o = 33\text{A}$
 $I_{\text{aux}} = 0.5\text{A}$

(2). Output ripple Vs Input and Output Voltages

24V

CONDITIONS: Iout:100%
Ta: -10°C -----
25°C -----
50°C -----



(2). Output ripple Vs Input and Output Voltages


CONDITIONS: I_{out}:100%

T_a: -10°C

25°C

50°C

48V



(2). Output ripple Vs Input and Output Voltages


CONDITIONS: $I_{out}: 100\%$

$T_a: -10^\circ\text{C}$

25°C

50°C

12V



(3). Efficiency and Input current vs. Output current

CONDITIONS:

Vin: 85 VAC

115 VAC

230 VAC

265 VAC


Vout:100%

Ta: 25°C

.....

————

12V




(3). Efficiency and Input current vs. Output current

CONDITIONS:

Vin: 85 VAC
115 VAC
230 VAC
265 VAC
Vout:100%
Ta: 25°C

=====

24V



(3). Efficiency and Input current vs. Output current

CONDITIONS:

Vin: 85 VAC

115 VAC

230 VAC

265 VAC


Vout:100%

Ta: 25°C

.....

————


48V




2.2. Warm up voltage drift characteristics

CONDITIONS: V_{in} : 230Vac
 I_{out} : 100%
 $T_a = 25^{\circ}\text{C}$


12V



24V




48V



2.3. Over Voltage protection (OVP) characteristics


CONDITIONS: V_{in} : 230Vac
 V_{out} : 12Vdc
 I_{out} : 0%
 $T_a = 25^{\circ}\text{C}$



2.3. Over Voltage protection (OVP) characteristics


CONDITIONS: V_{in} : 230Vac
 V_{out} : 24Vdc
 I_{out} : 0%
 $T_a = 25^{\circ}\text{C}$

24V



2.3. Over Voltage protection (OVP) characteristics


CONDITIONS: Vin: 230Vac
Vout: 48Vdc
Iout: 0%
Ta = 25°C




2.4. Over Current protection (OCP) characteristics

12V

CONDITIONS: Vin: 115Vac
Ta = 25°C




CONDITIONS: Vin: 230Vac
Ta = 25°C




2.4. Over Current protection (OCP) characteristics

24V

CONDITIONS: V_{in} : 115Vac
 $T_a = 25^{\circ}\text{C}$




CONDITIONS: V_{in} : 230Vac
 $T_a = 25^{\circ}\text{C}$




2.4. Over Current protection (OCP) characteristics

48V

CONDITIONS: Vin: 115Vac
Ta = 25°C




CONDITIONS: Vin: 230Vac
Ta = 25°C




2.5. Output rise characteristics

CONDITIONS: Vin: 85 VAC (A)
115 VAC (B)
230 VAC (C)
265 VAC (D)
Iout: 0%
Ta: 25°C


12V



24V




48V




2.5. Output rise characteristics

CONDITIONS: Vin: 85 VAC (A)
 115 VAC (B)
 230 VAC (C)
 265 VAC (D)
 Iout: 100%
 Ta: 25°C


12V



24V




48V




2.6. Output fall characteristics

CONDITIONS: Vin: 85 VAC (A)
 115 VAC (B)
 230 VAC (C)
 265 VAC (D)
 Iout: 0%
 Ta: 25°C


12V



24V




48V




2.6. Output fall characteristics

CONDITIONS: Vin: 85 VAC (A)
 115 VAC (B)
 230 VAC (C)
 265 VAC (D)
 Iout: 100%
 Ta: 25°C


12V



24V




48V




2.7. Output rise characteristics with On/Off control

CONDITIONS: Vin: 115 VAC
Iout: 100%
Ta: 25°C



CONDITIONS: Vin: 230 VAC
Iout: 100%
Ta: 25°C



2.7. Output rise characteristics with On/Off control


CONDITIONS:

Vin: 115 VAC

Iout: 100%

Ta: 25°C

24V




CONDITIONS:

Vin: 230 VAC

Iout: 100%

Ta: 25°C


24V



2.7. Output rise characteristics with On/Off control


CONDITIONS: Vin: 115 VAC
Iout: 100%
Ta: 25°C

48V



CONDITIONS: Vin: 230 VAC
Iout: 100%
Ta: 25°C


48V



2.8. Output fall characteristics with On/Off control


CONDITIONS: V_{in} : 115 VAC
 I_{out} : 100%
 T_a : 25°C

12V



CONDITIONS: V_{in} : 230 VAC
 I_{out} : 100%
 T_a : 25°C

12V



2.8. Output fall characteristics with On/Off control


CONDITIONS:

Vin: 115 VAC

Iout: 100%

Ta: 25°C

24V




CONDITIONS:

Vin: 230 VAC

Iout: 100%

Ta: 25°C


24V



2.8. Output fall characteristics with On/Off control


CONDITIONS: Vin: 115 VAC
Iout: 100%
Ta: 25°C

48V



CONDITIONS: Vin: 230 VAC
Iout: 100%
Ta: 25°C

48V




2.9. Hold up time characteristics

CONDITIONS: V_{out} : 100%
 T_a : 25°C


V_{in} : 115 VAC

12V



V_{in} : 230 VAC

12V




2.9. Hold up time characteristics

CONDITIONS: V_{out} : 100%
 T_a : 25°C


V_{in} : 115 VAC

24V



V_{in} : 230 VAC

24V




2.9. Hold up time characteristics

CONDITIONS: V_{out} : 100%
 T_a : 25°C


V_{in} : 115 VAC

48V



V_{in} : 230 VAC


48V




2.10. Dynamic line response characteristics

CONDITIONS: V_{in} : 85V↔132V
 I_{out} : 100%
 T_a : 25°C


12V



24V




48V




2.10. Dynamic line response characteristics

CONDITIONS: V_{in} : 170V $\leftrightarrow$ 265V
 I_{out} : 100%
 T_a : 25°C


12V



24V





48V



2.11. Dynamic load response characteristics

CONDITIONS: V_{in} : 230VAC
 V_{out} : 100%
 T_a : 25°C
 Load current: $t_r=t_f=100\mu\text{s}$

12V


 $f=100\text{Hz}$  $f=1\text{kHz}$ 

2.11. Dynamic load response characteristics


CONDITIONS: V_{in} : 230VAC
 V_{out} : 100%
 T_a : 25°C
 Load current: $t_r=t_f=100\mu s$

24V

$f=100\text{Hz}$





$f=1\text{kHz}$



2.11. Dynamic load response characteristics

CONDITIONS: V_{in} : 230VAC
 V_{out} : 100%
 T_a : 25°C
 Load current: $t_r=t_f=100\mu\text{s}$


48V

 $f=100\text{Hz}$  $f=1\text{kHz}$ 

2.12. Response to brown out characteristics

CONDITIONS: V_{in} : 115 VAC
 T_a : 25°C


12V



Brown-out time

A: 10ms
 B: 17ms
 C: 18ms

CONDITIONS: V_{in} : 230 VAC
 T_a : 25°C




Brown-out time

A: 8ms
 B: 31ms
 C: 32ms

2.12. Response to brown out characteristics

CONDITIONS: V_{in} : 115 VAC
 T_a : 25°C

24V


Brown-out time

A: 14ms

B: 16ms

C: 17ms

CONDITIONS: V_{in} : 230 VAC
 T_a : 25°C

Brown-out time

A: 10ms


B: 29ms

C: 30ms


2.12. Response to brown out characteristics

CONDITIONS: V_{in} : 115 VAC
 T_a : 25°C

48V




CONDITIONS: V_{in} : 230 VAC
 T_a : 25°C




2.13. Inrush current characteristics

CONDITIONS: Vin: 115 VAC ———
 230 VAC - - - -
 Vout: 100%
 Iout: 0%
 Ta: 25°C



2.13. Inrush current characteristics


CONDITIONS: V_{in} : 115 VAC ———
 230 VAC - - - -
 V_{out} : 100%
 I_{out} : 100%
 T_a : 25°C




2.14. Inrush current waveform

CONDITIONS: V_{in} : 115 VAC
 V_{out} : 100%
 T_a : 25°C

Switch on phase angle
of input AC voltage
 $\Phi=0^\circ$




Switch on phase angle
of input AC voltage
 $\Phi=90^\circ$




2.14. Inrush current waveform

CONDITIONS: V_{in} : 230 VAC
 V_{out} : 100%
 T_a : 25°C

Switch on phase angle
of input AC voltage
 $\phi=0^\circ$





Switch on phase angle
of input AC voltage
 $\phi=90^\circ$



2.15. Input current waveform


CONDITIONS: V_{out} : 100%
 T_a : 25°C




2.16. Leakage current characteristics

CONDITIONS: I_{out} : 100%
 T_a : 25°C
 f : 50Hz

L-G



N-G




2.17. Output ripple and noise waveform


CONDITIONS: Vin: 115VAC
Iout: 100%
Ta: 25°C

Normal Mode


12V



24V



48V




2.17. Output ripple and noise waveform


CONDITIONS: Vin: 230VAC
Iout: 100%
Ta: 25°C

Normal Mode


12V



24V




48V



2.18. Standby current

CONDITIONS: $T_a: 25^{\circ}\text{C}$

$I_o=0\%$



Remote control OFF

