

CUS30M

EVALUATION DATA

型式データ

INDEX

1. 測定方法	Evaluation Method	PAGE
1.1 測定回路	Circuit used for determination	
測定回路 1	Circuit 1 used for determination	T-1
静特性	Steady state data	
過電流保護特性	Over current protection (OCP) characteristics	
過電圧保護特性	Over voltage protection (OVP) characteristics	
出力立ち上がり特性	Output rise characteristics	
出力立ち下がり特性	Output fall characteristics	
出力保持時間特性	Hold up time characteristics	
測定回路 2	Circuit 2 used for determination	T-1
過渡応答（負荷急変）特性	Dynamic load response characteristics	
測定回路 3	Circuit 3 used for determination	T-1
入力サージ電流（突入電流）波形	Inrush current waveform	
測定回路 4	Circuit 4 used for determination	T-2
リーク電流特性	Leakage current characteristics	
測定回路 5	Circuit 5 used for determination	T-2
出力リップル、ノイズ波形	Output ripple and noise waveform	
測定構成	Configuration used for determination	T-3
EMI特性	Electro-Magnetic Interference characteristics	
(a) 雑音端子電圧（帰還ノイズ）	Conducted Emission	
(b) 雑音電界強度（放射ノイズ）	Radiated Emission	
1.2 使用測定機器	List of equipment used	T-4
2. 特性データ	Characteristics	
2.1 静特性	Steady state data	
(1) 入力・負荷・温度変動／出力起動・遮断電圧	Regulation - line and load, Temperature drift	
/ Start up voltage and Drop out voltage	T-5~6	
(2) 効率対出力電流	Efficiency vs. Output current	T-7~8
(3) 入力電流対出力電流	Input current vs. Output current	T-9~10
(4) 入力電力対出力電流	Input power vs. Output current	T-11~12
2.2 過電流保護特性	Over current protection (OCP) characteristics	T-13~14
2.3 過電圧保護特性	Over voltage protection (OVP) characteristics	T-15~17
2.4 出力立ち上がり特性	Output rise characteristics	T-18~19
2.5 出力立ち下がり特性	Output fall characteristics	T-20~21
2.6 出力保持時間特性	Hold up time characteristics	T-22~23
2.7 過渡応答（負荷急変）特性	Dynamic load response characteristics	T-24~27
2.8 入力電圧瞬停特性	Response to brown out characteristics	T-28~31
2.9 入力サージ電流（突入電流）波形	Inrush current waveform	T-32~34
2.10 リーク電流特性	Leakage current characteristics	T-35~43
2.11 出力リップル、ノイズ波形	Output ripple and noise waveform	T-44~47
2.12 E M I 特性	Electro-Magnetic Interference characteristics	T-48~71

使用記号 Terminology used

	定義	Definition
Vin	入力電圧 Input voltage
Vout	出力電圧 Output voltage
Iin	入力電流 Input current
Iout	出力電流 Output current
Ta	周囲温度 Ambient temperature
f	周波数 Frequency

1. 測定方法

Evaluation Method


1.1 測定回路

Circuit used for determination

CUS30M

測定回路1 Circuit 1 used for determination


- ・静特性 Steady state data
- ・過電流保護特性 Over current protection (OCP) characteristics
- ・過電圧保護特性 Over voltage protection (OVP) characteristics
- ・出力立ち上がり特性 Output rise characteristics
- ・出力立ち下がり特性 Output fall characteristics
- ・出力保持時間特性 Hold up time characteristics




Controlled Temp. Chanmber

測定回路2 Circuit 2 used for determination

- ・過渡応答(負荷急変) 特性 Dynamic load response characteristics




Output current waveform
Iout 25% <=> 75%



測定回路3 Circuit 3 used for determination

- ・入力サージ電流(突入電流) 波形 Inrush current waveform




測定回路4 Circuit 4 used for determination

CUS30M


- リーケ電流特性 Leakage current characteristics

(a) Earth leakage current of CLASS I equipment



Measure in all possible combination of position of S2 with : S1 closed (NORMAL CONDITION), and S1 open (Single fault condition).

(b) Patient leakage current



CLASS I equipment:

S1, S3 closed, measure under all possible position of S2.

Single fault condition: S1 open with S3 close or S1 close with S3 open.


CLASS II equipment:

S3 open, Protection Earth not connected, measure under all combination of position of S1 and S2.

Single fault condition: S1 open.

測定回路5 Circuit 5 used for determination

- 出力リップル、ノイズ波形 Output ripple and noise waveform




測定構成 Configuration used for determination


CUS30M

- E M I 特性 Electro-Magnetic Interference characteristics
- (a) 雜音端子電圧 (帰還ノイズ) Conducted Emission

CLASS I setup:




CLASS II setup:




(b) 雜音電界強度 (放射ノイズ) Radiated Emission

CLASS I setup:



CLASS II setup:



1.2 使用測定機器 List of equipment used

	EQUIPMENT USED	MANUFACTURER	MODEL NO.
1	DIGITAL STORAGE OSCILLOSCOPE	YOKOGAWA ELECT.	DL2054/DL9040
2	DIGITAL MULTIMETER	AGILENT	34970A
3	DIGITAL POWER METER	YOKOGAWA ELECT.	WT210
4	CURRENT PROBE	TEKTRONIX	63202
5	DC AMPERE METER	TEKTRONIX	P5100
6	DYNAMIC DUMMY LOAD	CHROMA	63030/63610/63640
7	AC SOURCE	KIKUSUI	PCR2000L
8	AC SOURCE	TAKAMISAWA	PSA-210
9	EARTH LEAKAGE CURRENT METER	SIMPSON	228
10	PATIENT LEAKAGE CURRENT METER	SIQ	SIQ16042
11	CONTROLLED TEMP. CHAMBER	TABAII-ESPEC	63203
12	EMI TEST RECEIVER	ROHDE & SCHWARZ	ESCI-03
13	LISN	ROHDE & SCHWARZ	ENV216
14	BICONICAL ANTENNA	EMCO	63208

2. 特性データ

Characteristics

CUS30M

2.1 静特性 Steady state data

(1) 入力・負荷・温度変動／出力起動・遮断電圧

Regulation - line and load, Temperature drift / Start up voltage and Drop out voltage

12V
(CUS30M-12)

1. Regulation - line and load

Condition Ta : 25 °C

Iout \ Vin	85VAC	115VAC	230VAC	265VAC	line regulation	
0%	12.074V	12.074V	12.075V	12.075V	1mV	0.008%
50%	12.050V	12.050V	12.050V	12.051V	1mV	0.008%
100%	12.025V	12.026V	12.026V	12.026V	1mV	0.008%
load regulation	49mV	48mV	49mV	49mV		
	0.408%	0.400%	0.408%	0.408%		

2. Temperature drift

Conditions Vin : 115 VAC
Iout : 100 %

Ta	-20°C	+25°C	+50°C	temperature stability
Vout	11.989V	12.026V	12.023V	37mV 0.004%

3. Start up voltage and Drop out voltage

Conditions Ta : 25 °C
Iout : 100 %

Start up voltage (Vin)	60.0Vac
Drop out voltage (Vin)	61.0Vac

24V
(CUS30M-24)

1. Regulation - line and load

Condition Ta : 25 °C

Iout \ Vin	85VAC	115VAC	230VAC	265VAC	line regulation	
0%	24.053V	24.054V	24.056V	24.058V	5mV	0.021%
50%	24.033V	24.033V	24.028V	24.026V	7mV	0.029%
100%	24.009V	24.003V	24.001V	24.001V	8mV	0.033%
load regulation	44mV	51mV	55mV	57mV		
	0.183%	0.212%	0.229%	0.237%		

2. Temperature drift

Conditions Vin : 115 VAC
Iout : 100 %

Ta	-20°C	+25°C	+50°C	temperature stability
Vout	23.981V	24.003V	23.972V	31mV 0.004%

3. Start up voltage and Drop out voltage

Conditions Ta : 25 °C
Iout : 100 %

Start up voltage (Vin)	61.0Vac
Drop out voltage (Vin)	63.0Vac

2. 特性データ

Characteristics

CUS30M

2.1 静特性 Steady state data

(1) 入力・負荷・温度変動／出力起動・遮断電圧

Regulation - line and load, Temperature drift / Start up voltage and Drop out voltage

48V
(CUS30M-48)

1. Regulation - line and load

Condition Ta : 25 °C

Iout \ Vin	85VAC	115VAC	230VAC	265VAC	line regulation	
0%	47.771V	47.772V	47.775V	47.779V	8mV	0.017%
50%	47.757V	47.759V	47.759V	47.758V	2mV	0.004%
100%	47.742V	47.744V	47.744V	47.742V	2mV	0.004%
load regulation	29mV	28mV	31mV	37mV		
	0.060%	0.058%	0.065%	0.077%		

2. Temperature drift

Conditions Vin : 115 VAC
Iout : 100 %

Ta	-20°C	+25°C	+45°C	temperature stability
Vout	47.529V	47.744V	47.810V	281mV 0.009%

3. Start up voltage and Drop out voltage

Conditions Ta : 25 °C
Iout : 100 %

Start up voltage (Vin)	61.5Vac
Drop out voltage (Vin)	65.0Vac


(2) 効率対出力電流

Efficiency vs. Output current

Conditions Vin : 85 VAC -----
 : 115 VAC - - - -
 : 230 VAC ——————
 : 265 VAC - - - -
Ta : 25 °C


12V

(CUS30M-12)



24V

(CUS30M-24)




(2) 効率対出力電流

Efficiency vs. Output current

Conditions Vin : 85 VAC -----
 : 115 VAC - - - -
 : 230 VAC —————
 : 265 VAC - - - -
Ta : 25 °C

48V

(CUS30M-48)



(3) 入力電流対出力電流


Input current vs. Output current

Conditions Vin : 85 VAC -----
 : 115 VAC - - - -
 : 230 VAC ————
 : 265 VAC - - - -
 Ta : 25 °C

12V

(CUS30M-12)


Io: 100%	
Vin	Input current
85Vac	0.693A
115Vac	0.554A
230Vac	0.344A
265Vac	0.311A



24V

(CUS30M-24)

Io: 100%	
Vin	Input current
85Vac	0.678A
115Vac	0.550A
230Vac	0.340A
265Vac	0.305A



(3) 入力電流対出力電流


Input current vs. Output current

48V

(CUS30M-48)

Io: 100%	
Vin	Input current
85Vac	0.663A
115Vac	0.524A
230Vac	0.318A
265Vac	0.290A

Conditions Vin : 85 VAC -----
 : 115 VAC -----
 : 230 VAC ————
 : 265 VAC -----
 Ta : 25 °C



(4) 入力電力対出力電流


Input power vs. Output current

Conditions Vin : 85 VAC -----
 : 115 VAC - - -
 : 230 VAC ———
 : 265 VAC - - - -
 Ta : 25 °C

12V
(CUS30M-12)

Io: 100%


Vin	Input power
85Vac	35.41W
115Vac	34.48W
230Vac	33.96W
265Vac	33.92W



24V
(CUS30M-24)

Io: 100%

Vin	Input power
85Vac	34.86W
115Vac	33.79W
230Vac	33.29W
265Vac	33.30W



(4) 入力電力対出力電流


Input power vs. Output current

Conditions Vin : 85 VAC -----
 : 115 VAC - - -
 : 230 VAC ———
 : 265 VAC - - - -
 Ta : 25 °C

48V
 (CUS30M-48)



Io: 100%

Vin	Input power
85Vac	34.31W
115Vac	33.61W
230Vac	32.97W
265Vac	33.15W




2.2 過電流保護特性

Over current protection (OCP) characteristics



2.2 過電流保護特性

Over current protection (OCP) characteristics




2.3 過電圧保護特性


Over voltage protection (OVP) characteristics

12V
(CUS30M-12)

Conditions Vin : 115 VAC
 Iout : 0 %
 Ta : 25 °C



Conditions Vin : 230 VAC
 Iout : 0 %
 Ta : 25 °C




2.3 過電圧保護特性

Over voltage protection (OVP) characteristics


24V

(CUS30M-24)

Conditions Vin : 115 VAC
 Iout : 0 %
 Ta : 25 °C



Conditions Vin : 230 VAC
 Iout : 0 %
 Ta : 25 °C




2.3 過電圧保護特性

Over voltage protection (OVP) characteristics


48V

(CUS30M-48)

Conditions Vin : 115 VAC
 Iout : 0 %
 Ta : 25 °C



Conditions Vin : 230 VAC
 Iout : 0 %
 Ta : 25 °C




2.4 出力立ち上がり特性
Output rise characteristics

CUS30M


Conditions Vin : 85 VAC (A)
 115 VAC (B)
 230 VAC (C)
 265 VAC (D)
Ta : 25 °C

12V
(CUS30M-12)

Iout : 0%




Iout : 100%




24V
(CUS30M-24)

Iout : 0%



Iout : 100%




2.4 出力立ち上がり特性
Output rise characteristics

CUS30M


Conditions Vin : 85 VAC (A)
 115 VAC (B)
 230 VAC (C)
 265 VAC (D)
Ta : 25 °C

48V
(CUS30M-48)

Iout : 0%



Iout : 100%



2.5 出力立ち下がり特性

Output fall characteristics

CUS30M

Conditions Vin : 85 VAC (A)

115 VAC (B)

230 VAC (C)

265 VAC (D)



Ta : 25 °C

12V

(CUS30M-12)

Iout : 0%

Iout : 100%





24V

(CUS30M-24)

Iout : 0%

Iout : 100%



2.5 出力立ち下がり特性

Output fall characteristics

CUS30M

Conditions Vin : 85 VAC (A)

115 VAC (B)

230 VAC (C)

265 VAC (D)


Ta : 25 °C

48V

(CUS30M-48)

Iout : 0%

Iout : 100%




2.6 出力保持時間特性


Hold up time characteristics

Conditions Vin : 115 VAC -----
 230 VAC ————
 Ta : 25 °C

12V
(CUS30M-12)



24V
(CUS30M-24)




2.6 出力保持時間特性

Hold up time characteristics

Conditions Vin : 115 VAC -----
 230 VAC ——
 Ta : 25 °C

48V
(CUS30M-48)



2.7 過渡応答（負荷急変）特性

Dynamic load response characteristics

Conditions

Vin : 115 VAC

Iout : 25 % \leftrightarrow 75 %


(tr = tf = 50us)

Ta : 25 °C


12V

(CUS30M-12)

f = 100Hz




f = 1kHz




24V

(CUS30M-24)

f = 100Hz



f = 1kHz



2.7 過渡応答（負荷急変）特性

Dynamic load response characteristics

Conditions

Vin : 115 VAC

Iout : 25 % \leftrightarrow 75 %


(tr = tf = 50us)

Ta : 25 °C


48V

(CUS30M-48)

f = 100Hz



f = 1kHz




2.7 過渡応答（負荷急変）特性
Dynamic load response characteristics

Conditions Vin : 230 VAC
 Iout : 25 % \leftrightarrow 75 %
 (tr = tf = 50us)
 Ta : 25 °C


12V

(CUS30M-12)

f = 100Hz



f = 1kHz





24V

(CUS30M-24)

f = 100Hz

f = 1kHz



2.7 過渡応答（負荷急変）特性

Dynamic load response characteristics

Conditions

Vin : 230 VAC

Iout : 25 % \leftrightarrow 75 %


(tr = tf = 50us)

Ta : 25 °C


48V

(CUS30M-48)

f = 100Hz



f = 1kHz




2.8 入力電圧瞬停特性

Response to brown out characteristics

Conditions
 Vin : 115 VAC
 Iout : 100 %
 Ta : 25 °C


12V
(CUS30M-12)

A = 25ms
 B = 32ms
 C = 40ms



24V
(CUS30M-24)


A=27ms
 B=32ms
 C=47ms



2.8 入力電圧瞬停特性

Response to brown out characteristics

Conditions
Vin : 115 VAC
Iout : 100 %
Ta : 25 °C




2.8 入力電圧瞬停特性


Response to brown out characteristics

Conditions
 Vin : 230 VAC
 Iout : 100 %
 Ta : 25 °C

12V
(CUS30M-12)




24V
(CUS30M-24)



2.8 入力電圧瞬停特性

Response to brown out characteristics


Conditions
Vin : 230 VAC
Iout : 100 %
Ta : 25 °C



2.9 入力サージ電流（突入電流）波形
Inrush current waveform


12V
(CUS30M-12)

Switch on phase angle of input AC voltage
 $\Phi=0^\circ$




Conditions Vin : 115 VAC
Iout : 100 %
Ta : 25 °C
Cold start

Switch on phase angle of input AC voltage
 $\Phi=90^\circ$




Switch on phase angle of input AC voltage
 $\Phi=0^\circ$



Conditions Vin : 230 VAC
Iout : 100 %
Ta : 25 °C
Cold start


Switch on phase angle of input AC voltage
 $\Phi=90^\circ$



2.9 入力サージ電流（突入電流）波形
Inrush current waveform


24V
(CUS30M-24)

Switch on phase angle of input AC voltage
 $\Phi=0^\circ$




Conditions V_{in} : 115 VAC
 I_{out} : 100 %
 T_a : 25 °C
 Cold start

Switch on phase angle of input AC voltage
 $\Phi=90^\circ$




Switch on phase angle of input AC voltage
 $\Phi=0^\circ$



Conditions V_{in} : 230 VAC
 I_{out} : 100 %
 T_a : 25 °C
 Cold start


Switch on phase angle of input AC voltage
 $\Phi=90^\circ$



2.9 入力サージ電流（突入電流）波形
Inrush current waveform


48V
(CUS30M-48)

Switch on phase angle of input AC voltage
 $\Phi=0^\circ$




Conditions Vin : 115 VAC
Iout : 100 %
Ta : 25 °C
Cold start

Switch on phase angle of input AC voltage
 $\Phi=90^\circ$




Switch on phase angle of input AC voltage
 $\Phi=0^\circ$



Conditions Vin : 230 VAC
Iout : 100 %
Ta : 25 °C
Cold start

Switch on phase angle of input AC voltage
 $\Phi=90^\circ$



2.10 リーク電流特性

Leakage current characteristics

CUS30M


Conditions Iout : 0 % -----
 100 % ———
 Ta : 25 °C
 Equipment used : SIQ16042

12V
(CUS30M-12)


Patient leakage current of CLASS I equipment

f : 50 Hz

Normal condition




Single fault condition(Open FG)




f : 60 Hz

Normal condition



Single fault condition(Open FG)




Conditions I_{out} : 0 % -----
 100 % ———
 Ta : 25 °C
 Equipment used : SIQ16042

12V
(CUS30M-12)


Patient leakage current of CLASS II equipment

 f : 50 Hz


Normal condition




Single fault condition(Open L or N)

 f : 60 Hz

Normal condition



Single fault condition(Open L or N)



2.10 リーク電流特性

Leakage current characteristics

CUS30M


Conditions Iout : 0 % -----
 100 % ——
 Ta : 25 °C
 Equipment used : SIMPSON228

12V
(CUS30M-12)


Earth leakage current of CLASS I equipment

f : 50 Hz

Normal condition




Single fault condition(Open L or N)




f : 60 Hz

Normal condition



Single fault condition(Open L or N)



2.10 リーク電流特性

Leakage current characteristics

CUS30M

Conditions Iout : 0 % -----
 100 % ——
 Ta : 25 °C
 Equipment used : SIQ16042


24V

(CUS30M-24)


Patient leakage current of CLASS I equipment

f : 50 Hz

Normal condition




Single fault condition(Open FG)




f : 60 Hz

Normal condition



Single fault condition(Open FG)



2.10 リーク電流特性

Leakage current characteristics

CUS30M


Conditions Iout : 0 % -----
 100 % ——
 Ta : 25 °C
 Equipment used : SIQ16042

24V
(CUS30M-24)


Patient leakage current of CLASS II equipment

f : 50 Hz

Normal condition




Single fault condition(Open L or N)




f : 60 Hz

Normal condition



Single fault condition(Open L or N)



2.10 リーク電流特性

Leakage current characteristics

CUS30M


Conditions I_{out} : 0 % -----
 100 % ———
 Ta : 25 °C
 Equipment used : SIMPSON228

24V
(CUS30M-24)


Earth leakage current of CLASS I equipment

 f : 50 Hz


Normal condition




Single fault condition(Open L or N)

 f : 60 Hz

Normal condition



Single fault condition(Open L or N)




Conditions I_{out} : 0 % -----
 100 % ———
 Ta : 25 °C
 Equipment used : SIQ16042

48V
(CUS30M-48)


Patient leakage current of CLASS I equipment

 f : 50 Hz


Normal condition




Single fault condition(Open FG)

 f : 60 Hz

Normal condition



Single fault condition(Open FG)




Conditions I_{out} : 0 % -----
 100 % ———
 Ta : 25 °C
 Equipment used : SIQ16042

48V
(CUS30M-48)


Patient leakage current of CLASS II equipment

 $f = 50 \text{ Hz}$


Normal condition




Single fault condition(Open L or N)

 $f = 60 \text{ Hz}$

Normal condition



Single fault condition(Open L or N)



2.10 リーク電流特性

Leakage current characteristics

CUS30M


Conditions I_{out} : 0 % -----
 100 % ———
 Ta : 25 °C
 Equipment used : SIMPSON228

48V
(CUS30M-48)


Earth leakage current of CLASS I equipment

 f : 50 Hz


Normal condition




Single fault condition(Open L or N)

 f : 60 Hz

Normal condition



Single fault condition(Open L or N)




2.11 出力リップル、ノイズ波形
Output ripple and noise waveform

CUS30M
Conditions
Vin : 115 VAC
Ta : 25 °C


12V

(CUS30M-12)

Iout : 100%




Iout : 100%




24V

(CUS30M-24)

Iout : 100%



Iout : 100%



CUS30M

2.11 出力リップル、ノイズ波形
Output ripple and noise waveform

Conditions



Vin : 115 VAC
Ta : 25 °C

48V

(CUS30M-48)

Iout : 100%

Iout : 100%




2.11 出力リップル、ノイズ波形
Output ripple and noise waveform

CUS30M
Conditions
Vin : 230 VAC
Ta : 25 °C


12V

(CUS30M-12)

Iout : 100%




Iout : 100%




24V

(CUS30M-24)

Iout : 100%



Iout : 100%




2.11 出力リップル、ノイズ波形
Output ripple and noise waveform

CUS30M
Conditions
Vin : 230 VAC
Ta : 25 °C


48V

(CUS30M-48)

Iout : 100%



Iout : 100%



2.12 EMI 特性

Electro-Magnetic Interference characteristics

CUS30M

Conditions
 Vin : 115 VAC
 Iout : 100 %
 Ta : 25 °C


雜音端子電圧

Conducted Emission (CLASS I)


12V

(CUS30M-12)

Point A (0.195MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	63.8	53.8
AV	53.6	38.2



Point B (0.190MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	64.0	51.3
AV	53.8	35.5



EN55011-B,VCCI-B,FCC-Bの限界値はEN55032 class Bの限界値と同じ

Limit of EN55011-B,VCCI-B,FCC-B are same as its EN55032 class B.


雜音端子電圧

Conducted Emission (CLASS I)


12V

(CUS30M-12)

Point A (0.195MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	63.8	51.8
AV	53.4	33.7



Point B (0.20MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	63.6	51.5
AV	53.4	32.1



EN55011-B,VCCI-B,FCC-Bの限界値はEN55032 class Bの限界値と同じ

Limit of EN55011-B,VCCI-B,FCC-B are same as its EN55032 class B.

2.12 EM I 特性

Electro-Magnetic Interference characteristics

Conditions
 Vin : 115 VAC
 Iout : 100 %
 Ta : 25 °C


雜音端子電圧

Conducted Emission (CLASS II)


12V

(CUS30M-12)

Point A (0.195MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	63.8	54.9
AV	53.8	42.1



Point B (0.204MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	63.4	51.7
AV	53.8	41.1



EN55011-B,VCCI-B,FCC-Bの限界値はEN55032 class Bの限界値と同じ

Limit of EN55011-B,VCCI-B,FCC-B are same as its EN55032 class B.

2.12 EM I 特性

Electro-Magnetic Interference characteristics

Conditions Vin : 230 VAC
 Iout : 100 %
 Ta : 25 °C


雜音端子電圧

Conducted Emission (CLASS II)


12V

(CUS30M-12)

Point A (0.195MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	63.8	53.8
AV	53.4	42.6



Point B (0.204MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	63.4	54.2
AV	53.8	44.8



EN55011-B,VCCI-B,FCC-Bの限界値はEN55032 class Bの限界値と同じ

Limit of EN55011-B,VCCI-B,FCC-B are same as its EN55032 class B.

2.12 EM I 特性

Electro-Magnetic Interference characteristics

Conditions Vin : 115 VAC
 Iout : 100 %
 Ta : 25 °C


雜音端子電圧

Conducted Emission (CLASS I)


24V

(CUS30M-24)

Point A (0.21MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	63.8	54.1
AV	53.8	34.7



Point B (0.20MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	63.8	53.2
AV	53.8	36.8



EN55011-B,VCCI-B,FCC-Bの限界値はEN55032 class Bの限界値と同じ

Limit of EN55011-B,VCCI-B,FCC-B are same as its EN55032 class B.


雜音端子電圧

Conducted Emission (CLASS I)


24V

(CUS30M-24)

Point A (0.19MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	63.8	53.1
AV	53.8	31.0



Point B (0.19MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	63.8	53.0
AV	53.8	32.2



EN55011-B,VCCI-B,FCC-Bの限界値はEN55032 class Bの限界値と同じ

Limit of EN55011-B,VCCI-B,FCC-B are same as its EN55032 class B.

2.12 EM I 特性

Electro-Magnetic Interference characteristics

Conditions Vin : 115 VAC
 Iout : 100 %
 Ta : 25 °C


雜音端子電圧

Conducted Emission (CLASS II)


24V

(CUS30M-24)

Point A (1.88MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	63.8	55.0
AV	53.8	44.1



Point B (3.18MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	63.8	55.9
AV	53.8	42.6



EN55011-B,VCCI-B,FCC-Bの限界値はEN55032 class Bの限界値と同じ

Limit of EN55011-B,VCCI-B,FCC-B are same as its EN55032 class B.

2.12 EM I 特性

Electro-Magnetic Interference characteristics

Conditions Vin : 230 VAC
 Iout : 100 %
 Ta : 25 °C


雜音端子電圧

Conducted Emission (CLASS II)


24V

(CUS30M-24)

Point A (0.20MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	63.8	56.8
AV	53.8	44.0



Point B (0.20MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	63.8	57.4
AV	53.8	47.3



EN55011-B,VCCI-B,FCC-Bの限界値はEN55032 class Bの限界値と同じ

Limit of EN55011-B,VCCI-B,FCC-B are same as its EN55032 class B.

2.12 EMI 特性

Electro-Magnetic Interference characteristics

CUS30M

Conditions
 Vin : 115 VAC
 Iout : 100 %
 Ta : 25 °C


雜音端子電圧

Conducted Emission (CLASS I)


48V

(CUS30M-48)

Point A (0.195MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	63.8	52.0
AV	53.6	35.0



Point B (0.195MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	63.8	48.6
AV	53.8	30.9



EN55011-B,VCCI-B,FCC-Bの限界値はEN55032 class Bの限界値と同じ

Limit of EN55011-B,VCCI-B,FCC-B are same as its EN55032 class B.

2.12 EMI 特性

CUS30M

Electro-Magnetic Interference characteristics

Conditions

Vin : 230 VAC

Iout : 100 %

Ta : 25 °C


雜音端子電圧

Conducted Emission (CLASS I)


48V

(CUS30M-48)

Point A (0.929MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	56.0	39.6
AV	46.0	30.0



Point B (0.925MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	56.0	39.3
AV	46.0	29.1



EN55011-B,VCCI-B,FCC-Bの限界値はEN55032 class Bの限界値と同じ

Limit of EN55011-B,VCCI-B,FCC-B are same as its EN55032 class B.

2.12 EMI 特性

Electro-Magnetic Interference characteristics

Conditions Vin : 115 VAC
 Iout : 100 %
 Ta : 25 °C


雜音端子電圧

Conducted Emission (CLASS II)


48V

(CUS30M-48)

Point A (0.195MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	63.8	53.9
AV	53.8	39.8



Point B (0.200MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	63.6	49.2
AV	53.6	39.3



EN55011-B,VCCI-B,FCC-Bの限界値はEN55032 class Bの限界値と同じ

Limit of EN55011-B,VCCI-B,FCC-B are same as its EN55032 class B.

2.12 EMI 特性

Electro-Magnetic Interference characteristics

Conditions Vin : 230 VAC
 Iout : 100 %
 Ta : 25 °C


雜音端子電圧

Conducted Emission (CLASS II)


48V

(CUS30M-48)

Point A (0.303MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	60.2	53.9
AV	50.2	44.9



Point B (0.299MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	60.3	52.9
AV	50.3	43.8



EN55011-B,VCCI-B,FCC-Bの限界値はEN55032 class Bの限界値と同じ

Limit of EN55011-B,VCCI-B,FCC-B are same as its EN55032 class B.

2.12 EMI 特性

Electro-Magnetic Interference characteristics

Conditions Vin : 115 VAC
 Iout : 100 %
 Ta : 25 °C


雜音電界強度

Radiated Emission (CLASS I)


12V

(CUS30M-12)

Point A (183.2MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	40.0	20.2



Point B (34.7MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	40.0	28.1



2.12 EMI 特性

Electro-Magnetic Interference characteristics

Conditions

Vin : 230 VAC

Iout : 100 %

Ta : 25 °C


雜音電界強度

Radiated Emission (CLASS I)


12V

(CUS30M-12)

Point A (182.4MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	40.0	20.1



Point B (30.6MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	40.0	26.8



2.12 EMI 特性

Electro-Magnetic Interference characteristics

Conditions Vin : 115 VAC
 Iout : 100 %
 Ta : 25 °C


雜音電界強度

Radiated Emission (CLASS II)


12V

(CUS30M-12)

Point A (183.3MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	40.0	22.4



Point B (64.1MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	40.0	32.0



2.12 EMI 特性

Electro-Magnetic Interference characteristics

Conditions

Vin : 230 VAC

Iout : 100 %

Ta : 25 °C


雜音電界強度

Radiated Emission (CLASS II)


12V

(CUS30M-12)

Point A (185.6MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	40.0	22.9



Point B (67.4MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	40.0	33.2



2.12 EMI 特性

Electro-Magnetic Interference characteristics

Conditions

Vin : 115 VAC

Iout : 100 %

Ta : 25 °C


雜音電界強度

Radiated Emission (CLASS I)


24V

(CUS30M-24)

Point A (1000MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	46.0	33.0



Point B (1000MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	46.0	33.0



2.12 EMI 特性

Electro-Magnetic Interference characteristics

Conditions

Vin : 230 VAC

Iout : 100 %

Ta : 25 °C


雜音電界強度

Radiated Emission (CLASS I)


24V

(CUS30M-24)

Point A (1000MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	46.0	33.0



Point B (1000MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	46.0	33.0



2.12 EMI 特性

Electro-Magnetic Interference characteristics

Conditions

Vin : 115 VAC

Iout : 100 %

Ta : 25 °C


雜音電界強度

Radiated Emission (CLASS II)


24V

(CUS30M-24)

Point A (200MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	40.0	30.0



Point B (50MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	40.0	34.0



2.12 EMI 特性

Electro-Magnetic Interference characteristics

Conditions

Vin : 230 VAC

Iout : 100 %

Ta : 25 °C


雜音電界強度

Radiated Emission (CLASS II)


24V

(CUS30M-24)

Point A (230MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	40.0	27.0


 EN55032
Class B
QP Limit

Point B (60MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	40.0	32.3


 EN55032
Class B
QP Limit

2.12 EMI 特性

Electro-Magnetic Interference characteristics

Conditions

Vin : 115 VAC

Iout : 100 %

Ta : 25 °C


雜音電界強度

Radiated Emission (CLASS I)


48V

(CUS30M-48)

Point A (1000MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	47.0	35.5



Point B (1000MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	47.0	35.0



2.12 EMI 特性

Electro-Magnetic Interference characteristics

Conditions

Vin : 230 VAC

Iout : 100 %

Ta : 25 °C


雜音電界強度

Radiated Emission (CLASS I)


48V

(CUS30M-48)

Point A (1000MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	47.0	36.0



Point B (1000MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	47.0	36.0



2.12 EMI 特性

Electro-Magnetic Interference characteristics

Conditions Vin : 115 VAC
 Iout : 100 %
 Ta : 25 °C


雜音電界強度

Radiated Emission (CLASS II)


48V

(CUS30M-48)

Point A (175MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	40.0	35.0



Point B (175MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	40.0	35.4



2.12 EMI 特性

Electro-Magnetic Interference characteristics

Conditions

Vin : 230 VAC

Iout : 100 %

Ta : 25 °C


雜音電界強度

Radiated Emission (CLASS II)

48V

(CUS30M-48)

Point A (172MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	40.0	31.2



Point B (63MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	40.0	36.9

