






Test Report issued under the responsibility of:







TEST REPORT IEC 62368-1 Audio/video, information and communication technology equipment Part 1: Safety requirements	
Report Number	E135494-A6085-CB-1
Date of issue	2024-05-08
Total number of pages	134
Name of Testing Laboratory preparing the Report	UL International Polska sp. z o.o.
Applicant's name	TDK-LAMBDA UK LTD
Address	KINGSLEY AVE ILFRACOMBE DEVON EX34 8ES UNITED KINGDOM
Test specification:	
Standard	IEC 62368-1: 2018
Test procedure.....	CB Scheme
Non-standard test method.....	N/A
TRF template used	IECEE OD-2020-F1:2021, Ed.1.4
Test Report Form No.....	IEC62368_1E
Test Report Form(s) Originator....	UL(US)
Master TRF	Dated 2022-04-14
Copyright © 2022 IEC System of Conformity Assessment Schemes for Electrotechnical Equipment and Components (IECEE System). All rights reserved.	
This publication may be reproduced in whole or in part for non-commercial purposes as long as the IECEE is acknowledged as copyright owner and source of the material. IECEE takes no responsibility for and will not assume liability for damages resulting from the reader's interpretation of the reproduced material due to its placement and context.	
If this Test Report Form is used by non-IECEE members, the IECEE/IEC logo and the reference to the CB Scheme procedure shall be removed.	
This report is not valid as a CB Test Report unless signed by an approved CB Testing Laboratory and appended to a CB Test Certificate issued by an NCB in accordance with IECEE 02.	
General disclaimer:	
The test results presented in this report relate only to the object tested.	
This report shall not be reproduced, except in full, without the written approval of the Issuing CB Testing Laboratory.	
The authenticity of this Test Report and its contents can be verified by contacting the NCB, responsible for this Test Report.	

Test Item Description	Power supply
Trade Mark(s)	TDK-Lambda 
Manufacturer	TDK-LAMBDA UK LTD KINGSLEY AVE ILFRACOMBE DEVON EX34 8ES UNITED KINGDOM
Model/Type reference	EFE400 or EFE-400 series Units may be marked with a Product Code: U4x or Y4x where x may be any number of characters. Unit Configuration Code (Description) may be prefixed by NS # (where # may be any number of characters indicating non- safety related model differences). May be prefixed by SP followed by / or – (SP represents a sales code). Followed by x-a-bcde-f-g-hij. See test report model differences for details of models and nomenclature. EFE400R or EFE-400R series Units may be marked with a Product Code: U4x or Y4x where x may be any number of characters. Unit Configuration Code (Description :) may be prefixed by NS # (where # may be any number of characters indicating non- safety related model differences). May be prefixed by SP followed by / or – (SP represents a sales code). Followed by x-a-bcde-km-f-g-hij. See test report model differences for details of models and nomenclature.
Ratings	100-240Vac, 45-440Hz, 6.1Arms Max, or, 133-318Vdc, 4.2Adc max

Responsible Testing Laboratory (as applicable), testing procedure and testing location(s):

<input checked="" type="checkbox"/>	CB Testing Laboratory:	
Testing location/ address	UL International Polska sp. z o.o. Równoległa 4, PL-02-235 Warszawa, Poland	
Tested by (name, function, signature)..... :	Kamil Janeczek / Project Handler	
Approved by (name, function, signature) .. :	Grzegorz Goraj / Reviewer	

<input type="checkbox"/>	Testing procedure: CTF Stage 1:	
Testing location/ address		
Tested by (name, function, signature)..... :		
Approved by (name, function, signature) .. :		

<input type="checkbox"/>	Testing procedure: CTF Stage 2:	
Testing location/ address :		
Tested by (name, function, signature)..... :		
Witnessed by (name, function, signature) .. :		
Approved by (name, function, signature) .. :		
<input checked="" type="checkbox"/>	Testing procedure: CTF Stage 3:	
<input type="checkbox"/>	Testing procedure: CTF Stage 4:	
Testing location/ address :		TDK-LAMBDA UK LTD, KINGSLEY AVENUE, ILFRACOMBE, DEVON, UNITED KINGDOM, EX34 8ES
Tested by (name, function, signature)..... :		Mark Gisbey / Test Engineer 
Witnessed by (name, function, signature) .. :		Mark John Desagun / Project Engineer 
Approved by (name, function, signature) .. :		Grzegorz Goraj / Reviewer 
Supervised by (name, function, signature) :		Kamil Janeczek / Project Handler 

<p>List of Attachments (including a total number of pages in each attachment):</p> <p>National Differences (46 pages) Enclosures (182 pages)</p>	
<p>Summary of testing:</p>	
<p>Tests performed (name of test and test clause):</p> <p>5.2.2.1-5.2.2.6 – CLASSIFICATION OF ELECTRICAL ENERGY SOURCES</p> <p>5.4.1.8 – DETERMINATION OF WORKING VOLTAGE</p> <p>5.4.1.10.3 – BALL PRESSURE TEST</p> <p>5.4.7, 5.4.1.5.3 – TESTS FOR SEMICONDUCTOR COMPONENTS AND CEMENTED JOINTS</p> <p>5.4.9.1 – ELECTRIC STRENGTH TEST – TYPE TESTING OF SOLID INSULATION</p> <p>5.5.2.2 – CAPACITOR DISCHARGE AFTER DISCONNECTION OF A CONNECTOR</p> <p>5.7.5 – TOUCH CURRENT MEASUREMENT – EARTHED ACCESSIBLE CONDUCTIVE PARTS – SINGLE-PHASE EQUIPMENT ON IT SYSTEM</p>	<p>Testing Location: Unless otherwise noted, test are all conducted in CTF Stage 3: TDK-LAMBDA UK LTD, KINGSLEY AVENUE, ILFRACOMBE, DEVON, UNITED KINGDOM, EX34 8ES</p> <p>Test data accepted based on CBTR Ref. No. E135494-A6005-1 issued on 2024-03-18, CBTC Ref. No. DK-81105-M2-UL issued on 2024-03-18. Test was conducted at TDK LAMBDA UK LTD, KINGSLEY AVENUE, ILFRACOMBE, DEVON, EX34 8ES, UNITED KINGDOM</p> <p>Test data accepted based on CBTR Ref. No. E135494-A6005-1 issued on 2024-03-18, CBTC Ref. No. DK-81105-M2-UL issued on 2024-03-18. Test was conducted at TDK LAMBDA UK LTD, KINGSLEY AVENUE, ILFRACOMBE, DEVON, EX34 8ES, UNITED KINGDOM</p> <p>Test data accepted based on CBTR Ref. No. E135494-A6005-1 issued on 2024-03-18, CBTC Ref. No. DK-81105-M2-UL issued on 2024-03-18. Test was conducted at TDK LAMBDA UK LTD, KINGSLEY AVENUE, ILFRACOMBE, DEVON, EX34 8ES, UNITED KINGDOM</p> <p>Multilayer PWB's accepted under CBTR Ref. No.: E349607-A23 dated 2014-07-31.</p> <p>Test data accepted based on CBTR Ref. No. E135494-A6005-1 issued on 2024-03-18, CBTC Ref. No. DK-81105-M2-UL issued on 2024-03-18. Test was conducted at TDK LAMBDA UK LTD, KINGSLEY AVENUE, ILFRACOMBE, DEVON, EX34 8ES, UNITED KINGDOM</p> <p>Additional tests were conducted under UL project 4790231446.11 to include the requirement of cl. 5.4.4.9 Solid insulation requirements at frequencies higher than 30 kHz</p> <p>Test data accepted based on CBTR Ref. No. E135494-A6005-1 issued on 2024-03-18, CBTC Ref. No. DK-81105-M2-UL issued on 2024-03-18. Test was conducted at TDK LAMBDA UK LTD, KINGSLEY AVENUE, ILFRACOMBE, DEVON, EX34 8ES, UNITED KINGDOM</p> <p>Test data accepted based on CBTR Ref. No. E135494-A6005-1 issued on 2024-03-18, CBTC Ref. No. DK-81105-M2-UL issued on 2024-03-18. Test was conducted</p>

B.2.5 – INPUT TEST: SINGLE PHASE	<p>at TDK LAMBDA UK LTD, KINGSLEY AVENUE, ILFRACOMBE, DEVON, EX34 8ES, UNITED KINGDOM</p> <p>Test data accepted based on CBTR Ref. No. E135494-A6005-1 issued on 2024-03-18, CBTC Ref. No. DK-81105-M2-UL issued on 2024-03-18. Test was conducted at TDK LAMBDA UK LTD, KINGSLEY AVENUE, ILFRACOMBE, DEVON, EX34 8ES, UNITED KINGDOM</p>
B.2.6, 5.4.1.4, 6.3, 9.3, B.1.5 – NORMAL OPERATING CONDITIONS TEMPERATURE MEASUREMENT	<p>Test data accepted based on CBTR Ref. No. E135494-A6005-1 issued on 2024-03-18, CBTC Ref. No. DK-81105-M2-UL issued on 2024-03-18. Test was conducted at TDK LAMBDA UK LTD, KINGSLEY AVENUE, ILFRACOMBE, DEVON, EX34 8ES, UNITED KINGDOM</p>
B.3 – SIMULATED ABNORMAL OPERATING CONDITIONS	<p>Test data accepted based on CBTR Ref. No. E135494-A6005-1 issued on 2024-03-18, CBTC Ref. No. DK-81105-M2-UL issued on 2024-03-18. Test was conducted at TDK LAMBDA UK LTD, KINGSLEY AVENUE, ILFRACOMBE, DEVON, EX34 8ES, UNITED KINGDOM</p>
B.4 – SIMULATED SINGLE FAULT CONDITIONS	<p>Test data accepted based on CBTR Ref. No. E135494-A6005-1 issued on 2024-03-18, CBTC Ref. No. DK-81105-M2-UL issued on 2024-03-18. Test was conducted at TDK LAMBDA UK LTD, KINGSLEY AVENUE, ILFRACOMBE, DEVON, EX34 8ES, UNITED KINGDOM</p>
G.5.3.3 – TRANSFORMER OVERLOAD	<p>Test data accepted based on CBTR Ref. No. E135494-A6005-1 issued on 2024-03-18, CBTC Ref. No. DK-81105-M2-UL issued on 2024-03-18. Test was conducted at TDK LAMBDA UK LTD, KINGSLEY AVENUE, ILFRACOMBE, DEVON, EX34 8ES, UNITED KINGDOM</p>
G.5.4.6.3 – ALTERNATIVE LOCKED-ROTOR OVERLOAD TEST FOR DC MOTORS	<p>Test data accepted based on CBTR Ref. No. E135494-A6005-1 issued on 2024-03-18, CBTC Ref. No. DK-81105-M2-UL issued on 2024-03-18. Test was conducted at TDK LAMBDA UK LTD, KINGSLEY AVENUE, ILFRACOMBE, DEVON, EX34 8ES, UNITED KINGDOM</p>
R.1-R.4 - LIMITED SHORT CIRCUIT TEST	<p>Test data accepted based on CBTR Ref. No. E135494-A6005-1 issued on 2024-03-18, CBTC Ref. No. DK-81105-M2-UL issued on 2024-03-18. Test was conducted at TDK LAMBDA UK LTD, KINGSLEY AVENUE, ILFRACOMBE, DEVON, EX34 8ES, UNITED KINGDOM</p>
T.2, 5.4.2.6, 5.4.3.2, G.15.2.6 – STEADY FORCE TEST, 10 N	<p>Test data accepted based on CBTR Ref. No. E135494-A6005-1 issued on 2024-03-18, CBTC Ref. No. DK-81105-M2-UL issued on 2024-03-18. Test was conducted at TDK LAMBDA UK LTD, KINGSLEY AVENUE, ILFRACOMBE, DEVON, EX34 8ES, UNITED KINGDOM</p>

Summary of compliance with National Differences (List of countries addressed):
 Australia - AU, New Zealand - NZ, China - CN, EU Group Differences, Japan - JP, United States of America - US, Canada - CA

BS EN IEC 62368-1:2020+A11:2020 (per customer's request shown separately)

The product fulfils the requirements of AS/NZS 62368.1:2022, EN IEC 62368-1:2020+A11:2020, J62368-1(2023), CSA/UL 62368-1:2019, GB 4943.1-2022, J62368-1(2023)

Use of uncertainty of measurement for decisions on conformity (decision rule) :

No decision rule is specified by the IEC standard, when comparing the measurement result with the applicable limit according to the specification in that standard. The decisions on conformity are made without applying the measurement uncertainty ("simple acceptance" decision rule, previously known as "accuracy method").

Other:... (to be specified, for example when required by the standard or client, or if national accreditation requirements apply)




Information on uncertainty of measurement:

The uncertainties of measurement are calculated by the laboratory based on application of criteria given by OD-5014 for test equipment and application of test methods, decision sheets and operational procedures of IECEE. IEC Guide 115 provides guidance on the application of measurement uncertainty principles and applying the decision rule when reporting test results within IECEE scheme, noting that the reporting of the measurement uncertainty for measurements is not necessary unless required by the test standard or customer.

Calculations leading to the reported values are on file with the NCB and testing laboratory that conducted the testing.

Copy of marking plate:

The artwork below may be only a draft. The use of certification marks on a product must be authorized by the respective NCBS that own these marks.

	<p>05-Sep-18 Made in the UK</p>
<p>TDK-Lambda EFE-400 www.emea.tdk-lambda.com</p>	
<p>Product Code : U4Y004K Serial Number : 8182480027 Description : EFE400-24-CCMDS Customer Data :</p>	 8182480027
	
<p>OUTPUT 24V_16.7A FAN SUPPLY 12V_0.25A</p>	<p>Refer to emea.tdk-lambda.com/manual for installation manual. For Test Certificate: Refer to http://testcert.emea.tdk-lambda.com pat: uk.tdk-lambda.com/patents</p>



 Made in the UK 10-Jul-12

 Standards: 62368-1, 60950-1 & 61010-1: 100-240Vac, 6.1A rms max, 45-440Hz.

TDK-Lambda EFE-400R

www.emea.tdk-lambda.com
 Product Code : Y40012C
 Serial Number : 1111111111
 Description : EFE400-24-CCMDS
 Customer Data :



1111111111



OUTPUT 24V_16.7A	Refer to emea.tdk-lambda.com/manual for installation manual. For Test Certificate: Refer to http://testcert.emea.tdk-lambda.com pat.uk.tdk-lambda.com/patents
FAN SUPPLY 12V_0.25A	

Refer to emea.tdk-lambda.com/manual for installation manual.
 For Test Certificate: Refer to <http://testcert.emea.tdk-lambda.com>
pat.uk.tdk-lambda.com/patents

OUTPUT 24V_16.7A
 FAN SUPPLY 12V_0.25A



Customer Data :

Description : EFE400-24-CCMDS

Serial Number : 8182480027

Product Code : U4Y004K

www.emea.tdk-lambda.com

TDK-Lambda EFE-400



8182480027

INPUT
 Standards
 62368-1, 60950-1 & 61010-1: 100-240Vac, 6.1A rms max, 45-440Hz
 62368-1 & 60950-1: 133-318Vdc, 4.2A dc max.

Made in the UK
 05-Sep-18



<p>pat: uk:tdk-lambda.com/patents http://testcert.emea.tdk-lambda.com For Test Certificate: Refer to for installation manual. Refer to emea.tdk-lambda.com/manual</p>	<p>OUTPUT 24V 16.7A FAN SUPPLY 12V 0.25A</p>
-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------	-----------------------------------------------------------------


 Customer Data : CUSTOMER
 Description : EFE400-24-CMDS
 Serial Number : 11111111111
 Product Code : Y40014A
www.emea.tdk-lambda.com
TDK-Lambda
EFE-400R


 11111111111

<p>Made in the UK 10-Jul-12</p>	<p>INPUT Standards 62368-1, 60950-1 & 61010-1: 100-240Vac, 6.1A rms max, 45-440Hz. 62368-1 & 60950-1: 133-318Vdc, 4.2A dc max.</p> 
-----------------------------------------	------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

Note: The above markings are the minimum requirements required by the safety lab. For the final production samples, the additional markings which do not give rise to misunderstanding may be added.

Test item particulars:	
Product group	built-in component
Classification of use by	Skilled person
Supply Connection	AC Mains DC Mains not mains connected: ES3
Supply tolerance	+10%/-10%
Supply connection – type	mating connector
Considered current rating of protective device	20 A; Location: building
Equipment mobility	for building-in
Over voltage category (OVC)	OVC II
Class of equipment	Class I
Special installation location	N/A
Pollution degree (PD)	PD 2
Manufacturer’s specified Tma (°C)	70°C (de-rated output power by 2.5% per °C above 50°C)
IP protection class	IPX0
Power systems	TN
Altitude during operation (m)	5000 m
Altitude of test laboratory (m)	2000 m or less
Mass of equipment (kg)	1kg max.
Possible test case verdicts:	
- test case does not apply to the test object.....:	N/A
- test object does meet the requirement.....:	P (Pass)
- test object does not meet the requirement.....:	F (Fail)
Testing:	
Date of receipt of test item	2023-02-09
Date (s) of performance of tests	2024-04-24
General remarks:	
<p>"(See Enclosure #)" refers to additional information appended to the report. "(See appended table)" refers to a table appended to the report.</p> <p>Throughout this report a <input type="checkbox"/> comma / <input checked="" type="checkbox"/> point is used as the decimal separator.</p>	
Manufacturer’s Declaration per sub-clause 4.2.5 of IEC62368-1:	

The application for obtaining a CB Test Certificate includes more than one factory location and a declaration from the Manufacturer stating that the sample(s) submitted for evaluation is (are) representative of the products from each factory has been provided

- Yes**
- Not applicable**

When differences exist; they shall be identified in the General product information section.

Name and address of factory (ies) : TDK-LAMBDA UK LTD
 KINGSLEY AVE
 ILFRACOMBE
 DEVON
 EX34 8ES UNITED KINGDOM

Panyu Trio Microtronics Co Ltd
 SHIJI INDUSTRIAL ESTATE
 DONGYONG
 NANSHA
 GUANGZHOU
 Guangdong Sheng 511453 CHINA

TDK-LAMBDA CORP
 2704-1 SETTAYA-MACHI
 NAGAOKA-SHI
 Niigata 940-1195 JAPAN

Trio-Tronics (Thailand) Ltd
 7/295 Mu. 6
 Map Yang Phon Sub-District
 Pluak Daeng District Rayong THAILAND

General product information and other remarks:

Product Description

The EFE400 or EFE-400 and EFE400R or EFE-400R Series are switch mode power supplies for building into host equipment.

Model Differences

EFE400 or EFE-400 models as described below:

Units may be marked with a Product Code: U4x or Y4x where x may be any number of characters.

Unit Configuration Code (Description) may be prefixed by NS # (where # may be any number of characters indicating non- safety related model differences).

May be prefixed by SP followed by / or – (SP represents a sales code)

Unit Configuration Code:

EFE400x-a-bcde-f-g-hij

Where:

x = Nothing or J for Japanese models (may have non-safety differences)

a = Channel 1 Output Voltage: any voltage within the Adjustment Range for the Vout (nom) from the Output Table below, e.g. 12.8 for 12.8V output (12Vout nom), 24.6 for 24.6V output (24Vout nom).

b = CN for Open Frame with fan output, CU for U chassis with fan output, CC for U chassis and cover with fan output, EC for U chassis and cover with fan (temperature controlled).

c = M for molex input connector or equivalent, J for JST connector or equivalent.

d = D for dual fused input, FL for single fuse input in the Live Line.

e = S for Standard Leakage, L for Low Leakage, R for Reduced Leakage, T for Tiny Leakage.*

f = Nothing for horizontal output connector, V for vertical output connector.

g = Nothing for standard channel 1 output voltage, xD or xPD where D is for units with programmed negative load regulation, PD is for units with programmed positive load regulation, x is the voltage of the regulation in 100mVolts and is within the Output Adjustment range (example, 7D = 0.7V of negative load regulation, 24PD = 2.4V of positive load regulation).

hij = Three numbers from 0 to 9 which denotes various output voltage/current settings within the specified ranges of each output for a particular unit or blank for standard output settings. (may define non-safety related parameters/feature, e.g. reduced primary current limit, reduced OVP).

Output Parameters

Standard models:

Output Channel	Vout Nom.	Adjustment Range (V)	Output Current (A)	Maximum Power (W)
Channel 1	12	11.4 - 13.2*	33.33	400 (530**)
	24	22.8 - 26.4*	16.67	400 (530**)
Fan output (optional)	12	Fixed	0.25	3

Variations and limitations of use:

1. Maximum ambient 70°C (de-rating output power 2.5% per °C above 50°C).
2. * Can be adjusted at the factory only.
3. Maximum continuous power output 400W (excluding fan output).
4. ** Peak power for 10 seconds maximum, maximum rms power of 400Wrms.

EFE400R or EFE-400R models as described below:

Units may be marked with a Product Code: U4x or Y4x where x may be any number of characters.

Unit Configuration Code (Description :) may be prefixed by NS # (where # may be any number of characters indicating non- safety related model differences).

Unit Configuration Code:

EFE400Rx-a-bcde-km-f-g-hij

Where:

x = Nothing or J for Japanese models (may have non-safety differences)
 a = Channel 1 Output Voltage: any voltage within the Adjustment Range for the Vout (nom) from the Output Table below.
 b = CN for Open Frame with fan output, CU for U chassis with fan output, CC for U chassis and cover with fan output, EC for U chassis and cover with fan (temperature controlled), NN for open frame with no fan output.
 c = M for molex input connector or equivalent, J for JST connector or equivalent.
 d = D for dual fused input, FL for single fuse input in the Live Line.
 e = S for Standard Leakage, L for Low Leakage, R for Reduced Leakage, T for Tiny Leakage.*
 f = Nothing for horizontal output connector, V for vertical output connector.
 g = Nothing for standard channel 1 output voltage, xD or xPD where D is for units with programmed negative load regulation, PD is for units with programmed positive load regulation, x is the voltage of the regulation in 100mVolts and is within the Output Adjustment range (example, 7D = 0.7V of negative load regulation, 24PD = 2.4V of positive load regulation).
 hij = Three numbers from 0 to 9 which denotes various output voltage/current settings within the specified ranges of each output for a particular unit or blank for standard output settings. (may define non-safety related parameters/feature, e.g. reduced primary current limit, reduced OVP).
 k = Y for or-ing device or N for none fitted.
 m = E for enable or T for inhibit.

Output Channel	Vout Nom.	Adjustment Range (V)	Max Output Current (A)	Maximum Power (W)
Channel 1	48	47-50*	8.5	400 (470**)
Fan output (optional)	12	Fixed	0.25	3

Variations and limitations of use:

1. Maximum ambient 70°C (de-rating output power 2.5% per °C above 50°C).
2. * Can be adjusted at the factory only.
3. Maximum continuous power output 400W (excluding fan output).
4. ** Peak power for 10 seconds maximum, maximum rms power of 400Wrms.

Series connection

It is possible to connect two units in series (EFE400 models only). Doing so changes the working voltages and also changes the Energy Source Classification. Refer to Conditions of Acceptability.

Additional Information

Factory Production Note: Model EFE400 Series is produced at all three Factories noted on the CB Certificate. Model EFE400R Series is produced in the UK and China Factories noted on the CB Certificate but is not produced in the Factory located in Japan.

Cooling for units with customer supplied air (all except EC models):

The following method must be used for determining the safe operation of PSUs.

The components listed in the following table must not exceed the temperatures given. To determine the component temperatures the heating tests must be conducted in accordance with the requirements of IEC62368-1. Consideration should also be given to the requirements of other safety standards.

Test requirements include: PSU to be fitted in its end-use equipment and operated under the most adverse conditions permitted in the end-use equipment Instruction Manual/specification and which will result in the highest temperatures in the PSU. To determine the most adverse conditions consideration should be given to the end use equipment maximum operating ambient, the PSU loading and input voltage, ventilation, end use equipment orientation, the position of doors & covers, etc. Temperatures should be monitored using type K fine wire thermocouples (secured with cyanoacrylate adhesive, or similar) placed on the hottest part of the component (out of any direct airflow) and the equipment should be run until all temperatures have stabilized.

COMPONENTS TO BE MONITORED

Circuit Ref.	Description	Max. Temperature (°C)
J1	Input connector	75* (105)
L1, L2	Common mode choke	core 115, wire 140
C7, C8	X capacitors	100
C9	Reservoir capacitor (electrolytic)	70 (105)
L3 (EFE400)	Boost choke	core 115, winding 140
L3 (EFE400R)	Boost choke/TRX	core 115, winding 120
TX2	Transformer winding	120
TX2	Transformer core	120
TX2	Transformer braid (to pin 13)	120
U2	Optocoupler	75
C11	Channel 1 output capacitor	90 (105)
L7	Channel 1 Output choke	115
L4	Primary choke (24V model only)	120 (130)
XU8	Fan regulator	95
XQ225	Boost FET (IMS board)	115
Q1(EFE400)	Channel 1 output FET	115
Q2(EFE400R)	Channel 1 output FET	115
XU3	Main driver IC	100
Various	All other electrolytic capacitors	90 (105)

See components to be monitored diagram in the Instruction Manual.

* For temperatures above 75°C a suitably temperature rated mating connector must be used.

Higher temperatures limits for electrolytic capacitors (in brackets) may be used but product life may be reduced.

Fans: The fan provided in this sub-assembly is provided with a fan guard to reduce the risk of operator contact with the rotor.

This report is a standard upgrade from IEC 62368-1 2nd edition to 3rd edition. Test data were accepted based on CBTR E135494-A6005-CB-1 and CBTC DK-81105-M2-UL dated 2024-03-18. Test records of 2nd edition are deemed representative for 3rd edition due to identical or onerous test methods were used and test results were found to meet edition 3 compliance criteria. The existing differences were covered by additional testing.

In this report, testing of ELECTRICAL STRENGTH TEST - TYPE TESTING OF SOLID INSULATION was conducted.

The test date and sample receipt date shown are those of the original testing and additional test under project no. 4790231446.

The marking label provided is representative of all models.

The following tests were selected as representative of the test program applicable to model covered by this CBTR: Input test: single phase (Cl. B.2.5), Operating temperature measurement conditions (Cl. B.2.6), Simulated Single Faults Conditions (B.4), Electric Strength (Cl. 5.4.9), Capacitor discharge after disconnection of a connector (Cl. 5.5.2.2), Touch current measurement - earth accessible conductive parts - single-phase equipment on TN or TT system, and Steady force test, 250 N (Cl. 4.4.3.2, T.5). These tests have been witnessed for models selected as representative of the standard covered by this report and the applicable test program. (4791153162, DA file 331).

The following scope limitations apply to this test report and additional evaluation and/or tests may be required when submitting this CB Report to a National Certification Body (NCB) to obtain a national mark:

- no EMC tests nor evaluation to EMC Directive 2004/108/EC and 2014/30/EU,
- no evaluation to RoHS Directives 2011/65/EU
- only English version of markings and instructions reviewed. Markings and instructions in French, German, Italian, Spanish and Portuguese or Chinese were not reviewed.

Technical Considerations

- The product was submitted and evaluated for use at the maximum ambient temperature (T_{ma}) permitted by the manufacturer's specification of : 50°C Full load, increasing to 70°C maximum (output power derated 2.5% per degree above 50°C)
- The product is intended for use on the following power systems : TN
- Considered current rating of protective device as part of the building installation (A) : 20
- Mains supply tolerance (%) or absolute mains supply : +10%/-10%
- The equipment disconnect device is considered to be : provided by the host installation
- The following are available from the Applicant upon request : Installation (Safety) Instructions / Manual
- The product was investigated to the following additional standard : AS/NZS 62368.1:2018, CAN/CSA C22.2 No. 62368-1:19, 3rd Edition, EN IEC 62368-1:2020+A11:2020, UL 62368-1 3rd Edition, Issued December 13, 2019
- PSU is linearly de-rated from 90Vac to 85Vac 5W per volt to 375W

Engineering Conditions of Acceptability

When installed in an end-product, consideration must be given to the following:

- The following product-line tests are conducted for this product : Earthing Continuity, Electric Strength
- The end-product Electric Strength Test is to be based upon a maximum working voltage of : Primary-Secondary: 402 Vrms, 768 Vpk, Primary-Earthed Dead Metal: 388 Vrms, 666 Vpk
- The following output circuits are at ES1 energy levels : 12V, 24V and Fan outputs
- The following output circuits are at ES2 energy levels : 48V output
- The following output circuits are at ES3 energy levels : Series connected outputs
- The following output circuits are at PS3 energy levels : All circuits
- The maximum investigated branch circuit rating is : 20 A
- The investigated Pollution Degree is : 2
- Proper bonding to the end-product main protective earthing termination is : Required
- An investigation of the protective bonding terminals has : been conducted
- The following end-product enclosures are required : Mechanical, Fire, Electrical
- The following components require special consideration during end-product Thermal (Heating) tests due to the indicated maximum temperature measurements during component-level testing : Models without a fan require component temperatures monitored as detailed in Additional Information.
- The equipment is suitable for direct connection to : AC and/or DC mains supply
- The power supply was evaluated to be used at altitudes up to : 5,000 m
- The equipment was evaluated for end-product where reverse polarity is prevented. Otherwise B.3.3 the test shall be considered in the end application
- The following magnetic devices (e.g. transformers or inductor) are provided with an OBJY3 insulation system with the indicated rating greater than Class A (105°C) : TX2, TX3, L3 and L5 (Class F) (155°C)
- The maximum of 2 units of EFE400 models having output voltage 12 VDC or 24 VDC can be connected in series. This allowance is not applicable for EFE400R models having output voltage 48 VDC.
- Series connected outputs are classified as ES3. Accessibility shall be determined in end-product
- DC supply tolerance is equal to +10% / -10% due to restriction of connection to a conditioned power supply system
- Equipment is not intended to be used at tropical climatic conditions